

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910112

Luminaire Tested: DFN2DIP-TR4F0-070D050US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910112
REPORT IS A COMBINATION OF REPORTS P900394 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D050US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10477.3 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910112
CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910112

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49	49	49	49
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42	42	42	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36	36	36	36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32	32	32	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28	28	28	28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25	25	25	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22	22	22	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18	18	18	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2321	2321	2321
5°	2325	2284	2299
10°	2302	2239	2224
15°	2270	2165	2108
20°	2228	2063	1966
25°	2185	1949	1829
30°	2128	1832	1655
35°	2071	1706	1503
40°	2014	1575	1327
45°	1947	1430	1169
50°	1878	1284	1014
55°	1806	1128	865
60°	1723	965	712
65°	1627	799	641
70°	1510	644	580
75°	1365	568	527
80°	1153	476	457
85°	803	318	343

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1947 cd/sqm



TEST NUMBER: P910112

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	2.6
10°-20°	751.7	7.2
20°-30°	1055.3	10.1
30°-40°	1150.4	11.0
40°-50°	1057.3	10.1
50°-60°	830.4	7.9
60°-70°	540.5	5.2
70°-80°	278.2	2.7
80°-90°	75.6	0.7
90°-100°	98.8	0.9
100°-110°	314.0	3.0
110°-120°	537.3	5.1
120°-130°	706.6	6.7
130°-140°	793.2	7.6
140°-150°	777.8	7.4
150°-160°	652.5	6.2
160°-170°	432.7	4.1
170°-180°	151.2	1.4
0°-30°	2080.9	19.9
0°-40°	3231.2	30.8
0°-60°	5118.9	48.9
0°-90°	6013.2	57.4
90°-120°	950.1	9.1
90°-150°	3227.7	30.8
90°-180°	4464.0	42.6
0°-180°	10477.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2922	2908	2874	2898	2890	277
15°	2779	2750	2660	2610	2583	783
25°	2522	2438	2263	2155	2115	1160
35°	2173	2038	1806	1639	1581	1360
45°	1777	1600	1322	1134	1071	1372
55°	1351	1145	859	701	651	1207
65°	912	698	460	370	362	904
75°	486	301	212	193	190	515
85°	114	58	50	50	50	130
90°	1	17	47	44	46	10
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P910112

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2921.6	2921.6	2921.6	2921.6	2921.6
2.5°	2934.8	2921.6	2892.5	2919.1	2913.8
5°	2921.6	2908.4	2874.0	2897.8	2889.9
7.5°	2897.8	2882.1	2845.1	2855.4	2842.3
10°	2866.1	2847.6	2794.8	2786.7	2771.0
12.5°	2826.5	2802.7	2731.2	2715.4	2686.2
15°	2778.8	2749.7	2659.9	2609.7	2583.3
17.5°	2723.3	2681.0	2569.9	2511.7	2469.4
20°	2659.9	2606.9	2474.8	2408.8	2350.5
22.5°	2591.2	2530.3	2376.8	2287.0	2247.6
25°	2522.4	2437.7	2263.2	2155.0	2115.2
27.5°	2440.5	2350.5	2157.5	2033.3	1972.4
30°	2353.3	2252.6	2041.0	1906.4	1834.9
32.5°	2268.6	2146.9	1930.3	1771.5	1705.3
35°	2173.4	2038.5	1806.0	1639.4	1581.0
37.5°	2080.9	1935.3	1689.6	1506.9	1441.1
40°	1983.0	1824.5	1567.8	1380.2	1311.4
42.5°	1882.6	1713.4	1446.3	1250.5	1184.7
45°	1776.9	1599.5	1322.1	1134.2	1070.8
47.5°	1676.4	1488.7	1203.2	1015.2	957.2
50°	1565.3	1377.7	1086.7	904.1	848.9
52.5°	1456.7	1258.4	975.6	801.1	750.9
55°	1351.0	1144.8	859.2	700.7	650.6
57.5°	1242.7	1031.2	756.3	608.1	565.8
60°	1131.7	920.1	647.7	513.1	470.7
62.5°	1023.3	811.8	555.1	428.4	407.3
65°	912.2	697.9	460.1	370.3	362.1
67.5°	806.5	592.2	370.3	325.1	317.3
70°	695.4	489.2	306.6	280.2	269.5
72.5°	589.7	393.8	256.4	235.4	230.0
75°	486.5	301.2	211.5	193.0	190.5
77.5°	383.4	214.0	166.6	155.9	150.7
80°	288.1	153.4	126.8	116.4	116.4
82.5°	200.9	103.2	87.3	81.9	81.9
85°	113.6	58.1	50.2	50.2	50.2
87.5°	42.3	21.0	21.0	18.5	18.5
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P910112

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P910112
 CATALOG NUMBER: DFN2DIP-TR4F0-070D050US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.73	11.62	11.63	12.54	13.70	6.70	7.60	7.60	8.51	9.67
	3H	12.41	13.21	13.32	14.13	15.32	7.90	8.70	8.81	9.62	10.81
	4H	13.02	13.78	13.95	14.71	15.91	8.35	9.11	9.28	10.03	11.23
	6H	13.45	14.14	14.38	15.08	16.29	8.68	9.37	9.61	10.31	11.52
	8H	13.58	14.24	14.52	15.19	16.40	8.77	9.43	9.71	10.38	11.59
	12H	13.64	14.27	14.59	15.21	16.45	8.82	9.45	9.76	10.39	11.62
4H	2H	10.76	11.51	11.69	12.44	13.64	7.31	8.06	8.24	8.99	10.19
	3H	12.59	13.22	13.53	14.18	15.39	8.66	9.29	9.60	10.25	11.46
	4H	13.29	13.86	14.24	14.81	16.05	9.21	9.79	10.17	10.74	11.98
	6H	13.80	14.30	14.77	15.27	16.51	9.64	10.13	10.60	11.11	12.35
	8H	13.98	14.44	14.95	15.41	16.66	9.77	10.23	10.73	11.20	12.45
	12H	14.08	14.49	15.06	15.48	16.74	9.84	10.25	10.82	11.24	12.50
8H	4H	13.26	13.72	14.22	14.69	15.94	9.50	9.96	10.46	10.93	12.18
	6H	13.83	14.21	14.82	15.22	16.47	10.02	10.40	11.01	11.41	12.66
	8H	14.04	14.38	15.04	15.38	16.65	10.21	10.55	11.21	11.55	12.82
	12H	14.18	14.48	15.19	15.47	16.79	10.34	10.63	11.34	11.62	12.94
12H	4H	13.21	13.63	14.20	14.61	15.87	9.51	9.92	10.49	10.91	12.17
	6H	13.80	14.14	14.80	15.14	16.41	10.07	10.41	11.07	11.41	12.68
	8H	14.03	14.32	15.03	15.31	16.63	10.28	10.58	11.29	11.57	12.89