

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910114

Luminaire Tested: DFN2DIP-TR4F0-070D060US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910114
REPORT IS A COMBINATION OF REPORTS P900411 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D060US840-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12360.8 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 110.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910114
CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910114

CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57	57	57	57
1	99	95	91	87	92	88	85	82	76	74	72	65	63	62	55	54	53	48	48	48	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44	40	40	40	40
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34	34	34	34
4	75	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29	29	29	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	32	35	31	28	25	25	25	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22	22	22	22
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22	20	20	20	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18	18	18	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16	16	16	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2185	2185	2185
5°	2189	2155	2169
10°	2171	2126	2140
15°	2139	2091	2094
20°	2096	2042	2047
25°	2053	1984	1992
30°	1999	1930	1923
35°	1948	1866	1850
40°	1886	1801	1780
45°	1823	1737	1709
50°	1755	1669	1627
55°	1683	1590	1551
60°	1602	1497	1464
65°	1514	1401	1362
70°	1402	1283	1251
75°	1246	1142	1150
80°	1059	963	955
85°	767	654	633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1823 cd/sqm



TEST NUMBER: P910114

CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	2.1
10°-20°	728.4	5.9
20°-30°	1070.5	8.7
30°-40°	1243.3	10.1
40°-50°	1241.7	10.0
50°-60°	1082.8	8.8
60°-70°	800.4	6.5
70°-80°	452.9	3.7
80°-90°	125.0	1.0
90°-100°	118.6	1.0
100°-110°	376.8	3.0
110°-120°	644.8	5.2
120°-130°	848.0	6.9
130°-140°	951.8	7.7
140°-150°	933.4	7.6
150°-160°	783.0	6.3
160°-170°	519.2	4.2
170°-180°	181.5	1.5
0°-30°	2057.8	16.6
0°-40°	3301.1	26.7
0°-60°	5625.6	45.5
0°-90°	7003.8	56.7
90°-120°	1140.1	9.2
90°-150°	3873.3	31.3
90°-180°	5357.0	43.3
0°-180°	12360.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2751	2751	2751	2751	2751	
5°	2751	2740	2711	2732	2727	261
15°	2618	2603	2568	2579	2566	737
25°	2370	2349	2304	2309	2304	1090
35°	2045	2018	1976	1960	1947	1277
45°	1664	1645	1605	1576	1566	1284
55°	1259	1243	1211	1180	1166	1126
65°	849	833	807	783	770	840
75°	444	439	426	410	415	474
85°	108	106	103	95	93	121
90°	2	21	57	53	55	12
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	



TEST NUMBER: P910114

CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.6	2750.6	2750.6	2750.6	2750.6
2.5°	2766.6	2753.4	2724.2	2750.6	2745.5
5°	2750.6	2740.3	2711.1	2732.1	2727.0
7.5°	2732.1	2716.3	2687.2	2708.6	2703.2
10°	2703.2	2684.6	2652.9	2674.0	2666.1
12.5°	2663.3	2647.7	2616.0	2629.1	2623.7
15°	2618.5	2602.7	2568.2	2578.9	2565.7
17.5°	2562.8	2547.2	2512.6	2525.9	2512.6
20°	2501.9	2486.3	2449.2	2457.1	2446.7
22.5°	2441.3	2417.5	2383.0	2383.0	2377.6
25°	2369.9	2348.7	2303.9	2309.0	2303.9
27.5°	2290.4	2271.9	2237.7	2229.8	2216.6
30°	2211.3	2189.9	2150.4	2142.5	2131.8
32.5°	2126.5	2110.8	2068.4	2052.5	2041.7
35°	2044.6	2018.2	1975.8	1959.8	1946.6
37.5°	1952.0	1928.1	1885.7	1867.2	1854.0
40°	1856.8	1835.5	1793.1	1769.6	1758.9
42.5°	1764.2	1742.9	1700.8	1674.2	1658.4
45°	1663.8	1645.3	1605.4	1576.5	1565.8
47.5°	1565.8	1547.3	1504.9	1475.7	1460.1
50°	1462.6	1449.4	1412.3	1375.3	1362.1
52.5°	1362.1	1343.6	1309.4	1280.2	1261.6
55°	1259.1	1243.1	1211.4	1179.7	1166.5
57.5°	1155.9	1142.7	1108.1	1076.4	1065.8
60°	1052.6	1042.2	1005.2	976.0	968.2
62.5°	952.1	933.6	907.3	880.9	870.2
65°	849.2	833.1	806.8	782.9	769.7
67.5°	743.4	729.9	706.3	687.8	677.1
70°	645.4	634.8	610.9	592.4	582.0
72.5°	544.9	534.3	521.1	502.6	494.7
75°	444.2	439.2	425.7	410.0	415.4
77.5°	354.5	343.8	338.4	330.5	322.8
80°	264.6	261.9	256.5	248.6	243.3
82.5°	179.9	179.9	177.3	166.7	166.7
85°	108.4	105.8	103.3	95.1	92.6
87.5°	47.7	42.4	37.1	29.2	26.4
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0



TEST NUMBER: P910114

CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3



TEST NUMBER: P910114
 CATALOG NUMBER: DFN2DIP-TR4F0-070D060US840-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.58	11.50	11.47	12.42	13.59	10.14	11.07	11.04	11.99	13.16
	3H	12.24	13.07	13.15	14.00	15.19	11.77	12.60	12.68	13.52	14.72
	4H	12.83	13.61	13.75	14.55	15.75	12.36	13.14	13.28	14.07	15.28
	6H	13.23	13.96	14.17	14.89	16.11	12.76	13.48	13.69	14.42	15.64
	8H	13.34	14.03	14.28	14.98	16.20	12.87	13.55	13.81	14.51	15.73
	12H	13.39	14.05	14.34	15.00	16.24	12.91	13.57	13.86	14.51	15.76
4H	2H	11.04	11.83	11.97	12.76	13.97	10.70	11.48	11.63	12.42	13.62
	3H	12.92	13.57	13.86	14.53	15.76	12.52	13.18	13.46	14.14	15.36
	4H	13.63	14.23	14.58	15.19	16.43	13.23	13.83	14.18	14.78	16.03
	6H	14.15	14.67	15.12	15.65	16.89	13.74	14.26	14.71	15.24	16.48
	8H	14.30	14.78	15.27	15.76	17.02	13.89	14.37	14.86	15.35	16.61
	12H	14.38	14.81	15.36	15.81	17.07	13.96	14.39	14.94	15.38	16.65
8H	4H	13.83	14.32	14.80	15.29	16.55	13.47	13.96	14.44	14.93	16.19
	6H	14.47	14.87	15.46	15.88	17.14	14.11	14.50	15.10	15.52	16.78
	8H	14.69	15.04	15.69	16.05	17.32	14.32	14.67	15.32	15.68	16.95
	12H	14.82	15.13	15.83	16.13	17.46	14.44	14.75	15.44	15.75	17.07
12H	4H	13.82	14.26	14.81	15.25	16.52	13.47	13.91	14.46	14.90	16.16
	6H	14.50	14.85	15.50	15.86	17.13	14.15	14.50	15.15	15.50	16.78
	8H	14.74	15.05	15.75	16.05	17.38	14.39	14.70	15.39	15.70	17.02