

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904581

Luminaire Tested: DFN2DIP-TR4F0-050D040US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904581
REPORT IS A COMBINATION OF REPORTS P901892 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D040US830-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7738.3 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1547	1547	1547
5°	1550	1523	1533
10°	1534	1493	1483
15°	1513	1444	1405
20°	1486	1375	1311
25°	1457	1299	1219
30°	1418	1221	1103
35°	1381	1137	1002
40°	1343	1050	885
45°	1298	954	779
50°	1252	856	676
55°	1204	752	577
60°	1148	643	475
65°	1084	533	427
70°	1007	429	386
75°	910	378	352
80°	769	317	305
85°	536	212	229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1298 cd/sqm

TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.4
10°-20°	501.1	6.5
20°-30°	703.6	9.1
30°-40°	766.9	9.9
40°-50°	704.9	9.1
50°-60°	553.6	7.2
60°-70°	360.3	4.7
70°-80°	185.5	2.4
80°-90°	49.6	0.6
90°-100°	41.9	0.5
100°-110°	156.4	2.0
110°-120°	414.8	5.4
120°-130°	688.0	8.9
130°-140°	730.8	9.4
140°-150°	679.2	8.8
150°-160°	546.1	7.1
160°-170°	351.9	4.5
170°-180°	121.1	1.6
0°-30°	1387.2	17.9
0°-40°	2154.2	27.8
0°-60°	3412.7	44.1
0°-90°	4008.1	51.8
90°-120°	613.2	7.9
90°-150°	2711.2	35.0
90°-180°	3730.0	48.2
0°-180°	7738.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	1	11	18	23	25	7
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7

TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4

TEST NUMBER: P904581

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.83	9.67	9.77	10.63	11.88	4.80	5.64	5.75	6.60	7.85
	3H	10.50	11.26	11.46	12.23	13.50	5.99	6.75	6.95	7.71	8.99
	4H	11.11	11.83	12.09	12.80	14.08	6.44	7.16	7.42	8.13	9.41
	6H	11.53	12.19	12.52	13.17	14.46	6.76	7.42	7.75	8.40	9.69
	8H	11.66	12.29	12.65	13.28	14.57	6.86	7.48	7.85	8.48	9.77
	12H	11.72	12.32	12.72	13.31	14.62	6.90	7.49	7.90	8.48	9.80
4H	2H	8.85	9.56	9.83	10.53	11.81	5.40	6.11	6.38	7.08	8.36
	3H	10.68	11.27	11.66	12.27	13.57	6.75	7.34	7.74	8.34	9.64
	4H	11.37	11.91	12.37	12.91	14.22	7.30	7.84	8.30	8.84	10.15
	6H	11.88	12.35	12.89	13.37	14.68	7.72	8.18	8.73	9.20	10.52
	8H	12.06	12.49	13.07	13.51	14.84	7.85	8.28	8.86	9.30	10.63
	12H	12.16	12.55	13.18	13.58	14.91	7.92	8.31	8.94	9.34	10.67
8H	4H	11.34	11.77	12.35	12.78	14.11	7.58	8.01	8.59	9.03	10.36
	6H	11.90	12.26	12.94	13.32	14.64	8.10	8.46	9.13	9.51	10.84
	8H	12.12	12.44	13.16	13.48	14.82	8.29	8.61	9.33	9.65	10.99
	12H	12.26	12.54	13.31	13.57	14.96	8.41	8.69	9.46	9.72	11.11
12H	4H	11.29	11.68	12.32	12.71	14.05	7.58	7.98	8.61	9.01	10.34
	6H	11.88	12.20	12.92	13.24	14.58	8.15	8.46	9.19	9.51	10.85
	8H	12.10	12.38	13.15	13.41	14.80	8.36	8.64	9.41	9.67	11.06

END OF REPORT