

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910155

Luminaire Tested: DFN2DIP-TR4F0-080D070US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910155
REPORT IS A COMBINATION OF REPORTS P901951 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-080D070US840-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14996.6 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 127.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2497	2497	2497
5°	2501	2463	2479
10°	2481	2429	2445
15°	2445	2389	2393
20°	2395	2334	2339
25°	2346	2267	2277
30°	2285	2205	2198
35°	2227	2132	2114
40°	2155	2059	2035
45°	2084	1985	1954
50°	2005	1907	1859
55°	1924	1818	1773
60°	1831	1711	1673
65°	1731	1601	1556
70°	1602	1467	1430
75°	1424	1306	1314
80°	1210	1101	1091
85°	875	747	723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2084 cd/sqm

TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.9	2.0
10°-20°	832.5	5.6
20°-30°	1223.4	8.2
30°-40°	1420.9	9.5
40°-50°	1419.1	9.5
50°-60°	1237.5	8.3
60°-70°	914.7	6.1
70°-80°	517.6	3.5
80°-90°	140.8	0.9
90°-100°	78.7	0.5
100°-110°	293.3	2.0
110°-120°	777.8	5.2
120°-130°	1290.0	8.6
130°-140°	1370.3	9.1
140°-150°	1273.5	8.5
150°-160°	1023.9	6.8
160°-170°	659.7	4.4
170°-180°	227.1	1.5
0°-30°	2351.8	15.7
0°-40°	3772.7	25.2
0°-60°	6429.3	42.9
0°-90°	8002.4	53.4
90°-120°	1149.7	7.7
90°-150°	5083.5	33.9
90°-180°	6994.0	46.6
0°-180°	14996.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3144	3144	3144	3144	3144	
5°	3144	3132	3098	3122	3117	298
15°	2992	2975	2935	2947	2932	843
25°	2708	2684	2633	2639	2633	1246
35°	2337	2306	2258	2240	2225	1459
45°	1902	1880	1835	1802	1790	1467
55°	1439	1421	1384	1348	1333	1287
65°	970	952	922	895	880	959
75°	508	502	487	469	475	542
85°	124	121	118	109	106	138
90°	2	21	34	43	47	14
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3143.5	3143.5	3143.5	3143.5	3143.5
2.5°	3161.8	3146.7	3113.4	3143.5	3137.8
5°	3143.5	3131.7	3098.4	3122.4	3116.6
7.5°	3122.4	3104.4	3071.1	3095.4	3089.4
10°	3089.4	3068.2	3031.9	3056.0	3047.1
12.5°	3043.8	3025.9	2989.6	3004.7	2998.6
15°	2992.5	2974.6	2935.1	2947.3	2932.2
17.5°	2929.0	2911.0	2871.6	2886.7	2871.6
20°	2859.4	2841.5	2799.1	2808.1	2796.2
22.5°	2790.2	2762.9	2723.4	2723.4	2717.3
25°	2708.4	2684.3	2633.0	2638.8	2633.0
27.5°	2617.6	2596.5	2557.3	2548.3	2533.2
30°	2527.2	2502.7	2457.6	2448.6	2436.4
32.5°	2430.3	2412.4	2363.9	2345.6	2333.5
35°	2336.6	2306.5	2258.1	2239.8	2224.7
37.5°	2230.8	2203.5	2155.2	2133.9	2118.9
40°	2122.1	2097.7	2049.3	2022.4	2010.1
42.5°	2016.3	1991.9	1943.8	1913.3	1895.4
45°	1901.5	1880.3	1834.7	1801.7	1789.6
47.5°	1789.6	1768.4	1719.9	1686.6	1668.6
50°	1671.5	1656.5	1614.1	1571.8	1556.7
52.5°	1556.7	1535.5	1496.4	1463.1	1441.9
55°	1439.0	1420.7	1384.5	1348.3	1333.1
57.5°	1321.0	1306.0	1266.5	1230.2	1218.0
60°	1203.0	1191.1	1148.7	1115.4	1106.4
62.5°	1088.1	1067.0	1036.8	1006.7	994.5
65°	970.5	952.2	922.0	894.7	879.7
67.5°	849.5	834.1	807.2	786.1	773.9
70°	737.6	725.4	698.2	677.0	665.1
72.5°	622.8	610.7	595.5	574.4	565.4
75°	507.7	501.9	486.6	468.6	474.6
77.5°	405.1	392.8	386.8	377.8	368.8
80°	302.5	299.2	293.2	284.2	278.0
82.5°	205.6	205.6	202.7	190.5	190.5
85°	123.8	120.9	118.1	108.8	105.8
87.5°	54.5	48.5	42.3	33.3	30.2
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P910155

CATALOG NUMBER: DFN2DIP-TR4F0-080D070US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.75	11.64	11.68	12.59	13.81	10.32	11.21	11.25	12.16	13.38
	3H	12.41	13.22	13.35	14.17	15.42	11.94	12.74	12.88	13.70	14.94
	4H	13.00	13.76	13.96	14.72	15.97	12.53	13.29	13.48	14.25	15.50
	6H	13.40	14.10	14.37	15.07	16.34	12.93	13.63	13.89	14.59	15.86
	8H	13.51	14.18	14.48	15.16	16.42	13.04	13.70	14.01	14.68	15.95
	12H	13.56	14.19	14.54	15.17	16.46	13.08	13.71	14.06	14.69	15.98
4H	2H	11.22	11.98	12.18	12.93	14.19	10.87	11.63	11.83	12.59	13.84
	3H	13.09	13.72	14.06	14.71	15.98	12.69	13.33	13.66	14.31	15.58
	4H	13.80	14.38	14.78	15.36	16.66	13.40	13.97	14.37	14.96	16.25
	6H	14.32	14.82	15.31	15.82	17.11	13.91	14.41	14.90	15.41	16.70
	8H	14.47	14.93	15.46	15.93	17.24	14.06	14.52	15.05	15.52	16.83
	12H	14.54	14.96	15.55	15.98	17.29	14.12	14.54	15.13	15.56	16.87
8H	4H	14.00	14.47	14.99	15.47	16.77	13.64	14.11	14.63	15.11	16.41
	6H	14.63	15.02	15.65	16.06	17.36	14.27	14.66	15.29	15.70	17.00
	8H	14.85	15.19	15.88	16.22	17.54	14.49	14.83	15.51	15.85	17.18
	12H	14.99	15.29	16.02	16.31	17.68	14.60	14.90	15.63	15.92	17.29
12H	4H	13.99	14.41	15.00	15.42	16.74	13.64	14.06	14.65	15.07	16.38
	6H	14.66	15.00	15.69	16.03	17.35	14.31	14.65	15.34	15.68	17.00
	8H	14.91	15.21	15.94	16.23	17.60	14.55	14.85	15.58	15.87	17.24

END OF REPORT