

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910168

Luminaire Tested: DFN2DIP-TR4F0-080D100US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910168
REPORT IS A COMBINATION OF REPORTS P900486 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-080D100US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15804.4 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 151.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910168
CATALOG NUMBER: DFN2DIP-TR4F0-080D100US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910168

CATALOG NUMBER: DFN2DIP-TR4FO-080D100US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50				44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43				37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37				32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32				28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28				24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25				21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22				19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20				17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18				15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16				14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2653	2653	2653
5°	2657	2610	2627
10°	2631	2559	2542
15°	2594	2475	2409
20°	2547	2358	2247
25°	2498	2227	2090
30°	2432	2093	1892
35°	2367	1949	1717
40°	2301	1800	1517
45°	2225	1635	1336
50°	2146	1468	1159
55°	2064	1289	989
60°	1969	1103	814
65°	1859	913	732
70°	1726	736	663
75°	1559	649	603
80°	1317	544	522
85°	919	363	392

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2490 cd/sqm



TEST NUMBER: P910168

CATALOG NUMBER: DFN2DIP-TR4F0-080D100US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.9	2.0
10°-20°	859.1	5.4
20°-30°	1206.1	7.6
30°-40°	1314.7	8.3
40°-50°	1208.4	7.6
50°-60°	949.0	6.0
60°-70°	617.7	3.9
70°-80°	318.0	2.0
80°-90°	90.2	0.6
90°-100°	197.6	1.3
100°-110°	627.9	4.0
110°-120°	1074.6	6.8
120°-130°	1413.3	8.9
130°-140°	1586.4	10.0
140°-150°	1555.6	9.8
150°-160°	1304.9	8.3
160°-170°	865.4	5.5
170°-180°	302.5	1.9
0°-30°	2378.1	15.0
0°-40°	3692.9	23.4
0°-60°	5850.2	37.0
0°-90°	6876.2	43.5
90°-120°	1900.2	12.0
90°-150°	6455.4	40.8
90°-180°	8928.0	56.5
0°-180°	15804.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3339	3339	3339	3339	3339	
5°	3339	3324	3284	3312	3303	317
15°	3176	3142	3040	2982	2952	895
25°	2883	2786	2587	2463	2417	1326
35°	2484	2330	2064	1874	1807	1555
45°	2031	1828	1511	1296	1224	1568
55°	1544	1308	982	801	744	1380
65°	1043	798	526	423	414	1034
75°	556	344	242	221	218	588
85°	130	66	57	57	57	149
90°	3	35	94	89	92	16
95°	141	168	172	172	168	156
105°	580	587	593	598	598	612
115°	1078	1094	1089	1086	1078	1067
125°	1568	1593	1585	1576	1573	1402
135°	2029	2059	2064	2062	2054	1568
145°	2463	2482	2498	2500	2490	1539
155°	2816	2824	2833	2846	2838	1296
165°	3064	3061	3061	3080	3067	864
175°	3188	3180	3175	3194	3177	303
180°	3194	3194	3194	3194	3194	



TEST NUMBER: P910168

CATALOG NUMBER: DFN2DIP-TR4F0-080D100US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3339.0	3339.0	3339.0	3339.0	3339.0
2.5°	3354.1	3339.0	3305.7	3336.1	3330.0
5°	3339.0	3324.0	3284.5	3311.8	3302.8
7.5°	3311.8	3293.8	3251.5	3263.4	3248.2
10°	3275.5	3254.4	3194.1	3184.8	3166.8
12.5°	3230.4	3203.1	3121.3	3103.3	3070.0
15°	3175.8	3142.5	3039.9	2982.5	2952.3
17.5°	3112.3	3063.9	2937.0	2870.6	2822.2
20°	3039.9	2979.3	2828.3	2753.0	2686.2
22.5°	2961.3	2891.7	2716.4	2613.8	2568.6
25°	2882.8	2786.0	2586.6	2462.9	2417.3
27.5°	2789.1	2686.2	2465.7	2323.7	2254.1
30°	2689.5	2574.3	2332.7	2178.8	2097.0
32.5°	2592.6	2453.6	2206.1	2024.6	1948.9
35°	2484.0	2329.8	2064.0	1873.6	1806.9
37.5°	2378.1	2211.8	1931.0	1722.2	1646.9
40°	2266.3	2085.2	1791.8	1577.3	1498.7
42.5°	2151.5	1958.2	1652.9	1429.3	1353.8
45°	2030.6	1828.1	1511.0	1296.2	1223.8
47.5°	1915.9	1701.4	1375.0	1160.2	1093.9
50°	1788.9	1574.5	1242.0	1033.3	970.1
52.5°	1664.9	1438.1	1115.0	915.6	858.3
55°	1544.0	1308.4	982.0	800.8	743.5
57.5°	1420.3	1178.5	864.3	695.1	646.6
60°	1293.2	1051.6	740.2	586.3	538.0
62.5°	1169.5	927.8	634.5	489.6	465.5
65°	1042.6	797.6	525.7	423.2	413.8
67.5°	921.7	676.8	423.2	371.5	362.6
70°	794.8	559.2	350.4	320.2	308.1
72.5°	673.9	450.1	293.1	269.0	262.9
75°	555.9	344.4	241.8	220.6	217.7
77.5°	438.3	244.6	190.5	178.2	172.2
80°	329.2	175.4	144.9	133.0	133.0
82.5°	229.5	118.0	99.7	93.6	93.6
85°	129.9	66.3	57.4	57.4	57.4
87.5°	48.4	24.0	24.0	21.2	21.2
90°	2.9	34.6	94.3	88.6	91.5
92.5°	59.7	80.9	83.8	86.6	86.6
95°	140.6	167.5	172.4	172.4	167.5
97.5°	234.0	259.0	269.6	269.6	269.6
100°	341.8	364.0	371.6	371.6	368.8
102.5°	455.4	471.8	482.4	485.2	482.4
105°	579.7	587.3	593.1	597.9	597.9
107.5°	702.9	714.5	714.5	716.4	702.9
110°	822.3	837.7	837.7	837.7	830.0



TEST NUMBER: P910168

CATALOG NUMBER: DFN2DIP-TR4F0-080D100US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	951.3	967.7	964.8	957.0	951.3
115°	1078.4	1093.8	1089.0	1086.1	1078.4
117.5°	1204.6	1225.8	1212.2	1204.6	1196.8
120°	1331.6	1352.8	1331.6	1331.6	1323.0
122.5°	1447.1	1474.1	1460.7	1453.0	1447.1
125°	1568.5	1592.6	1584.9	1576.2	1573.4
127.5°	1687.0	1716.8	1706.2	1694.7	1687.0
130°	1797.7	1832.3	1827.6	1821.7	1811.2
132.5°	1921.9	1948.8	1950.8	1937.3	1929.6
135°	2028.7	2058.6	2064.4	2061.5	2053.8
137.5°	2148.2	2172.2	2177.1	2175.1	2163.5
140°	2253.1	2277.1	2290.7	2290.7	2280.1
142.5°	2361.0	2385.0	2392.7	2395.6	2385.0
145°	2463.0	2482.2	2497.7	2500.5	2489.9
147.5°	2554.5	2578.6	2590.1	2595.0	2584.3
150°	2648.9	2665.2	2675.8	2684.4	2675.8
152.5°	2732.6	2749.0	2762.5	2773.1	2762.5
155°	2816.4	2824.1	2832.8	2846.2	2837.5
157.5°	2888.6	2894.4	2899.2	2918.4	2905.0
160°	2953.1	2958.9	2961.7	2978.1	2966.6
162.5°	3012.8	3012.8	3015.7	3033.9	3020.5
165°	3063.8	3060.9	3060.9	3080.2	3066.8
167.5°	3110.1	3101.4	3101.4	3120.7	3107.2
170°	3144.7	3137.0	3134.1	3153.4	3137.0
172.5°	3168.8	3161.1	3158.2	3177.4	3161.1
175°	3188.0	3180.4	3174.6	3193.8	3177.4
177.5°	3198.6	3191.0	3185.1	3201.5	3185.1
180°	3193.8	3193.8	3193.8	3193.8	3193.8



TEST NUMBER: P910168
 CATALOG NUMBER: DFN2DIP-TR4F0-080D100US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.89	10.67	10.91	11.69	13.06	5.87	6.65	6.88	7.67	9.03
	3H	11.56	12.26	12.59	13.29	14.68	7.05	7.75	8.08	8.78	10.16
	4H	12.17	12.83	13.21	13.86	15.26	7.50	8.16	8.54	9.19	10.58
	6H	12.59	13.20	13.64	14.23	15.64	7.82	8.43	8.87	9.46	10.87
	8H	12.71	13.29	13.77	14.35	15.74	7.91	8.49	8.96	9.54	10.94
	12H	12.77	13.32	13.83	14.37	15.79	7.95	8.50	9.01	9.55	10.97
4H	2H	9.90	10.56	10.95	11.60	12.99	6.45	7.11	7.50	8.15	9.54
	3H	11.73	12.28	12.78	13.34	14.74	7.80	8.35	8.85	9.41	10.81
	4H	12.42	12.92	13.48	13.97	15.40	8.35	8.85	9.41	9.90	11.33
	6H	12.93	13.36	14.00	14.44	15.86	8.76	9.20	9.83	10.27	11.69
	8H	13.10	13.51	14.17	14.58	16.01	8.89	9.30	9.96	10.36	11.80
	12H	13.20	13.56	14.28	14.64	16.08	8.96	9.32	10.04	10.40	11.84
8H	4H	12.38	12.78	13.45	13.85	15.29	8.62	9.03	9.69	10.09	11.53
	6H	12.95	13.28	14.04	14.39	15.82	9.14	9.47	10.23	10.58	12.02
	8H	13.16	13.45	14.26	14.55	16.00	9.33	9.62	10.43	10.72	12.17
	12H	13.30	13.56	14.40	14.64	16.14	9.45	9.71	10.55	10.80	12.29
12H	4H	12.33	12.70	13.42	13.78	15.22	8.63	8.99	9.71	10.07	11.51
	6H	12.92	13.21	14.02	14.31	15.76	9.19	9.48	10.29	10.58	12.03
	8H	13.14	13.40	14.24	14.49	15.98	9.40	9.66	10.50	10.74	12.24