

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910187

Luminaire Tested: DFN2DIP-TR4F0-090D060US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910187
REPORT IS A COMBINATION OF REPORTS P901935 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D060US840-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14996.5 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 132.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	110	110	110	110		102	102	102	102		89	89	89		77	77	77		65	65	65
1	100	96	92	88		93	90	86	83		78	75	73		67	66	64		58	56	55
2	91	84	77	72		85	78	73	68		68	64	61		59	56	53		51	49	47
3	83	73	66	60		77	69	62	57		60	55	51		52	48	45		45	42	40
4	76	65	57	51		71	61	54	48		54	48	44		47	42	39		40	37	34
5	70	58	50	44		65	55	47	42		48	42	38		42	37	34		36	33	30
6	64	52	44	38		60	49	42	36		43	37	33		38	33	30		33	29	26
7	60	47	39	33		56	44	37	32		39	33	29		35	30	26		30	26	23
8	55	43	35	30		52	40	33	28		36	30	26		32	27	23		28	24	21
9	52	39	32	26		48	37	30	25		33	27	23		29	24	21		26	22	19
10	48	36	29	24		45	34	27	23		30	25	21		27	22	19		24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2809	2809	2809
5°	2814	2770	2789
10°	2791	2733	2751
15°	2750	2688	2692
20°	2695	2625	2631
25°	2640	2551	2562
30°	2571	2481	2473
35°	2505	2399	2379
40°	2424	2316	2289
45°	2344	2233	2198
50°	2256	2146	2092
55°	2164	2045	1994
60°	2060	1925	1883
65°	1947	1801	1751
70°	1802	1650	1609
75°	1602	1469	1478
80°	1361	1238	1228
85°	985	840	814

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2344 cd/sqm

TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.9	2.2
10°-20°	936.5	6.2
20°-30°	1376.3	9.2
30°-40°	1598.5	10.7
40°-50°	1596.5	10.6
50°-60°	1392.1	9.3
60°-70°	1029.1	6.9
70°-80°	582.2	3.9
80°-90°	157.3	1.0
90°-100°	67.4	0.4
100°-110°	251.4	1.7
110°-120°	666.7	4.4
120°-130°	1105.7	7.4
130°-140°	1174.5	7.8
140°-150°	1091.6	7.3
150°-160°	877.6	5.9
160°-170°	565.5	3.8
170°-180°	194.6	1.3
0°-30°	2645.7	17.6
0°-40°	4244.2	28.3
0°-60°	7232.9	48.2
0°-90°	9001.5	60.0
90°-120°	985.5	6.6
90°-150°	4357.2	29.1
90°-180°	5995.0	40.0
0°-180°	14996.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3536	3536	3536	3536	3536	
5°	3536	3523	3486	3513	3506	336
15°	3367	3346	3302	3316	3299	948
25°	3047	3020	2962	2969	2962	1402
35°	2629	2595	2540	2520	2503	1642
45°	2139	2115	2064	2027	2013	1651
55°	1619	1598	1558	1517	1500	1447
65°	1092	1071	1037	1007	990	1079
75°	571	565	547	527	534	610
85°	139	136	133	122	119	155
90°	1	18	30	37	40	14
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3536.4	3536.4	3536.4	3536.4	3536.4
2.5°	3557.0	3540.1	3502.6	3536.4	3530.0
5°	3536.4	3523.1	3485.7	3512.7	3506.2
7.5°	3512.7	3492.5	3455.0	3482.4	3475.6
10°	3475.6	3451.7	3410.9	3438.0	3427.9
12.5°	3424.3	3404.1	3363.4	3380.2	3373.5
15°	3366.6	3346.4	3302.0	3315.7	3298.7
17.5°	3295.1	3274.9	3230.6	3247.5	3230.6
20°	3216.8	3196.6	3149.0	3159.1	3145.7
22.5°	3138.9	3108.3	3063.8	3063.8	3057.0
25°	3046.9	3019.8	2962.1	2968.6	2962.1
27.5°	2944.8	2920.9	2877.0	2866.9	2849.9
30°	2843.1	2815.6	2764.7	2754.6	2741.0
32.5°	2734.1	2713.9	2659.4	2638.9	2625.1
35°	2628.8	2594.8	2540.3	2519.8	2502.9
37.5°	2509.7	2479.0	2424.5	2400.8	2383.8
40°	2387.3	2360.0	2305.4	2275.1	2261.5
42.5°	2268.3	2240.9	2186.8	2152.5	2132.3
45°	2139.1	2115.4	2064.1	2026.9	2013.3
47.5°	2013.3	1989.4	1934.9	1897.4	1877.2
50°	1880.5	1863.5	1815.8	1768.3	1751.3
52.5°	1751.3	1727.5	1683.4	1646.0	1622.1
55°	1618.9	1598.3	1557.5	1516.8	1499.9
57.5°	1486.1	1469.2	1424.8	1384.0	1370.3
60°	1353.3	1340.0	1292.3	1254.9	1244.8
62.5°	1224.2	1200.3	1166.4	1132.6	1118.8
65°	1091.8	1071.2	1037.2	1006.6	989.7
67.5°	955.7	938.5	908.1	884.3	870.6
70°	829.8	816.1	785.5	761.6	748.3
72.5°	700.6	686.9	669.9	646.2	636.1
75°	571.2	564.6	547.3	527.1	534.0
77.5°	455.7	442.0	435.2	425.1	415.0
80°	340.2	336.6	329.7	319.6	312.9
82.5°	231.3	231.3	228.0	214.3	214.3
85°	139.3	136.0	132.8	122.3	119.1
87.5°	61.3	54.4	47.7	37.6	33.9
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9

TEST NUMBER: P910187

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.73	12.69	12.60	13.58	14.70	11.30	12.26	12.17	13.15	14.27
	3H	13.40	14.26	14.28	15.16	16.30	12.93	13.79	13.81	14.69	15.83
	4H	13.99	14.81	14.89	15.71	16.87	13.52	14.33	14.41	15.24	16.39
	6H	14.40	15.15	15.30	16.06	17.23	13.92	14.67	14.83	15.58	16.75
	8H	14.50	15.22	15.42	16.15	17.31	14.03	14.74	14.94	15.67	16.84
	12H	14.56	15.24	15.48	16.16	17.35	14.08	14.76	14.99	15.68	16.87
4H	2H	12.21	13.02	13.11	13.92	15.08	11.86	12.68	12.76	13.58	14.73
	3H	14.08	14.76	14.99	15.69	16.87	13.69	14.37	14.60	15.30	16.47
	4H	14.80	15.42	15.72	16.35	17.55	14.39	15.01	15.31	15.94	17.14
	6H	15.32	15.85	16.25	16.81	18.01	14.91	15.45	15.85	16.40	17.60
	8H	15.47	15.97	16.41	16.92	18.13	15.06	15.56	16.00	16.51	17.72
	12H	15.55	16.00	16.51	16.97	18.18	15.13	15.58	16.08	16.54	17.76
8H	4H	15.00	15.50	15.94	16.45	17.66	14.64	15.14	15.58	16.09	17.30
	6H	15.64	16.05	16.60	17.04	18.25	15.28	15.69	16.24	16.68	17.89
	8H	15.86	16.23	16.83	17.21	18.43	15.49	15.86	16.46	16.84	18.07
	12H	16.00	16.32	16.97	17.29	18.57	15.61	15.93	16.59	16.91	18.18
12H	4H	14.99	15.44	15.95	16.41	17.63	14.64	15.09	15.60	16.06	17.28
	6H	15.67	16.04	16.64	17.02	18.24	15.32	15.68	16.29	16.66	17.89
	8H	15.92	16.24	16.89	17.21	18.49	15.56	15.88	16.54	16.85	18.13