

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910188

Luminaire Tested: DFN2DIP-TR4F0-090D060US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910188
REPORT IS A COMBINATION OF REPORTS P900416 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D060US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13087.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 132.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		64
1	100	96	92	89	94	90	87	84	78	76	74		68	66	64		58
2	92	85	79	74	86	79	74	70	69	65	62		60	57	55		52
3	84	75	68	62	78	70	64	59	62	57	53		54	50	47		46
4	77	67	59	53	72	63	56	51	55	50	46		48	44	41		42
5	71	60	52	46	66	56	49	44	50	44	40		44	39	36		38
6	66	54	46	40	61	51	44	39	45	39	35		40	35	32		35
7	61	49	41	36	57	46	39	34	41	35	31		36	32	28		32
8	57	45	37	32	53	42	35	30	38	32	28		33	29	25		29
9	53	41	34	29	50	39	32	27	35	29	25		31	26	23		27
10	50	38	31	26	47	36	29	25	32	27	23		29	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2984	2984	2984
5°	2989	2937	2956
10°	2959	2879	2859
15°	2919	2784	2711
20°	2865	2653	2528
25°	2810	2506	2352
30°	2736	2355	2128
35°	2663	2193	1932
40°	2589	2025	1707
45°	2503	1839	1503
50°	2415	1651	1304
55°	2322	1450	1112
60°	2215	1240	915
65°	2091	1027	824
70°	1942	828	745
75°	1754	730	678
80°	1482	612	588
85°	1032	408	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2503 cd/sqm

TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	2.7
10°-20°	966.5	7.4
20°-30°	1356.9	10.4
30°-40°	1479.1	11.3
40°-50°	1359.4	10.4
50°-60°	1067.6	8.2
60°-70°	694.9	5.3
70°-80°	357.7	2.7
80°-90°	96.8	0.7
90°-100°	118.6	0.9
100°-110°	376.8	2.9
110°-120°	644.8	4.9
120°-130°	848.0	6.5
130°-140°	951.8	7.3
140°-150°	933.4	7.1
150°-160°	783.0	6.0
160°-170°	519.2	4.0
170°-180°	181.5	1.4
0°-30°	2675.4	20.4
0°-40°	4154.5	31.7
0°-60°	6581.5	50.3
0°-90°	7730.9	59.1
90°-120°	1140.1	8.7
90°-150°	3873.3	29.6
90°-180°	5357.0	40.9
0°-180°	13087.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	2	21	57	53	55	13
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	

TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0



TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3

TEST NUMBER: P910188

CATALOG NUMBER: DFN2DIP-TR4F0-090D060US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.66	12.63	13.55	14.69	7.72	8.63	8.60	9.53	10.67
	3H	13.43	14.24	14.32	15.15	16.32	8.92	9.73	9.81	10.64	11.80
	4H	14.04	14.81	14.95	15.72	16.90	9.37	10.14	10.28	11.05	12.23
	6H	14.47	15.17	15.39	16.09	17.28	9.70	10.40	10.62	11.32	12.51
	8H	14.60	15.27	15.53	16.21	17.39	9.79	10.46	10.72	11.40	12.58
	12H	14.66	15.30	15.59	16.23	17.44	9.84	10.48	10.77	11.41	12.62
4H	2H	11.77	12.54	12.69	13.46	14.63	8.32	9.09	9.24	10.01	11.18
	3H	13.61	14.25	14.54	15.19	16.38	9.68	10.32	10.61	11.27	12.45
	4H	14.31	14.89	15.24	15.83	17.04	10.24	10.82	11.17	11.76	12.97
	6H	14.83	15.33	15.78	16.29	17.50	10.66	11.16	11.61	12.12	13.34
	8H	15.00	15.47	15.95	16.43	17.65	10.79	11.26	11.74	12.22	13.44
	12H	15.10	15.52	16.07	16.50	17.73	10.86	11.28	11.83	12.26	13.49
8H	4H	14.28	14.75	15.23	15.70	16.93	10.52	10.99	11.47	11.95	13.17
	6H	14.85	15.23	15.83	16.23	17.46	11.04	11.43	12.02	12.43	13.65
	8H	15.07	15.41	16.05	16.39	17.64	11.24	11.58	12.22	12.56	13.81
	12H	15.21	15.51	16.20	16.49	17.78	11.36	11.66	12.35	12.64	13.93
12H	4H	14.24	14.66	15.21	15.63	16.86	10.53	10.95	11.50	11.92	13.16
	6H	14.82	15.17	15.81	16.15	17.40	11.09	11.43	12.08	12.42	13.67
	8H	15.05	15.35	16.04	16.33	17.62	11.31	11.61	12.30	12.59	13.88