

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910200

Luminaire Tested: DFN2DIP-TR4F0-090D090US840-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910200
REPORT IS A COMBINATION OF REPORTS P900470 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D090US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15769.1 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 155.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2984	2984	2984
5°	2989	2937	2956
10°	2959	2879	2859
15°	2919	2784	2711
20°	2865	2653	2528
25°	2810	2506	2352
30°	2736	2355	2128
35°	2663	2193	1932
40°	2589	2025	1707
45°	2503	1839	1503
50°	2415	1651	1304
55°	2322	1450	1112
60°	2215	1240	915
65°	2091	1027	824
70°	1942	828	745
75°	1754	730	678
80°	1482	612	588
85°	1032	408	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2503 cd/sqm

TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	2.2
10°-20°	966.5	6.1
20°-30°	1356.9	8.6
30°-40°	1479.1	9.4
40°-50°	1359.4	8.6
50°-60°	1067.6	6.8
60°-70°	694.9	4.4
70°-80°	357.7	2.3
80°-90°	99.5	0.6
90°-100°	177.9	1.1
100°-110°	565.2	3.6
110°-120°	967.2	6.1
120°-130°	1272.0	8.1
130°-140°	1427.7	9.1
140°-150°	1400.0	8.9
150°-160°	1174.4	7.4
160°-170°	778.9	4.9
170°-180°	272.2	1.7
0°-30°	2675.4	17.0
0°-40°	4154.5	26.3
0°-60°	6581.5	41.7
0°-90°	7733.6	49.0
90°-120°	1710.2	10.8
90°-150°	5809.9	36.8
90°-180°	8035.0	51.0
0°-180°	15769.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	3	31	85	80	82	16
95°	126	151	155	155	151	141
105°	522	529	534	538	538	551
115°	971	984	980	978	971	960
125°	1412	1433	1426	1419	1416	1261
135°	1826	1853	1858	1855	1848	1411
145°	2217	2234	2248	2250	2241	1385
155°	2535	2542	2550	2562	2554	1167
165°	2757	2755	2755	2772	2760	778
175°	2869	2862	2857	2874	2860	273
180°	2874	2874	2874	2874	2874	

TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	2.6	31.2	84.9	79.7	82.3
92.5°	53.7	72.8	75.4	78.0	78.0
95°	126.5	150.8	155.1	155.1	150.8
97.5°	210.6	233.1	242.7	242.7	242.7
100°	307.6	327.6	334.5	334.5	331.9
102.5°	409.9	424.6	434.1	436.8	434.1
105°	521.7	528.6	533.8	538.2	538.2
107.5°	632.6	643.0	643.0	644.7	632.6
110°	740.0	754.0	754.0	754.0	747.0

TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	856.2	870.9	868.3	861.4	856.2
115°	970.6	984.4	980.1	977.5	970.6
117.5°	1084.1	1103.2	1091.1	1084.1	1077.1
120°	1198.5	1217.5	1198.5	1198.5	1190.6
122.5°	1302.4	1326.8	1314.6	1307.7	1302.4
125°	1411.7	1433.3	1426.4	1418.6	1416.0
127.5°	1518.2	1545.1	1535.6	1525.2	1518.2
130°	1617.9	1649.1	1644.8	1639.5	1630.0
132.5°	1729.7	1753.9	1755.7	1743.5	1736.7
135°	1825.8	1852.7	1858.0	1855.3	1848.5
137.5°	1933.3	1955.0	1959.3	1957.6	1947.2
140°	2027.8	2049.4	2061.5	2061.5	2052.0
142.5°	2124.9	2146.5	2153.4	2156.1	2146.5
145°	2216.8	2234.0	2247.9	2250.5	2241.0
147.5°	2299.1	2320.7	2331.1	2335.4	2325.9
150°	2384.0	2398.7	2408.2	2416.0	2408.2
152.5°	2459.3	2474.1	2486.2	2495.8	2486.2
155°	2534.8	2541.6	2549.5	2561.6	2553.8
157.5°	2599.7	2604.9	2609.3	2626.6	2614.4
160°	2657.8	2663.0	2665.6	2680.3	2669.9
162.5°	2711.5	2711.5	2714.1	2730.6	2718.5
165°	2757.4	2754.8	2754.8	2772.2	2760.1
167.5°	2799.0	2791.3	2791.3	2808.5	2796.4
170°	2830.2	2823.3	2820.8	2838.0	2823.3
172.5°	2851.9	2845.0	2842.4	2859.7	2845.0
175°	2869.2	2862.3	2857.1	2874.5	2859.7
177.5°	2878.7	2871.9	2866.6	2881.3	2866.6
180°	2874.5	2874.5	2874.5	2874.5	2874.5

TEST NUMBER: P910200

CATALOG NUMBER: DFN2DIP-TR4F0-090D090US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.85	11.67	11.82	12.65	13.94	6.82	7.64	7.79	8.63	9.91
	3H	12.53	13.26	13.51	14.25	15.56	8.01	8.75	8.99	9.74	11.05
	4H	13.13	13.83	14.13	14.82	16.14	8.46	9.16	9.46	10.15	11.47
	6H	13.55	14.19	14.56	15.19	16.52	8.78	9.42	9.79	10.42	11.75
	8H	13.68	14.29	14.69	15.30	16.63	8.87	9.48	9.89	10.50	11.82
	12H	13.74	14.32	14.76	15.33	16.68	8.92	9.50	9.94	10.51	11.86
4H	2H	10.87	11.56	11.87	12.56	13.87	7.42	8.11	8.42	9.11	10.42
	3H	12.69	13.27	13.71	14.30	15.63	8.77	9.34	9.78	10.37	11.70
	4H	13.39	13.91	14.40	14.93	16.28	9.32	9.84	10.33	10.86	12.21
	6H	13.90	14.35	14.93	15.39	16.75	9.74	10.19	10.76	11.23	12.58
	8H	14.08	14.50	15.11	15.53	16.90	9.86	10.29	10.89	11.32	12.69
	12H	14.17	14.55	15.22	15.60	16.97	9.93	10.31	10.98	11.36	12.73
8H	4H	13.35	13.78	14.38	14.81	16.17	9.59	10.02	10.63	11.05	12.42
	6H	13.92	14.27	14.97	15.34	16.71	10.11	10.46	11.17	11.54	12.90
	8H	14.14	14.44	15.20	15.50	16.88	10.31	10.61	11.37	11.67	13.05
	12H	14.27	14.54	15.34	15.60	17.02	10.42	10.70	11.49	11.75	13.17
12H	4H	13.31	13.69	14.35	14.73	16.11	9.60	9.98	10.65	11.03	12.40
	6H	13.89	14.20	14.96	15.26	16.64	10.16	10.47	11.22	11.53	12.91
	8H	14.11	14.39	15.18	15.44	16.86	10.37	10.64	11.44	11.70	13.12