

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904650

Luminaire Tested: DFN2DIP-TR4F0-070D040US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904650
REPORT IS A COMBINATION OF REPORTS P900375 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D040US830-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9868.4 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 95.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904650
CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P904650
 CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56			
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47			
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40			
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34			
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30			
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26			
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23			
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21			
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19			
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2039	2039	2039
5°	2043	2011	2025
10°	2026	1984	1997
15°	1996	1951	1954
20°	1956	1906	1910
25°	1916	1852	1860
30°	1866	1801	1795
35°	1819	1741	1727
40°	1760	1681	1662
45°	1702	1621	1595
50°	1638	1558	1518
55°	1571	1484	1448
60°	1495	1397	1367
65°	1413	1307	1271
70°	1308	1197	1168
75°	1163	1066	1073
80°	988	899	891
85°	715	610	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1702 cd/sqm



TEST NUMBER: P904650

CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	2.4
10°-20°	679.9	6.9
20°-30°	999.1	10.1
30°-40°	1160.4	11.8
40°-50°	1159.0	11.7
50°-60°	1010.6	10.2
60°-70°	747.1	7.6
70°-80°	422.7	4.3
80°-90°	115.0	1.2
90°-100°	73.8	0.7
100°-110°	234.4	2.4
110°-120°	401.2	4.1
120°-130°	527.6	5.3
130°-140°	592.2	6.0
140°-150°	580.8	5.9
150°-160°	487.2	4.9
160°-170°	323.1	3.3
170°-180°	112.9	1.1
0°-30°	1920.6	19.5
0°-40°	3081.0	31.2
0°-60°	5250.6	53.2
0°-90°	6535.2	66.2
90°-120°	709.4	7.2
90°-150°	2410.0	24.4
90°-180°	3333.0	33.8
0°-180°	9868.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2395	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	793	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	1	13	35	33	34	9
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	



TEST NUMBER: P904650

CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2567.2	2567.2	2567.2	2567.2	2567.2
2.5°	2582.2	2569.8	2542.6	2567.2	2562.5
5°	2567.2	2557.6	2530.3	2550.0	2545.2
7.5°	2550.0	2535.3	2508.0	2528.0	2523.0
10°	2523.0	2505.7	2476.1	2495.8	2488.4
12.5°	2485.8	2471.2	2441.6	2453.8	2448.8
15°	2443.9	2429.2	2397.0	2407.0	2394.6
17.5°	2392.0	2377.4	2345.1	2357.5	2345.1
20°	2335.1	2320.5	2285.9	2293.3	2283.6
22.5°	2278.6	2256.4	2224.1	2224.1	2219.1
25°	2211.9	2192.2	2150.3	2155.0	2150.3
27.5°	2137.7	2120.4	2088.5	2081.1	2068.8
30°	2063.9	2043.9	2007.0	1999.7	1989.7
32.5°	1984.7	1970.1	1930.5	1915.6	1905.6
35°	1908.3	1883.7	1844.1	1829.2	1816.8
37.5°	1821.8	1799.6	1760.0	1742.8	1730.4
40°	1733.1	1713.2	1673.6	1651.6	1641.6
42.5°	1646.6	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.6	1498.4	1471.4	1461.4
47.5°	1461.4	1444.2	1404.6	1377.3	1362.7
50°	1365.1	1352.7	1318.1	1283.6	1271.3
52.5°	1271.3	1254.1	1222.1	1194.9	1177.5
55°	1175.2	1160.3	1130.7	1101.1	1088.7
57.5°	1078.8	1066.5	1034.3	1004.7	994.8
60°	982.4	972.7	938.2	911.0	903.6
62.5°	888.6	871.4	846.8	822.2	812.2
65°	792.6	777.6	753.0	730.8	718.4
67.5°	693.8	681.3	659.2	642.0	632.0
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.4	469.1	461.8
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.1	227.1
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9



TEST NUMBER: P904650

CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3



TEST NUMBER: P904650
 CATALOG NUMBER: DFN2DIP-TR4F0-070D040US830-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.12	12.15	11.92	12.97	13.99	10.69	11.72	11.49	12.54	13.56
	3H	12.79	13.72	13.61	14.55	15.60	12.32	13.24	13.14	14.08	15.13
	4H	13.39	14.26	14.22	15.10	16.16	12.91	13.79	13.75	14.63	15.69
	6H	13.79	14.60	14.64	15.45	16.52	13.32	14.12	14.17	14.98	16.05
	8H	13.90	14.67	14.76	15.54	16.61	13.43	14.20	14.28	15.07	16.14
	12H	13.96	14.69	14.82	15.55	16.65	13.48	14.21	14.34	15.07	16.17
4H	2H	11.60	12.47	12.44	13.32	14.38	11.26	12.13	12.09	12.97	14.03
	3H	13.48	14.21	14.33	15.09	16.16	13.09	13.82	13.94	14.69	15.77
	4H	14.20	14.87	15.07	15.74	16.84	13.80	14.46	14.66	15.34	16.44
	6H	14.73	15.30	15.61	16.20	17.30	14.32	14.89	15.20	15.79	16.89
	8H	14.88	15.42	15.76	16.31	17.43	14.47	15.01	15.35	15.90	17.02
	12H	14.96	15.44	15.86	16.36	17.48	14.54	15.02	15.44	15.94	17.06
8H	4H	14.41	14.95	15.29	15.84	16.96	14.05	14.59	14.93	15.48	16.60
	6H	15.05	15.50	15.96	16.43	17.55	14.69	15.13	15.60	16.07	17.18
	8H	15.27	15.67	16.19	16.59	17.73	14.90	15.30	15.82	16.23	17.36
	12H	15.41	15.76	16.33	16.68	17.87	15.03	15.38	15.95	16.30	17.48
12H	4H	14.41	14.89	15.31	15.80	16.93	14.05	14.54	14.96	15.45	16.57
	6H	15.08	15.48	16.00	16.40	17.54	14.73	15.13	15.65	16.05	17.19
	8H	15.33	15.68	16.25	16.60	17.79	14.98	15.32	15.90	16.24	17.43