

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904681

Luminaire Tested: DFN2DIP-TR4F0-070D110US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904681
REPORT IS A COMBINATION OF REPORTS P902022 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D110US830-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15872.3 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 150.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37
2	87	80	74	69	78	72	67	63	58	55	52	46	44	41	34	33	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27
4	73	62	55	49	65	57	50	45	46	42	38	36	33	31	27	25	24
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	24	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2166	2166	2166
5°	2170	2132	2146
10°	2148	2090	2076
15°	2119	2021	1968
20°	2080	1926	1835
25°	2040	1819	1707
30°	1986	1710	1545
35°	1933	1592	1402
40°	1880	1470	1239
45°	1817	1335	1091
50°	1753	1199	946
55°	1686	1053	807
60°	1608	900	664
65°	1518	746	598
70°	1410	601	541
75°	1273	530	492
80°	1076	445	427
85°	750	296	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1856 cd/sqm

TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	1.6
10°-20°	701.6	4.4
20°-30°	985.0	6.2
30°-40°	1073.7	6.8
40°-50°	986.9	6.2
50°-60°	775.0	4.9
60°-70°	504.5	3.2
70°-80°	259.7	1.6
80°-90°	72.4	0.5
90°-100°	115.4	0.7
100°-110°	430.1	2.7
110°-120°	1140.7	7.2
120°-130°	1892.0	11.9
130°-140°	2009.7	12.7
140°-150°	1867.8	11.8
150°-160°	1501.7	9.5
160°-170°	967.6	6.1
170°-180°	333.0	2.1
0°-30°	1942.1	12.2
0°-40°	3015.8	19.0
0°-60°	4777.7	30.1
0°-90°	5614.2	35.4
90°-120°	1686.2	10.6
90°-150°	7455.8	47.0
90°-180°	10258.0	64.6
0°-180°	15872.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2705	2697	259
15°	2594	2566	2483	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1903	1686	1530	1476	1270
45°	1658	1493	1234	1059	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	2	30	50	63	68	15
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2140	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3254	3231	3261	3276	3256	1499
165°	3428	3413	3421	3438	3421	969
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.9	2726.9	2726.9	2726.9	2726.9
2.5°	2739.1	2726.9	2699.6	2724.5	2719.5
5°	2726.9	2714.5	2682.4	2704.6	2697.3
7.5°	2704.6	2689.9	2655.4	2665.0	2652.8
10°	2675.0	2657.8	2608.5	2600.9	2586.2
12.5°	2638.1	2615.8	2549.1	2534.4	2507.2
15°	2593.6	2566.4	2482.6	2435.7	2411.1
17.5°	2541.8	2502.3	2398.6	2344.3	2304.8
20°	2482.6	2433.1	2309.8	2248.2	2193.8
22.5°	2418.5	2361.6	2218.4	2134.6	2097.7
25°	2354.3	2275.2	2112.3	2011.3	1974.2
27.5°	2277.8	2193.8	2013.6	1897.7	1840.9
30°	2196.4	2102.4	1905.0	1779.3	1712.6
32.5°	2117.3	2003.8	1801.6	1653.4	1591.6
35°	2028.5	1902.6	1685.6	1530.1	1475.6
37.5°	1942.2	1806.3	1577.0	1406.5	1345.0
40°	1850.8	1702.9	1463.3	1288.2	1224.0
42.5°	1757.1	1599.2	1349.9	1167.2	1105.7
45°	1658.4	1492.9	1234.0	1058.6	999.4
47.5°	1564.6	1389.5	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.3	843.9	792.3
52.5°	1359.6	1174.5	910.6	747.7	700.9
55°	1260.9	1068.5	801.9	654.0	607.2
57.5°	1159.9	962.4	705.9	567.6	528.1
60°	1056.2	858.8	604.5	478.9	439.3
62.5°	955.1	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.6	286.2	261.6	251.6
72.5°	550.4	367.6	239.3	219.7	214.7
75°	454.0	281.2	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.7	845.7	154.6	182.2	192.5
107.5°	949.5	1012.6	159.7	187.3	197.6
110°	1121.7	1174.7	443.2	190.0	199.9

TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.2	1286.2	194.8	202.6
115°	1455.8	1498.7	1562.3	389.9	207.7
117.5°	1605.2	1655.8	1699.0	1336.7	673.4
120°	1772.4	1810.2	1856.0	1886.3	1544.4
122.5°	1914.0	1954.5	2005.4	2020.4	2023.2
125°	2058.3	2091.4	2139.5	2157.2	2164.7
127.5°	2190.0	2225.4	2263.6	2288.9	2291.3
130°	2314.1	2354.8	2382.4	2410.4	2408.0
132.5°	2440.7	2473.8	2501.5	2524.3	2522.0
135°	2547.2	2587.7	2610.3	2635.9	2630.7
137.5°	2658.4	2688.8	2714.3	2739.6	2732.1
140°	2767.3	2787.7	2815.4	2838.2	2825.6
142.5°	2858.6	2876.4	2909.2	2929.3	2916.7
145°	2954.9	2952.1	2995.1	3012.9	3000.3
147.5°	3038.2	3030.7	3073.6	3086.3	3076.4
150°	3119.3	3101.6	3142.2	3157.2	3144.6
152.5°	3187.6	3167.4	3205.3	3220.7	3202.9
155°	3253.5	3230.8	3261.2	3276.3	3256.1
157.5°	3306.6	3286.5	3309.4	3327.1	3306.6
160°	3352.3	3337.0	3352.3	3367.3	3349.6
162.5°	3392.6	3377.6	3390.2	3408.0	3385.1
165°	3428.1	3413.0	3420.6	3438.3	3420.6
167.5°	3456.0	3440.8	3448.6	3466.3	3443.5
170°	3478.9	3463.6	3468.6	3486.5	3463.6
172.5°	3493.9	3478.9	3484.0	3501.7	3478.9
175°	3506.5	3488.8	3493.9	3511.7	3486.5
177.5°	3511.7	3493.9	3496.6	3514.4	3491.6
180°	3499.1	3499.1	3499.1	3499.1	3499.1

TEST NUMBER: P904681

CATALOG NUMBER: DFN2DIP-TR4F0-070D110US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.29	9.01	9.36	10.08	11.55	4.26	4.98	5.34	6.06	7.53
	3H	9.95	10.60	11.04	11.69	13.17	5.44	6.09	6.53	7.17	8.66
	4H	10.56	11.17	11.66	12.26	13.75	5.89	6.50	6.98	7.58	9.08
	6H	10.97	11.54	12.08	12.63	14.13	6.20	6.77	7.31	7.86	9.36
	8H	11.10	11.63	12.21	12.74	14.23	6.29	6.83	7.40	7.93	9.43
	12H	11.16	11.66	12.27	12.76	14.28	6.33	6.84	7.45	7.94	9.46
4H	2H	8.29	8.90	9.40	9.99	11.48	4.84	5.45	5.95	6.54	8.03
	3H	10.11	10.62	11.22	11.73	13.24	6.18	6.69	7.29	7.80	9.31
	4H	10.80	11.27	11.91	12.37	13.89	6.73	7.19	7.84	8.30	9.82
	6H	11.31	11.71	12.43	12.83	14.35	7.14	7.54	8.26	8.67	10.19
	8H	11.48	11.85	12.60	12.97	14.50	7.27	7.64	8.39	8.76	10.29
	12H	11.57	11.91	12.71	13.04	14.58	7.33	7.67	8.47	8.80	10.34
8H	4H	10.76	11.13	11.88	12.25	13.78	7.00	7.37	8.12	8.49	10.02
	6H	11.32	11.63	12.46	12.79	14.32	7.51	7.82	8.66	8.98	10.51
	8H	11.54	11.81	12.69	12.94	14.50	7.71	7.98	8.86	9.11	10.67
	12H	11.67	11.91	12.82	13.04	14.63	7.82	8.06	8.97	9.19	10.78
12H	4H	10.70	11.04	11.84	12.17	13.71	7.00	7.34	8.14	8.47	10.01
	6H	11.29	11.56	12.44	12.70	14.25	7.56	7.83	8.71	8.97	10.52
	8H	11.51	11.75	12.66	12.88	14.47	7.77	8.01	8.92	9.14	10.73

END OF REPORT