

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904687

Luminaire Tested: DFN2DIP-TR4F0-080D040US830-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P904687  
REPORT IS A COMBINATION OF REPORTS P901897 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-080D040US830-FLLONL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11197.4 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 105.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P904687  
CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P904687

CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67				67
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56				56
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47				47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40				40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34				34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30				30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23				23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21				21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2331	2331	2331
5°	2335	2298	2314
10°	2316	2267	2282
15°	2282	2230	2233
20°	2236	2178	2183
25°	2190	2116	2125
30°	2133	2058	2051
35°	2078	1990	1973
40°	2011	1921	1899
45°	1945	1853	1823
50°	1872	1780	1735
55°	1795	1696	1654
60°	1709	1597	1562
65°	1615	1494	1452
70°	1495	1369	1335
75°	1329	1219	1226
80°	1130	1027	1019
85°	817	697	675

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1945 cd/sqm



TEST NUMBER: P904687

CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.1	2.5
10°-20°	777.0	6.9
20°-30°	1141.8	10.2
30°-40°	1326.2	11.8
40°-50°	1324.5	11.8
50°-60°	1155.0	10.3
60°-70°	853.8	7.6
70°-80°	483.0	4.3
80°-90°	129.7	1.2
90°-100°	41.9	0.4
100°-110°	156.4	1.4
110°-120°	414.8	3.7
120°-130°	688.0	6.1
130°-140°	730.8	6.5
140°-150°	679.2	6.1
150°-160°	546.1	4.9
160°-170°	351.9	3.1
170°-180°	121.1	1.1
0°-30°	2195.0	19.6
0°-40°	3521.1	31.4
0°-60°	6000.6	53.6
0°-90°	7467.2	66.7
90°-120°	613.2	5.5
90°-150°	2711.2	24.2
90°-180°	3730.0	33.3
0°-180°	11197.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	1	11	18	23	25	10
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	



TEST NUMBER: P904687

CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7



TEST NUMBER: P904687

CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4



TEST NUMBER: P904687  
 CATALOG NUMBER: DFN2DIP-TR4F0-080D040US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.62	12.65	12.42	13.48	14.49	11.19	12.22	11.99	13.04	14.06
	3H	13.29	14.22	14.10	15.05	16.09	12.82	13.75	13.63	14.58	15.62
	4H	13.89	14.77	14.72	15.60	16.66	13.41	14.29	14.24	15.13	16.18
	6H	14.30	15.11	15.14	15.95	17.02	13.82	14.63	14.66	15.48	16.54
	8H	14.41	15.18	15.26	16.04	17.11	13.93	14.70	14.78	15.57	16.63
	12H	14.46	15.20	15.32	16.05	17.15	13.98	14.71	14.84	15.57	16.67
4H	2H	12.10	12.98	12.94	13.82	14.87	11.76	12.63	12.59	13.47	14.52
	3H	13.98	14.72	14.83	15.59	16.66	13.59	14.32	14.44	15.20	16.26
	4H	14.70	15.37	15.56	16.24	17.34	14.30	14.97	15.16	15.84	16.93
	6H	15.23	15.81	16.10	16.70	17.80	14.82	15.40	15.69	16.29	17.39
	8H	15.38	15.92	16.26	16.81	17.92	14.97	15.51	15.85	16.40	17.51
	12H	15.46	15.95	16.36	16.86	17.97	15.04	15.53	15.94	16.44	17.55
8H	4H	14.92	15.45	15.79	16.34	17.45	14.56	15.09	15.43	15.98	17.09
	6H	15.55	16.00	16.46	16.93	18.04	15.19	15.64	16.10	16.57	17.68
	8H	15.78	16.17	16.69	17.10	18.22	15.41	15.80	16.32	16.73	17.85
	12H	15.92	16.26	16.83	17.18	18.36	15.53	15.88	16.45	16.80	17.98
12H	4H	14.91	15.40	15.81	16.30	17.42	14.56	15.04	15.45	15.95	17.07
	6H	15.58	15.98	16.50	16.91	18.03	15.23	15.63	16.15	16.55	17.68
	8H	15.84	16.18	16.75	17.10	18.28	15.48	15.83	16.40	16.74	17.92