

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912908

Luminaire Tested: DFN2DIP-TR4F0-090D040US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912908
REPORT IS A COMBINATION OF REPORTS P900380 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D040US850-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12409.7 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 117.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	103	98	95	91	97	93	90	87	83	81	78	74	72	70	66	64	63
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54
3	86	77	70	64	81	73	67	61	66	61	56	59	55	51	52	49	47
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41
5	73	62	53	48	69	59	51	46	53	47	43	48	43	39	43	39	36
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32
7	63	51	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24
10	51	39	32	27	48	37	31	26	34	29	25	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3277	3277	3277
5°	3282	3225	3246
10°	3250	3162	3140
15°	3205	3057	2977
20°	3146	2913	2776
25°	3086	2752	2583
30°	3004	2586	2337
35°	2924	2408	2122
40°	2843	2224	1874
45°	2749	2019	1650
50°	2652	1813	1431
55°	2550	1593	1221
60°	2432	1362	1005
65°	2297	1128	905
70°	2133	910	818
75°	1926	802	744
80°	1628	672	645
85°	1134	449	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2749 cd/sqm

TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.6	3.1
10°-20°	1061.3	8.6
20°-30°	1490.1	12.0
30°-40°	1624.3	13.1
40°-50°	1492.9	12.0
50°-60°	1172.4	9.4
60°-70°	763.1	6.1
70°-80°	392.8	3.2
80°-90°	104.3	0.8
90°-100°	86.8	0.7
100°-110°	275.8	2.2
110°-120°	472.0	3.8
120°-130°	620.8	5.0
130°-140°	696.8	5.6
140°-150°	683.3	5.5
150°-160°	573.2	4.6
160°-170°	380.1	3.1
170°-180°	132.9	1.1
0°-30°	2938.0	23.7
0°-40°	4562.3	36.8
0°-60°	7227.6	58.2
0°-90°	8487.9	68.4
90°-120°	834.7	6.7
90°-150°	2835.6	22.8
90°-180°	3922.0	31.6
0°-180°	12409.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4125	4125	4125	4125	4125	
5°	4125	4106	4058	4091	4080	391
15°	3924	3882	3756	3685	3648	1106
25°	3562	3442	3196	3043	2986	1638
35°	3069	2878	2550	2315	2232	1921
45°	2509	2258	1867	1601	1512	1937
55°	1908	1616	1213	989	918	1705
65°	1288	986	650	523	511	1277
75°	687	425	299	272	269	726
85°	160	82	71	71	71	184
90°	1	15	42	39	40	12
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4125.1	4125.1	4125.1	4125.1	4125.1
2.5°	4143.8	4125.1	4083.9	4121.6	4114.1
5°	4125.1	4106.5	4057.8	4091.4	4080.3
7.5°	4091.4	4069.3	4017.0	4031.7	4013.0
10°	4046.7	4020.6	3946.2	3934.6	3912.4
12.5°	3990.8	3957.2	3856.2	3834.0	3792.8
15°	3923.5	3882.4	3755.6	3684.7	3647.5
17.5°	3845.1	3785.3	3628.4	3546.5	3486.7
20°	3755.6	3680.8	3494.1	3401.1	3318.7
22.5°	3658.6	3572.6	3355.9	3229.2	3173.4
25°	3561.6	3441.9	3195.6	3042.7	2986.4
27.5°	3445.9	3318.7	3046.2	2870.8	2784.8
30°	3322.7	3180.5	2881.8	2691.8	2590.7
32.5°	3203.0	3031.1	2725.4	2501.2	2407.7
35°	3068.8	2878.3	2549.9	2314.7	2232.3
37.5°	2938.1	2732.6	2385.6	2127.7	2034.7
40°	2799.9	2576.1	2213.7	1948.7	1851.7
42.5°	2658.1	2419.3	2042.1	1765.7	1672.6
45°	2508.8	2258.5	1866.7	1601.3	1511.8
47.5°	2366.9	2102.0	1698.8	1433.4	1351.4
50°	2210.1	1945.1	1534.4	1276.6	1198.5
52.5°	2056.9	1776.8	1377.6	1131.2	1060.3
55°	1907.5	1616.4	1213.1	989.4	918.5
57.5°	1754.7	1456.0	1067.9	858.7	798.9
60°	1597.7	1299.1	914.6	724.4	664.6
62.5°	1444.9	1146.3	783.8	604.8	575.1
65°	1288.0	985.5	649.5	522.8	511.4
67.5°	1138.7	836.1	522.8	459.0	447.9
70°	981.9	690.8	433.0	395.7	380.6
72.5°	832.5	556.1	362.0	332.3	324.8
75°	686.8	425.4	298.7	272.5	268.9
77.5°	541.4	302.2	235.2	220.2	212.7
80°	406.8	216.7	179.0	164.4	164.4
82.5°	283.6	145.7	123.2	115.7	115.7
85°	160.4	82.0	70.9	70.9	70.9
87.5°	59.8	29.7	29.7	26.2	26.2
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P912908

CATALOG NUMBER: DFN2DIP-TR4F0-090D040US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.83	13.84	13.62	14.65	15.63	8.81	9.81	9.59	10.62	11.60
	3H	14.52	15.42	15.33	16.24	17.25	10.01	10.91	10.81	11.73	12.74
	4H	15.14	15.99	15.96	16.81	17.84	10.47	11.32	11.29	12.14	13.17
	6H	15.57	16.35	16.40	17.18	18.22	10.80	11.58	11.63	12.41	13.45
	8H	15.70	16.45	16.54	17.30	18.33	10.89	11.64	11.74	12.49	13.53
	12H	15.77	16.48	16.61	17.32	18.39	10.94	11.65	11.79	12.50	13.56
4H	2H	12.87	13.72	13.70	14.54	15.57	9.42	10.27	10.25	11.10	12.12
	3H	14.72	15.42	15.55	16.28	17.32	10.79	11.49	11.62	12.35	13.39
	4H	15.42	16.06	16.26	16.91	17.98	11.35	11.99	12.19	12.84	13.91
	6H	15.94	16.49	16.80	17.37	18.45	11.77	12.33	12.64	13.21	14.28
	8H	16.12	16.64	16.99	17.51	18.59	11.91	12.42	12.78	13.30	14.38
	12H	16.22	16.69	17.11	17.58	18.67	11.98	12.45	12.87	13.34	14.43
8H	4H	15.40	15.91	16.26	16.79	17.87	11.64	12.15	12.51	13.03	14.11
	6H	15.97	16.40	16.86	17.31	18.40	12.16	12.59	13.06	13.51	14.59
	8H	16.19	16.56	17.09	17.47	18.58	12.36	12.73	13.26	13.65	14.75
	12H	16.33	16.67	17.24	17.57	18.72	12.48	12.82	13.39	13.72	14.87
12H	4H	15.36	15.82	16.24	16.72	17.81	11.65	12.11	12.54	13.01	14.10
	6H	15.95	16.32	16.85	17.23	18.34	12.21	12.59	13.12	13.50	14.61
	8H	16.17	16.51	17.08	17.41	18.56	12.43	12.77	13.34	13.67	14.82