

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907297

Luminaire Tested: DFN2DIP-TR4F0-040D100US835-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907297  
REPORT IS A COMBINATION OF REPORTS P901998 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-040D100US835-RLLONL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13300.0 lumens  
Efficiency: N/A  
Efficacy: 122.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 108.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907297  
CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P907297

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				26
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22				22
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21	16				16
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14				14
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12				12
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11				11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				10
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12	9				9
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1313	1313	1313
5°	1315	1292	1301
10°	1302	1267	1258
15°	1285	1225	1193
20°	1261	1167	1113
25°	1237	1103	1035
30°	1204	1036	937
35°	1172	965	850
40°	1140	891	751
45°	1102	809	661
50°	1063	727	574
55°	1022	638	489
60°	975	546	403
65°	920	452	362
70°	855	364	328
75°	772	321	298
80°	652	269	259
85°	455	180	194

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1791 cd/sqm



TEST NUMBER: P907297

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.9	1.2
10°-20°	425.3	3.2
20°-30°	597.2	4.5
30°-40°	650.9	4.9
40°-50°	598.3	4.5
50°-60°	469.9	3.5
60°-70°	305.8	2.3
70°-80°	157.4	1.2
80°-90°	46.1	0.3
90°-100°	111.3	0.8
100°-110°	414.9	3.1
110°-120°	1100.3	8.3
120°-130°	1824.9	13.7
130°-140°	1938.4	14.6
140°-150°	1801.5	13.5
150°-160°	1448.4	10.9
160°-170°	933.3	7.0
170°-180°	321.2	2.4
0°-30°	1177.4	8.9
0°-40°	1828.4	13.7
0°-60°	2896.5	21.8
0°-90°	3405.9	25.6
90°-120°	1626.4	12.2
90°-150°	7191.2	54.1
90°-180°	9894.0	74.4
0°-180°	13300.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	2	29	49	61	66	12
95°	159	78	95	108	105	188
105°	742	816	149	176	186	793
115°	1404	1446	1507	376	200	1382
125°	1985	2017	2064	2081	2088	1771
135°	2457	2496	2518	2542	2537	1898
145°	2850	2847	2889	2906	2894	1782
155°	3138	3116	3146	3160	3141	1446
165°	3306	3292	3299	3316	3299	934
175°	3382	3365	3370	3387	3363	322
180°	3375	3375	3375	3375	3375	



TEST NUMBER: P907297

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	2.3	29.3	48.7	61.2	65.8
92.5°	61.2	51.3	58.6	63.5	65.8
95°	158.6	78.0	95.1	107.6	105.0
97.5°	285.6	85.5	124.4	131.9	134.3
100°	432.4	97.7	139.2	158.6	163.6
102.5°	593.3	588.7	144.1	170.8	178.3
105°	742.4	815.7	149.1	175.7	185.6
107.5°	915.8	976.7	154.0	180.7	190.5
110°	1081.9	1133.0	427.4	183.3	192.8



TEST NUMBER: P907297

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1238.2	1282.0	1240.6	187.9	195.5
115°	1404.1	1445.6	1506.8	376.1	200.4
117.5°	1548.2	1597.0	1638.7	1289.3	649.6
120°	1709.5	1746.0	1790.1	1819.4	1489.7
122.5°	1846.1	1885.2	1934.2	1948.7	1951.3
125°	1985.3	2017.2	2063.6	2080.7	2087.9
127.5°	2112.3	2146.5	2183.3	2207.7	2210.0
130°	2232.0	2271.2	2297.9	2324.8	2322.5
132.5°	2354.1	2386.0	2412.7	2434.7	2432.4
135°	2456.8	2495.9	2517.7	2542.3	2537.4
137.5°	2564.1	2593.4	2618.0	2642.4	2635.1
140°	2669.0	2688.8	2715.4	2737.5	2725.3
142.5°	2757.2	2774.3	2805.9	2825.3	2813.2
145°	2850.0	2847.4	2888.9	2906.0	2893.8
147.5°	2930.3	2923.1	2964.5	2976.7	2967.2
150°	3008.6	2991.5	3030.7	3045.2	3033.0
152.5°	3074.4	3055.0	3091.6	3106.3	3089.2
155°	3138.0	3116.2	3145.5	3160.0	3140.6
157.5°	3189.3	3169.9	3191.9	3209.0	3189.3
160°	3233.4	3218.6	3233.4	3247.9	3230.8
162.5°	3272.2	3257.7	3269.9	3287.0	3265.0
165°	3306.4	3291.9	3299.2	3316.3	3299.2
167.5°	3333.4	3318.6	3326.2	3343.3	3321.2
170°	3355.4	3340.7	3345.6	3362.7	3340.7
172.5°	3369.9	3355.4	3360.4	3377.5	3355.4
175°	3382.1	3365.0	3369.9	3387.1	3362.7
177.5°	3387.1	3369.9	3372.6	3389.7	3367.6
180°	3374.9	3374.9	3374.9	3374.9	3374.9



TEST NUMBER: P907297  
 CATALOG NUMBER: DFN2DIP-TR4F0-040D100US835-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.21	5.88	6.36	7.01	8.59	1.19	1.85	2.33	2.98	4.57
	3H	6.88	7.47	8.03	8.61	10.21	2.36	2.96	3.52	4.10	5.70
	4H	7.48	8.04	8.64	9.18	10.79	2.81	3.37	3.97	4.51	6.12
	6H	7.89	8.41	9.06	9.55	11.17	3.12	3.64	4.29	4.78	6.40
	8H	8.01	8.51	9.19	9.66	11.27	3.21	3.70	4.38	4.86	6.46
	12H	8.07	8.54	9.25	9.69	11.32	3.25	3.71	4.42	4.86	6.49
4H	2H	5.21	5.78	6.38	6.92	8.52	1.76	2.33	2.93	3.47	5.07
	3H	7.03	7.49	8.20	8.66	10.28	3.10	3.57	4.27	4.73	6.35
	4H	7.71	8.14	8.89	9.30	10.93	3.64	4.07	4.82	5.23	6.86
	6H	8.22	8.59	9.40	9.76	11.39	4.05	4.42	5.23	5.60	7.22
	8H	8.39	8.73	9.57	9.90	11.54	4.18	4.52	5.36	5.69	7.33
	12H	8.48	8.79	9.67	9.97	11.61	4.23	4.55	5.43	5.73	7.37
8H	4H	7.67	8.01	8.85	9.18	10.82	3.91	4.25	5.09	5.42	7.06
	6H	8.23	8.51	9.43	9.72	11.36	4.42	4.71	5.62	5.92	7.55
	8H	8.44	8.69	9.65	9.88	11.54	4.61	4.86	5.82	6.05	7.71
	12H	8.57	8.79	9.78	9.98	11.67	4.72	4.94	5.93	6.13	7.82
12H	4H	7.61	7.92	8.81	9.10	10.75	3.90	4.22	5.10	5.40	7.04
	6H	8.20	8.45	9.41	9.64	11.29	4.47	4.72	5.67	5.91	7.56
	8H	8.41	8.63	9.62	9.82	11.51	4.67	4.89	5.88	6.08	7.77