

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913007

Luminaire Tested: DFN2DIP-TR4F0-110D110US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913007
REPORT IS A COMBINATION OF REPORTS P902029 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D110US850-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24154.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 197.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3771	3771	3771
5°	3777	3718	3743
10°	3746	3668	3692
15°	3691	3608	3613
20°	3617	3524	3532
25°	3543	3424	3438
30°	3450	3330	3319
35°	3362	3220	3193
40°	3254	3109	3073
45°	3146	2997	2950
50°	3028	2880	2807
55°	2905	2745	2677
60°	2765	2584	2527
65°	2613	2417	2350
70°	2419	2214	2160
75°	2150	1971	1984
80°	1827	1662	1648
85°	1322	1128	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3146 cd/sqm

TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	1.8
10°-20°	1257.0	5.2
20°-30°	1847.3	7.6
30°-40°	2145.5	8.9
40°-50°	2142.9	8.9
50°-60°	1868.5	7.7
60°-70°	1381.3	5.7
70°-80°	781.5	3.2
80°-90°	213.5	0.9
90°-100°	135.7	0.6
100°-110°	506.1	2.1
110°-120°	1342.2	5.6
120°-130°	2226.1	9.2
130°-140°	2364.7	9.8
140°-150°	2197.7	9.1
150°-160°	1766.9	7.3
160°-170°	1138.5	4.7
170°-180°	391.9	1.6
0°-30°	3551.1	14.7
0°-40°	5696.6	23.6
0°-60°	9708.0	40.2
0°-90°	12084.2	50.0
90°-120°	1984.0	8.2
90°-150°	8772.5	36.3
90°-180°	12070.0	50.0
0°-180°	24154.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	3	36	59	75	80	22
95°	194	95	116	131	128	229
105°	906	995	182	214	226	968
115°	1713	1763	1838	459	244	1686
125°	2422	2461	2517	2538	2547	2160
135°	2997	3045	3071	3101	3095	2315
145°	3477	3474	3524	3545	3530	2174
155°	3828	3801	3837	3855	3831	1764
165°	4034	4016	4025	4046	4025	1140
175°	4126	4105	4111	4132	4102	393
180°	4117	4117	4117	4117	4117	

TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	2.9	35.7	59.4	74.6	80.3
92.5°	74.6	62.7	71.4	77.5	80.3
95°	193.5	95.2	116.0	131.2	128.1
97.5°	348.4	104.4	151.7	160.9	163.8
100°	527.4	119.2	169.8	193.5	199.5
102.5°	723.7	718.1	175.8	208.4	217.6
105°	905.6	995.1	181.9	214.4	226.5
107.5°	1117.2	1191.4	187.9	220.4	232.4
110°	1319.8	1382.1	521.5	223.6	235.2

TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1510.6	1563.9	1513.3	229.2	238.4
115°	1712.9	1763.4	1838.2	458.8	244.4
117.5°	1888.7	1948.2	1999.1	1572.8	792.4
120°	2085.4	2129.9	2183.7	2219.4	1817.2
122.5°	2252.0	2299.7	2359.5	2377.3	2380.5
125°	2421.8	2460.8	2517.3	2538.2	2547.0
127.5°	2576.8	2618.5	2663.4	2693.1	2696.0
130°	2722.8	2770.6	2803.1	2836.0	2833.3
132.5°	2871.8	2910.7	2943.3	2970.1	2967.4
135°	2997.1	3044.8	3071.3	3101.4	3095.3
137.5°	3127.9	3163.6	3193.7	3223.4	3214.5
140°	3256.0	3280.0	3312.6	3339.4	3324.6
142.5°	3363.5	3384.3	3422.9	3446.7	3431.8
145°	3476.7	3473.5	3524.1	3545.0	3530.2
147.5°	3574.8	3565.9	3616.4	3631.3	3619.7
150°	3670.2	3649.4	3697.1	3714.8	3700.0
152.5°	3750.5	3726.8	3771.4	3789.5	3768.6
155°	3828.0	3801.4	3837.1	3854.9	3831.2
157.5°	3890.6	3866.9	3893.8	3914.7	3890.6
160°	3944.4	3926.3	3944.4	3962.0	3941.2
162.5°	3991.7	3974.1	3989.0	4009.8	3983.0
165°	4033.5	4015.8	4024.7	4045.5	4024.7
167.5°	4066.4	4048.4	4057.6	4078.5	4051.6
170°	4093.3	4075.2	4081.2	4102.2	4075.2
172.5°	4111.0	4093.3	4099.3	4120.2	4093.3
175°	4125.8	4105.0	4111.0	4131.9	4102.2
177.5°	4131.9	4111.0	4114.2	4135.0	4108.2
180°	4117.1	4117.1	4117.1	4117.1	4117.1

TEST NUMBER: P913007

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.88	12.74	12.84	13.72	14.99	11.45	12.31	12.41	13.28	14.55
	3H	13.54	14.31	14.51	15.30	16.59	13.07	13.84	14.04	14.82	16.12
	4H	14.13	14.86	15.11	15.85	17.15	13.66	14.39	14.64	15.37	16.67
	6H	14.53	15.20	15.52	16.19	17.51	14.05	14.73	15.05	15.72	17.03
	8H	14.63	15.27	15.63	16.28	17.59	14.16	14.80	15.16	15.81	17.12
	12H	14.68	15.29	15.69	16.29	17.63	14.20	14.81	15.21	15.81	17.15
4H	2H	12.34	13.07	13.33	14.06	15.36	12.00	12.73	12.99	13.72	15.02
	3H	14.21	14.82	15.21	15.83	17.15	13.82	14.43	14.81	15.44	16.76
	4H	14.92	15.48	15.93	16.49	17.83	14.52	15.08	15.52	16.08	17.42
	6H	15.44	15.92	16.45	16.95	18.29	15.03	15.51	16.05	16.54	17.88
	8H	15.59	16.04	16.61	17.06	18.41	15.18	15.63	16.19	16.65	18.00
	12H	15.66	16.07	16.70	17.11	18.46	15.24	15.65	16.28	16.68	18.04
8H	4H	15.12	15.57	16.14	16.59	17.94	14.76	15.21	15.78	16.23	17.58
	6H	15.75	16.12	16.79	17.19	18.54	15.39	15.76	16.43	16.83	18.17
	8H	15.97	16.30	17.02	17.35	18.72	15.60	15.93	16.65	16.98	18.35
	12H	16.10	16.39	17.16	17.44	18.85	15.72	16.01	16.77	17.05	18.46
12H	4H	15.11	15.51	16.14	16.55	17.91	14.75	15.16	15.79	16.20	17.55
	6H	15.78	16.11	16.83	17.16	18.53	15.43	15.76	16.48	16.81	18.18
	8H	16.02	16.31	17.08	17.36	18.77	15.67	15.95	16.72	17.00	18.41

END OF REPORT