

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907491

Luminaire Tested: DFN2DIP-TR4F0-100D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907491
REPORT IS A COMBINATION OF REPORTS P901919 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D050US835-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14850.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 138.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3091	3091	3091
5°	3096	3048	3069
10°	3071	3007	3027
15°	3026	2957	2962
20°	2965	2889	2895
25°	2904	2806	2818
30°	2828	2730	2721
35°	2756	2639	2617
40°	2667	2548	2519
45°	2579	2457	2418
50°	2482	2361	2301
55°	2381	2250	2194
60°	2267	2118	2071
65°	2142	1982	1926
70°	1983	1815	1770
75°	1763	1616	1626
80°	1498	1362	1351
85°	1083	925	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2579 cd/sqm

TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	2.5
10°-20°	1030.4	6.9
20°-30°	1514.3	10.2
30°-40°	1758.8	11.8
40°-50°	1756.6	11.8
50°-60°	1531.7	10.3
60°-70°	1132.3	7.6
70°-80°	640.6	4.3
80°-90°	172.1	1.2
90°-100°	55.7	0.4
100°-110°	207.4	1.4
110°-120°	550.1	3.7
120°-130°	912.4	6.1
130°-140°	969.2	6.5
140°-150°	900.8	6.1
150°-160°	724.2	4.9
160°-170°	466.6	3.1
170°-180°	160.6	1.1
0°-30°	2911.0	19.6
0°-40°	4669.7	31.4
0°-60°	7958.0	53.6
0°-90°	9903.0	66.7
90°-120°	813.2	5.5
90°-150°	3595.6	24.2
90°-180°	4947.0	33.3
0°-180°	14850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	1	15	24	31	33	14
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P907491

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.60	13.63	13.40	14.46	15.47	12.17	13.20	12.97	14.03	15.04
	3H	14.27	15.20	15.09	16.03	17.07	13.80	14.73	14.61	15.56	16.60
	4H	14.87	15.75	15.70	16.59	17.64	14.40	15.27	15.23	16.11	17.16
	6H	15.28	16.09	16.12	16.93	18.00	14.80	15.61	15.64	16.46	17.52
	8H	15.39	16.16	16.24	17.02	18.09	14.91	15.68	15.76	16.55	17.61
	12H	15.44	16.18	16.30	17.04	18.13	14.96	15.70	15.82	16.55	17.65
4H	2H	13.08	13.96	13.92	14.80	15.85	12.74	13.62	13.57	14.46	15.51
	3H	14.96	15.70	15.81	16.57	17.64	14.57	15.30	15.42	16.18	17.24
	4H	15.69	16.35	16.54	17.22	18.32	15.28	15.95	16.14	16.82	17.91
	6H	16.21	16.79	17.08	17.68	18.78	15.80	16.38	16.68	17.27	18.37
	8H	16.36	16.90	17.24	17.79	18.90	15.95	16.49	16.83	17.38	18.49
	12H	16.45	16.93	17.34	17.84	18.96	16.02	16.51	16.92	17.42	18.53
8H	4H	15.90	16.44	16.77	17.32	18.43	15.54	16.08	16.41	16.96	18.07
	6H	16.53	16.98	17.44	17.91	19.02	16.17	16.62	17.08	17.55	18.66
	8H	16.76	17.15	17.67	18.08	19.20	16.39	16.78	17.30	17.71	18.84
	12H	16.90	17.25	17.81	18.16	19.34	16.51	16.86	17.43	17.78	18.96
12H	4H	15.89	16.38	16.79	17.28	18.40	15.54	16.02	16.44	16.93	18.05
	6H	16.57	16.96	17.48	17.89	19.01	16.21	16.61	17.13	17.53	18.66
	8H	16.82	17.17	17.73	18.08	19.26	16.46	16.81	17.38	17.72	18.90

END OF REPORT