

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913009

Luminaire Tested: DFN2DIP-TR4F0-110D110US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913009
REPORT IS A COMBINATION OF REPORTS P902030 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D110US850-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22446.1 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 197.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4005	4005	4005
5°	4012	3942	3967
10°	3972	3864	3838
15°	3917	3737	3638
20°	3845	3561	3393
25°	3771	3363	3157
30°	3672	3161	2857
35°	3574	2943	2593
40°	3475	2718	2291
45°	3360	2468	2017
50°	3241	2216	1750
55°	3116	1947	1493
60°	2973	1665	1229
65°	2807	1378	1105
70°	2606	1111	1000
75°	2354	980	910
80°	1989	822	789
85°	1387	548	592

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3360 cd/sqm

TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	2.1
10°-20°	1297.2	5.8
20°-30°	1821.2	8.1
30°-40°	1985.2	8.8
40°-50°	1824.6	8.1
50°-60°	1433.0	6.4
60°-70°	932.7	4.2
70°-80°	480.1	2.1
80°-90°	129.8	0.6
90°-100°	135.7	0.6
100°-110°	506.1	2.3
110°-120°	1342.2	6.0
120°-130°	2226.1	9.9
130°-140°	2364.7	10.5
140°-150°	2197.7	9.8
150°-160°	1766.9	7.9
160°-170°	1138.5	5.1
170°-180°	391.9	1.7
0°-30°	3590.9	16.0
0°-40°	5576.1	24.8
0°-60°	8833.7	39.4
0°-90°	10376.4	46.2
90°-120°	1984.0	8.8
90°-150°	8772.5	39.1
90°-180°	12070.0	53.8
0°-180°	22446.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5042	5042	5042	5042	5042	
5°	5042	5019	4960	5001	4987	478
15°	4795	4745	4590	4504	4458	1351
25°	4353	4207	3906	3719	3650	2002
35°	3751	3518	3117	2829	2728	2348
45°	3066	2760	2282	1957	1848	2368
55°	2331	1976	1483	1209	1123	2083
65°	1574	1204	794	639	625	1561
75°	839	520	365	333	329	888
85°	196	100	87	87	87	225
90°	3	36	59	75	80	21
95°	194	95	116	131	128	229
105°	906	995	182	214	226	968
115°	1713	1763	1838	459	244	1686
125°	2422	2461	2517	2538	2547	2160
135°	2997	3045	3071	3101	3095	2315
145°	3477	3474	3524	3545	3530	2174
155°	3828	3801	3837	3855	3831	1764
165°	4034	4016	4025	4046	4025	1140
175°	4126	4105	4111	4132	4102	393
180°	4117	4117	4117	4117	4117	



TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5041.8	5041.8	5041.8	5041.8	5041.8
2.5°	5064.6	5041.8	4991.5	5037.5	5028.3
5°	5041.8	5019.1	4959.6	5000.7	4987.2
7.5°	5000.7	4973.5	4909.7	4927.6	4904.8
10°	4946.0	4914.0	4823.0	4809.0	4781.9
12.5°	4877.7	4836.6	4713.1	4686.0	4635.6
15°	4795.4	4745.1	4590.2	4503.5	4458.0
17.5°	4699.6	4626.5	4434.8	4334.5	4261.4
20°	4590.2	4498.7	4270.6	4156.9	4056.2
22.5°	4471.6	4366.5	4101.7	3946.8	3878.5
25°	4352.9	4206.8	3905.7	3718.8	3650.1
27.5°	4211.6	4056.2	3723.1	3508.7	3403.6
30°	4061.0	3887.3	3522.3	3289.8	3166.4
32.5°	3914.9	3704.7	3331.0	3057.1	2942.8
35°	3750.7	3517.9	3116.6	2829.1	2728.4
37.5°	3591.1	3339.8	2915.7	2600.5	2486.8
40°	3422.0	3148.6	2705.6	2381.7	2263.1
42.5°	3248.7	2956.8	2496.0	2158.1	2044.3
45°	3066.3	2760.3	2281.5	1957.2	1847.8
47.5°	2892.9	2569.1	2076.3	1751.9	1651.7
50°	2701.2	2377.4	1875.4	1560.3	1464.9
52.5°	2513.9	2171.6	1683.7	1382.6	1295.9
55°	2331.3	1975.6	1482.7	1209.3	1122.6
57.5°	2144.6	1779.5	1305.1	1049.6	976.4
60°	1952.8	1587.9	1117.8	885.4	812.3
62.5°	1766.0	1401.0	958.1	739.3	702.9
65°	1574.2	1204.4	793.9	639.0	624.9
67.5°	1391.8	1021.9	639.0	561.0	547.5
70°	1200.0	844.3	529.1	483.6	465.2
72.5°	1017.5	679.7	442.5	406.1	396.9
75°	839.4	519.9	365.0	333.0	328.7
77.5°	661.7	369.4	287.6	269.2	259.9
80°	497.2	264.8	218.8	201.0	201.0
82.5°	346.6	178.1	150.6	141.4	141.4
85°	196.1	100.3	86.6	86.6	86.6
87.5°	73.1	36.3	36.3	31.9	31.9
90°	2.9	35.7	59.4	74.6	80.3
92.5°	74.6	62.7	71.4	77.5	80.3
95°	193.5	95.2	116.0	131.2	128.1
97.5°	348.4	104.4	151.7	160.9	163.8
100°	527.4	119.2	169.8	193.5	199.5
102.5°	723.7	718.1	175.8	208.4	217.6
105°	905.6	995.1	181.9	214.4	226.5
107.5°	1117.2	1191.4	187.9	220.4	232.4
110°	1319.8	1382.1	521.5	223.6	235.2

TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1510.6	1563.9	1513.3	229.2	238.4
115°	1712.9	1763.4	1838.2	458.8	244.4
117.5°	1888.7	1948.2	1999.1	1572.8	792.4
120°	2085.4	2129.9	2183.7	2219.4	1817.2
122.5°	2252.0	2299.7	2359.5	2377.3	2380.5
125°	2421.8	2460.8	2517.3	2538.2	2547.0
127.5°	2576.8	2618.5	2663.4	2693.1	2696.0
130°	2722.8	2770.6	2803.1	2836.0	2833.3
132.5°	2871.8	2910.7	2943.3	2970.1	2967.4
135°	2997.1	3044.8	3071.3	3101.4	3095.3
137.5°	3127.9	3163.6	3193.7	3223.4	3214.5
140°	3256.0	3280.0	3312.6	3339.4	3324.6
142.5°	3363.5	3384.3	3422.9	3446.7	3431.8
145°	3476.7	3473.5	3524.1	3545.0	3530.2
147.5°	3574.8	3565.9	3616.4	3631.3	3619.7
150°	3670.2	3649.4	3697.1	3714.8	3700.0
152.5°	3750.5	3726.8	3771.4	3789.5	3768.6
155°	3828.0	3801.4	3837.1	3854.9	3831.2
157.5°	3890.6	3866.9	3893.8	3914.7	3890.6
160°	3944.4	3926.3	3944.4	3962.0	3941.2
162.5°	3991.7	3974.1	3989.0	4009.8	3983.0
165°	4033.5	4015.8	4024.7	4045.5	4024.7
167.5°	4066.4	4048.4	4057.6	4078.5	4051.6
170°	4093.3	4075.2	4081.2	4102.2	4075.2
172.5°	4111.0	4093.3	4099.3	4120.2	4093.3
175°	4125.8	4105.0	4111.0	4131.9	4102.2
177.5°	4131.9	4111.0	4114.2	4135.0	4108.2
180°	4117.1	4117.1	4117.1	4117.1	4117.1

TEST NUMBER: P913009

CATALOG NUMBER: DFN2DIP-TR4F0-110D110US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.60	12.40	12.60	13.40	14.73	7.57	8.37	8.57	9.38	10.70
	3H	13.27	13.99	14.28	15.00	16.35	8.76	9.48	9.77	10.49	11.84
	4H	13.88	14.56	14.90	15.57	16.93	9.21	9.89	10.23	10.90	12.26
	6H	14.30	14.92	15.33	15.94	17.31	9.53	10.15	10.56	11.17	12.54
	8H	14.43	15.02	15.46	16.05	17.42	9.62	10.21	10.66	11.25	12.61
	12H	14.49	15.05	15.53	16.08	17.47	9.66	10.23	10.70	11.26	12.64
4H	2H	11.61	12.29	12.64	13.31	14.66	8.17	8.84	9.19	9.86	11.21
	3H	13.44	14.00	14.47	15.05	16.42	9.51	10.08	10.55	11.12	12.49
	4H	14.13	14.65	15.17	15.68	17.07	10.06	10.58	11.10	11.61	13.00
	6H	14.65	15.09	15.70	16.15	17.53	10.48	10.92	11.53	11.98	13.37
	8H	14.82	15.23	15.87	16.28	17.69	10.61	11.02	11.66	12.07	13.47
	12H	14.91	15.29	15.98	16.35	17.76	10.67	11.05	11.74	12.11	13.52
8H	4H	14.10	14.51	15.15	15.56	16.96	10.34	10.75	11.39	11.80	13.20
	6H	14.66	15.00	15.74	16.10	17.50	10.86	11.20	11.93	12.29	13.69
	8H	14.88	15.18	15.96	16.25	17.67	11.05	11.35	12.13	12.43	13.84
	12H	15.02	15.28	16.10	16.35	17.81	11.17	11.43	12.25	12.50	13.96
12H	4H	14.05	14.42	15.12	15.49	16.89	10.34	10.71	11.41	11.78	13.19
	6H	14.64	14.94	15.72	16.01	17.43	10.91	11.21	11.99	12.28	13.70
	8H	14.86	15.12	15.94	16.19	17.65	11.12	11.38	12.20	12.45	13.91

END OF REPORT