

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913028

Luminaire Tested: DFN2DIP-TR4F0-120D070US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913028
REPORT IS A COMBINATION OF REPORTS P900440 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D070US850-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18182.1 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 177.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38
5	72	60	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	33	29	27
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	26	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4370	4370	4370
5°	4377	4300	4328
10°	4333	4216	4187
15°	4274	4076	3969
20°	4195	3884	3702
25°	4114	3669	3444
30°	4005	3448	3116
35°	3899	3211	2829
40°	3791	2965	2499
45°	3665	2693	2200
50°	3535	2418	1909
55°	3400	2124	1628
60°	3243	1816	1340
65°	3062	1504	1206
70°	2843	1212	1091
75°	2568	1069	992
80°	2170	896	860
85°	1513	598	646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3665 cd/sqm

TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	2.8
10°-20°	1415.1	7.8
20°-30°	1986.8	10.9
30°-40°	2165.7	11.9
40°-50°	1990.5	10.9
50°-60°	1563.2	8.6
60°-70°	1017.5	5.6
70°-80°	523.8	2.9
80°-90°	140.7	0.8
90°-100°	151.9	0.8
100°-110°	482.7	2.7
110°-120°	826.1	4.5
120°-130°	1086.4	6.0
130°-140°	1219.5	6.7
140°-150°	1195.8	6.6
150°-160°	1003.1	5.5
160°-170°	665.3	3.7
170°-180°	232.5	1.3
0°-30°	3917.3	21.5
0°-40°	6083.0	33.5
0°-60°	9636.8	53.0
0°-90°	11318.7	62.3
90°-120°	1460.7	8.0
90°-150°	4962.4	27.3
90°-180°	6863.0	37.7
0°-180°	18182.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	2	27	72	68	70	18
95°	108	129	132	132	129	120
105°	446	452	456	460	460	470
115°	829	841	837	835	829	820
125°	1206	1224	1218	1212	1210	1077
135°	1560	1582	1587	1585	1579	1205
145°	1893	1908	1920	1922	1914	1183
155°	2165	2171	2178	2188	2181	997
165°	2355	2353	2353	2368	2357	664
175°	2451	2445	2440	2455	2443	233
180°	2455	2455	2455	2455	2455	

TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	2.2	26.6	72.5	68.1	70.3
92.5°	45.9	62.2	64.4	66.7	66.7
95°	108.0	128.8	132.5	132.5	128.8
97.5°	179.9	199.1	207.3	207.3	207.3
100°	262.7	279.8	285.7	285.7	283.5
102.5°	350.1	362.6	370.8	373.1	370.8
105°	445.6	451.5	455.9	459.7	459.7
107.5°	540.3	549.2	549.2	550.7	540.3
110°	632.1	644.0	644.0	644.0	638.0

TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	731.3	743.9	741.7	735.7	731.3
115°	829.0	840.8	837.2	835.0	829.0
117.5°	925.9	942.2	931.9	925.9	920.0
120°	1023.6	1039.9	1023.6	1023.6	1017.0
122.5°	1112.4	1133.2	1122.9	1116.9	1112.4
125°	1205.7	1224.2	1218.3	1211.7	1209.5
127.5°	1296.8	1319.7	1311.6	1302.7	1296.8
130°	1381.9	1408.5	1404.9	1400.4	1392.2
132.5°	1477.4	1498.1	1499.6	1489.3	1483.3
135°	1559.6	1582.4	1587.0	1584.7	1578.8
137.5°	1651.3	1669.8	1673.5	1672.0	1663.2
140°	1732.0	1750.6	1760.9	1760.9	1752.8
142.5°	1814.9	1833.4	1839.3	1841.5	1833.4
145°	1893.4	1908.1	1920.0	1922.2	1914.1
147.5°	1963.7	1982.2	1991.1	1994.8	1986.7
150°	2036.2	2048.8	2057.0	2063.6	2057.0
152.5°	2100.6	2113.2	2123.5	2131.7	2123.5
155°	2165.0	2170.9	2177.6	2187.9	2181.3
157.5°	2220.6	2225.0	2228.6	2243.5	2233.1
160°	2270.1	2274.6	2276.8	2289.3	2280.4
162.5°	2316.0	2316.0	2318.3	2332.2	2321.9
165°	2355.2	2353.0	2353.0	2367.8	2357.4
167.5°	2390.8	2384.1	2384.1	2398.9	2388.6
170°	2417.4	2411.5	2409.3	2424.1	2411.5
172.5°	2435.9	2429.9	2427.7	2442.6	2429.9
175°	2450.7	2444.8	2440.4	2455.1	2442.6
177.5°	2458.9	2452.9	2448.5	2461.1	2448.5
180°	2455.1	2455.1	2455.1	2455.1	2455.1

TEST NUMBER: P913028

CATALOG NUMBER: DFN2DIP-TR4F0-120D070US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.34	14.28	14.19	15.15	16.23	9.31	10.25	10.16	11.12	12.21
	3H	15.02	15.87	15.89	16.74	17.86	10.51	11.35	11.37	12.23	13.34
	4H	15.64	16.43	16.52	17.32	18.44	10.97	11.76	11.85	12.64	13.77
	6H	16.06	16.80	16.96	17.69	18.82	11.29	12.02	12.18	12.92	14.05
	8H	16.19	16.89	17.09	17.80	18.93	11.39	12.08	12.29	12.99	14.13
	12H	16.26	16.92	17.16	17.82	18.99	11.43	12.10	12.34	13.00	14.16
4H	2H	13.37	14.16	14.25	15.05	16.17	9.92	10.71	10.81	11.60	12.72
	3H	15.21	15.87	16.10	16.78	17.92	11.28	11.94	12.18	12.86	14.00
	4H	15.90	16.51	16.81	17.42	18.58	11.83	12.43	12.74	13.35	14.51
	6H	16.43	16.94	17.35	17.88	19.05	12.26	12.78	13.18	13.71	14.88
	8H	16.60	17.09	17.53	18.02	19.20	12.39	12.87	13.32	13.80	14.99
	12H	16.70	17.14	17.65	18.09	19.27	12.46	12.90	13.41	13.85	15.03
8H	4H	15.88	16.36	16.80	17.29	18.47	12.12	12.61	13.05	13.54	14.72
	6H	16.45	16.85	17.40	17.82	19.00	12.65	13.04	13.60	14.02	15.20
	8H	16.67	17.02	17.63	17.98	19.18	12.84	13.19	13.80	14.15	15.35
	12H	16.81	17.12	17.77	18.08	19.32	12.96	13.27	13.92	14.23	15.48
12H	4H	15.84	16.27	16.78	17.22	18.41	12.13	12.57	13.07	13.52	14.70
	6H	16.43	16.78	17.39	17.74	18.94	12.69	13.05	13.65	14.01	15.21
	8H	16.65	16.96	17.61	17.92	19.17	12.91	13.22	13.87	14.18	15.42

END OF REPORT