

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907497

Luminaire Tested: DFN2DIP-TR4F0-100D060US835-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907497  
REPORT IS A COMBINATION OF REPORTS P901938 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-100D060US835-RLLONL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14440.0 lumens  
Efficiency: N/A  
Efficacy: 99.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 145.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907497  
CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P907497

CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51			
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43			
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37			
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26			
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19			
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3283	3283	3283
5°	3289	3231	3252
10°	3256	3168	3146
15°	3211	3063	2982
20°	3152	2919	2781
25°	3091	2757	2588
30°	3010	2591	2342
35°	2930	2413	2126
40°	2849	2228	1878
45°	2754	2023	1653
50°	2657	1817	1434
55°	2555	1596	1224
60°	2437	1365	1007
65°	2301	1130	906
70°	2136	911	820
75°	1930	803	746
80°	1630	674	646
85°	1136	449	485

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2754 cd/sqm



TEST NUMBER: P907497

CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	387.3	2.7
10°-20°	1063.3	7.4
20°-30°	1492.9	10.3
30°-40°	1627.4	11.3
40°-50°	1495.7	10.4
50°-60°	1174.7	8.1
60°-70°	764.6	5.3
70°-80°	393.6	2.7
80°-90°	104.0	0.7
90°-100°	66.8	0.5
100°-110°	248.9	1.7
110°-120°	660.2	4.6
120°-130°	1094.9	7.6
130°-140°	1163.0	8.1
140°-150°	1080.9	7.5
150°-160°	869.0	6.0
160°-170°	560.0	3.9
170°-180°	192.7	1.3
0°-30°	2943.6	20.4
0°-40°	4571.0	31.7
0°-60°	7241.3	50.1
0°-90°	8503.5	58.9
90°-120°	975.8	6.8
90°-150°	4314.7	29.9
90°-180°	5936.0	41.1
0°-180°	14440.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	1	18	29	37	40	14
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	



TEST NUMBER: P907497

CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7



TEST NUMBER: P907497

CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9



TEST NUMBER: P907497  
 CATALOG NUMBER: DFN2DIP-TR4F0-100D060US835-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.06	12.97	12.95	13.87	15.01	8.04	8.95	8.92	9.85	10.99
	3H	13.75	14.56	14.64	15.47	16.64	9.23	10.05	10.13	10.95	12.12
	4H	14.36	15.13	15.27	16.04	17.22	9.69	10.45	10.60	11.37	12.55
	6H	14.78	15.49	15.71	16.41	17.60	10.01	10.72	10.94	11.64	12.83
	8H	14.91	15.58	15.84	16.52	17.71	10.11	10.78	11.04	11.72	12.90
	12H	14.98	15.62	15.91	16.55	17.76	10.15	10.79	11.09	11.72	12.94
4H	2H	12.09	12.86	13.01	13.77	14.95	8.64	9.41	9.56	10.32	11.50
	3H	13.93	14.57	14.86	15.51	16.70	10.00	10.64	10.93	11.58	12.77
	4H	14.62	15.20	15.56	16.14	17.36	10.55	11.13	11.49	12.07	13.29
	6H	15.14	15.64	16.09	16.61	17.82	10.98	11.48	11.93	12.44	13.66
	8H	15.32	15.79	16.27	16.74	17.97	11.11	11.57	12.06	12.53	13.76
	12H	15.42	15.84	16.39	16.81	18.05	11.18	11.60	12.15	12.57	13.81
8H	4H	14.60	15.06	15.55	16.02	17.25	10.84	11.30	11.79	12.26	13.49
	6H	15.17	15.55	16.14	16.55	17.78	11.36	11.75	12.34	12.75	13.98
	8H	15.38	15.72	16.37	16.71	17.96	11.55	11.89	12.54	12.88	14.13
	12H	15.52	15.82	16.51	16.81	18.10	11.68	11.98	12.67	12.96	14.25
12H	4H	14.55	14.97	15.52	15.95	17.18	10.85	11.27	11.82	12.24	13.48
	6H	15.14	15.48	16.13	16.47	17.72	11.41	11.75	12.40	12.74	13.99
	8H	15.37	15.67	16.36	16.65	17.94	11.63	11.92	12.62	12.91	14.20