

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915465

Luminaire Tested: DFN2DIP-TR4F0-040D060US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915465
REPORT IS A COMBINATION OF REPORTS P901926 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D060US927-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7398.9 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915465
CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915465
 CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31			31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27			27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1040	1040	1040
5°	1042	1024	1030
10°	1032	1004	997
15°	1018	971	945
20°	999	925	881
25°	980	874	820
30°	954	821	742
35°	928	764	674
40°	903	706	595
45°	873	641	524
50°	842	576	454
55°	810	506	388
60°	772	432	319
65°	729	358	287
70°	677	289	260
75°	611	254	236
80°	517	213	205
85°	360	142	154

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 873 cd/sqm



TEST NUMBER: P915465
 CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	1.7
10°-20°	336.9	4.6
20°-30°	473.1	6.4
30°-40°	515.7	7.0
40°-50°	473.9	6.4
50°-60°	372.2	5.0
60°-70°	242.3	3.3
70°-80°	124.7	1.7
80°-90°	34.7	0.5
90°-100°	52.9	0.7
100°-110°	197.2	2.7
110°-120°	523.0	7.1
120°-130°	867.4	11.7
130°-140°	921.3	12.5
140°-150°	856.3	11.6
150°-160°	688.4	9.3
160°-170°	443.6	6.0
170°-180°	152.7	2.1
0°-30°	932.7	12.6
0°-40°	1448.4	19.6
0°-60°	2294.6	31.0
0°-90°	2696.2	36.4
90°-120°	773.0	10.4
90°-150°	3418.0	46.2
90°-180°	4703.0	63.6
0°-180°	7398.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	14	23	29	31	7
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	



TEST NUMBER: P915465

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7



TEST NUMBER: P915465

CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1



TEST NUMBER: P915465
 CATALOG NUMBER: DFN2DIP-TR4F0-040D060US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.86	6.60	6.94	7.66	9.12	1.84	2.57	2.91	3.64	5.09
	3H	7.53	8.19	8.61	9.27	10.74	3.02	3.67	4.10	4.75	6.22
	4H	8.14	8.76	9.23	9.84	11.32	3.47	4.09	4.56	5.16	6.64
	6H	8.55	9.12	9.65	10.21	11.70	3.78	4.35	4.88	5.43	6.93
	8H	8.68	9.22	9.78	10.32	11.80	3.87	4.41	4.98	5.51	7.00
	12H	8.74	9.25	9.84	10.34	11.85	3.91	4.43	5.02	5.52	7.03
4H	2H	5.87	6.49	6.97	7.57	9.05	2.42	3.04	3.52	4.12	5.60
	3H	7.69	8.21	8.80	9.31	10.80	3.76	4.28	4.87	5.38	6.88
	4H	8.38	8.85	9.49	9.95	11.46	4.31	4.78	5.42	5.88	7.39
	6H	8.89	9.29	10.00	10.41	11.92	4.72	5.13	5.84	6.25	7.75
	8H	9.06	9.44	10.18	10.55	12.07	4.85	5.23	5.97	6.34	7.86
	12H	9.15	9.49	10.28	10.62	12.14	4.91	5.25	6.04	6.38	7.90
8H	4H	8.34	8.72	9.46	9.83	11.35	4.58	4.96	5.70	6.07	7.59
	6H	8.90	9.21	10.04	10.37	11.88	5.10	5.41	6.23	6.56	8.08
	8H	9.12	9.39	10.26	10.52	12.06	5.29	5.56	6.43	6.69	8.23
	12H	9.25	9.49	10.40	10.62	12.20	5.40	5.64	6.55	6.77	8.35
12H	4H	8.29	8.63	9.42	9.75	11.28	4.58	4.92	5.71	6.05	7.57
	6H	8.88	9.15	10.02	10.28	11.82	5.15	5.42	6.29	6.55	8.09
	8H	9.09	9.33	10.24	10.46	12.04	5.35	5.59	6.50	6.72	8.30