

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907530

Luminaire Tested: DFN2DIP-TR4F0-110D060US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907530
REPORT IS A COMBINATION OF REPORTS P900419 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D060US835-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16200.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	97	93	90	96	92	88	85	82	79	76	72	70	68	64	62	61
2	93	85	79	73	87	80	75	70	72	67	63	63	60	57	56	54	51
3	85	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38
5	71	59	51	45	67	56	49	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	51	43	37	45	39	35	41	36	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3400	3400	3400
5°	3406	3353	3375
10°	3378	3308	3330
15°	3329	3253	3258
20°	3261	3178	3185
25°	3195	3087	3100
30°	3111	3003	2993
35°	3032	2903	2879
40°	2934	2803	2771
45°	2837	2703	2660
50°	2731	2597	2532
55°	2619	2475	2414
60°	2493	2330	2278
65°	2356	2180	2119
70°	2181	1997	1947
75°	1939	1778	1789
80°	1648	1499	1486
85°	1192	1017	985

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2837 cd/sqm

TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.8	2.5
10°-20°	1133.5	7.0
20°-30°	1665.7	10.3
30°-40°	1934.7	11.9
40°-50°	1932.3	11.9
50°-60°	1684.9	10.4
60°-70°	1245.5	7.7
70°-80°	704.7	4.3
80°-90°	191.4	1.2
90°-100°	117.4	0.7
100°-110°	373.1	2.3
110°-120°	638.5	3.9
120°-130°	839.7	5.2
130°-140°	942.5	5.8
140°-150°	924.2	5.7
150°-160°	775.3	4.8
160°-170°	514.2	3.2
170°-180°	179.7	1.1
0°-30°	3202.1	19.8
0°-40°	5136.7	31.7
0°-60°	8753.8	54.0
0°-90°	10895.4	67.3
90°-120°	1129.0	7.0
90°-150°	3835.4	23.7
90°-180°	5305.0	32.7
0°-180°	16200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4280	4280	4280	4280	4280	
5°	4280	4264	4219	4251	4244	406
15°	4074	4050	3996	4013	3992	1148
25°	3688	3655	3585	3593	3585	1697
35°	3182	3140	3074	3050	3029	1987
45°	2589	2560	2498	2453	2437	1998
55°	1959	1934	1885	1836	1815	1752
65°	1321	1296	1255	1218	1198	1306
75°	691	683	662	638	646	738
85°	169	165	161	148	144	188
90°	2	21	56	53	54	15
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	

TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4280.2	4280.2	4280.2	4280.2	4280.2
2.5°	4305.0	4284.5	4239.1	4280.2	4272.3
5°	4280.2	4264.0	4218.6	4251.3	4243.5
7.5°	4251.3	4226.9	4181.5	4214.7	4206.4
10°	4206.4	4177.5	4128.2	4160.9	4148.7
12.5°	4144.4	4119.9	4070.6	4091.1	4082.8
15°	4074.5	4050.0	3996.3	4012.9	3992.4
17.5°	3988.0	3963.6	3909.9	3930.4	3909.9
20°	3893.3	3868.8	3811.2	3823.4	3807.3
22.5°	3799.0	3761.8	3708.1	3708.1	3699.8
25°	3687.6	3654.9	3585.0	3592.9	3585.0
27.5°	3564.0	3535.2	3481.9	3469.7	3449.2
30°	3440.9	3407.7	3346.1	3333.9	3317.3
32.5°	3309.0	3284.6	3218.6	3193.7	3177.1
35°	3181.5	3140.5	3074.5	3049.6	3029.1
37.5°	3037.4	3000.3	2934.4	2905.5	2885.0
40°	2889.4	2856.2	2790.3	2753.6	2737.0
42.5°	2745.3	2712.1	2646.6	2605.1	2580.7
45°	2589.0	2560.1	2498.1	2453.2	2436.6
47.5°	2436.6	2407.8	2341.8	2296.4	2271.9
50°	2275.9	2255.4	2197.7	2140.1	2119.6
52.5°	2119.6	2090.7	2037.5	1992.0	1963.2
55°	1959.3	1934.4	1885.1	1835.7	1815.2
57.5°	1798.6	1778.1	1724.4	1675.0	1658.4
60°	1637.9	1621.8	1564.1	1518.7	1506.5
62.5°	1481.6	1452.8	1411.7	1370.7	1354.1
65°	1321.3	1296.4	1255.4	1218.3	1197.8
67.5°	1156.7	1135.8	1099.1	1070.3	1053.7
70°	1004.3	987.7	950.6	921.8	905.6
72.5°	848.0	831.4	810.9	782.1	769.8
75°	691.2	683.4	662.4	638.0	646.3
77.5°	551.5	534.9	526.6	514.4	502.2
80°	411.8	407.4	399.1	386.9	378.6
82.5°	279.9	279.9	276.0	259.4	259.4
85°	168.6	164.6	160.7	148.0	144.1
87.5°	74.2	65.9	57.6	45.4	41.0
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1

TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6

TEST NUMBER: P907530

CATALOG NUMBER: DFN2DIP-TR4F0-110D060US835-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.98	14.02	13.77	14.83	15.83	12.54	13.58	13.34	14.40	15.40
	3H	14.65	15.58	15.46	16.41	17.44	14.18	15.11	14.98	15.94	16.97
	4H	15.24	16.13	16.07	16.96	18.00	14.77	15.65	15.59	16.49	17.53
	6H	15.65	16.47	16.49	17.31	18.36	15.18	15.99	16.01	16.83	17.89
	8H	15.76	16.54	16.61	17.40	18.45	15.29	16.06	16.13	16.93	17.98
	12H	15.82	16.56	16.67	17.41	18.49	15.34	16.08	16.19	16.93	18.01
4H	2H	13.46	14.34	14.29	15.18	16.22	13.11	14.00	13.94	14.83	15.87
	3H	15.34	16.08	16.18	16.94	18.00	14.95	15.69	15.79	16.55	17.61
	4H	16.06	16.73	16.91	17.60	18.68	15.66	16.33	16.51	17.19	18.28
	6H	16.59	17.17	17.46	18.06	19.14	16.18	16.76	17.05	17.65	18.74
	8H	16.74	17.28	17.61	18.17	19.27	16.33	16.87	17.20	17.76	18.86
	12H	16.82	17.31	17.71	18.22	19.32	16.40	16.89	17.29	17.79	18.90
8H	4H	16.27	16.82	17.14	17.70	18.80	15.91	16.46	16.78	17.34	18.44
	6H	16.91	17.36	17.81	18.29	19.39	16.55	17.00	17.45	17.92	19.03
	8H	17.13	17.53	18.04	18.45	19.57	16.77	17.16	17.68	18.08	19.20
	12H	17.27	17.63	18.19	18.54	19.71	16.89	17.24	17.80	18.15	19.32
12H	4H	16.27	16.76	17.16	17.66	18.77	15.92	16.40	16.81	17.31	18.41
	6H	16.94	17.34	17.85	18.26	19.38	16.59	16.99	17.50	17.91	19.03
	8H	17.19	17.55	18.11	18.46	19.63	16.84	17.19	17.75	18.10	19.27