

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910184

Luminaire Tested: DFN2DIP-TR4F0-090D050US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910184
REPORT IS A COMBINATION OF REPORTS P900398 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D050US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12194.1 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 125.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	68	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	47	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2984	2984	2984
5°	2989	2937	2956
10°	2959	2879	2859
15°	2919	2784	2711
20°	2865	2653	2528
25°	2810	2506	2352
30°	2736	2355	2128
35°	2663	2193	1932
40°	2589	2025	1707
45°	2503	1839	1503
50°	2415	1651	1304
55°	2322	1450	1112
60°	2215	1240	915
65°	2091	1027	824
70°	1942	828	745
75°	1754	730	678
80°	1482	612	588
85°	1032	408	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2503 cd/sqm

TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	2.9
10°-20°	966.5	7.9
20°-30°	1356.9	11.1
30°-40°	1479.1	12.1
40°-50°	1359.4	11.1
50°-60°	1067.6	8.8
60°-70°	694.9	5.7
70°-80°	357.7	2.9
80°-90°	95.9	0.8
90°-100°	98.8	0.8
100°-110°	314.0	2.6
110°-120°	537.3	4.4
120°-130°	706.6	5.8
130°-140°	793.2	6.5
140°-150°	777.8	6.4
150°-160°	652.5	5.4
160°-170°	432.7	3.5
170°-180°	151.2	1.2
0°-30°	2675.4	21.9
0°-40°	4154.5	34.1
0°-60°	6581.5	54.0
0°-90°	7730.0	63.4
90°-120°	950.1	7.8
90°-150°	3227.7	26.5
90°-180°	4464.0	36.6
0°-180°	12194.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	1	17	47	44	46	12
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	

TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9

TEST NUMBER: P910184

CATALOG NUMBER: DFN2DIP-TR4F0-090D050US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.11	13.06	12.95	13.92	14.99	8.08	9.03	8.92	9.89	10.96
	3H	13.79	14.65	14.65	15.51	16.61	9.28	10.13	10.13	11.00	12.09
	4H	14.41	15.21	15.28	16.08	17.19	9.73	10.54	10.60	11.41	12.52
	6H	14.83	15.57	15.72	16.46	17.58	10.06	10.80	10.94	11.68	12.80
	8H	14.96	15.67	15.85	16.57	17.69	10.16	10.86	11.05	11.76	12.88
	12H	15.03	15.70	15.92	16.59	17.74	10.21	10.88	11.10	11.77	12.91
4H	2H	12.14	12.94	13.01	13.82	14.92	8.69	9.49	9.56	10.37	11.47
	3H	13.98	14.65	14.86	15.55	16.68	10.05	10.72	10.94	11.63	12.75
	4H	14.68	15.28	15.57	16.19	17.33	10.61	11.21	11.50	12.12	13.26
	6H	15.20	15.72	16.11	16.65	17.80	11.03	11.56	11.94	12.48	13.63
	8H	15.38	15.86	16.29	16.78	17.95	11.16	11.65	12.08	12.57	13.74
	12H	15.48	15.92	16.41	16.85	18.02	11.24	11.68	12.17	12.61	13.78
8H	4H	14.65	15.14	15.57	16.06	17.23	10.89	11.38	11.81	12.30	13.47
	6H	15.22	15.63	16.16	16.59	17.75	11.42	11.82	12.36	12.78	13.95
	8H	15.44	15.80	16.39	16.75	17.93	11.61	11.97	12.56	12.92	14.10
	12H	15.58	15.90	16.54	16.84	18.08	11.74	12.05	12.69	13.00	14.23
12H	4H	14.61	15.05	15.54	15.99	17.16	10.90	11.34	11.84	12.28	13.45
	6H	15.20	15.56	16.15	16.51	17.69	11.47	11.83	12.42	12.78	13.96
	8H	15.43	15.74	16.38	16.69	17.92	11.68	12.00	12.64	12.95	14.18