

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915662

Luminaire Tested: DFN2DIP-TR4F0-090D110US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915662
REPORT IS A COMBINATION OF REPORTS P900505 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D110US927-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14770.2 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 172.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915662
CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915662

CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38	34	34	34	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29	29	29	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25	25	25	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21	21	21	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17	17	17	17
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17	15	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13	13	13	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2204	2204	2204
5°	2207	2173	2188
10°	2190	2144	2158
15°	2157	2109	2112
20°	2114	2059	2064
25°	2071	2001	2009
30°	2016	1946	1940
35°	1965	1882	1866
40°	1902	1817	1796
45°	1839	1752	1724
50°	1770	1683	1641
55°	1698	1604	1564
60°	1616	1510	1477
65°	1527	1413	1373
70°	1414	1294	1262
75°	1257	1152	1159
80°	1068	971	963
85°	772	659	638

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2147 cd/sqm



TEST NUMBER: P915662

CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.1	1.8
10°-20°	734.7	5.0
20°-30°	1079.6	7.3
30°-40°	1253.9	8.5
40°-50°	1252.4	8.5
50°-60°	1092.1	7.4
60°-70°	807.3	5.5
70°-80°	456.7	3.1
80°-90°	128.4	0.9
90°-100°	170.5	1.2
100°-110°	541.8	3.7
110°-120°	927.3	6.3
120°-130°	1219.5	8.3
130°-140°	1368.8	9.3
140°-150°	1342.3	9.1
150°-160°	1126.0	7.6
160°-170°	746.7	5.1
170°-180°	261.0	1.8
0°-30°	2075.4	14.1
0°-40°	3329.4	22.5
0°-60°	5673.8	38.4
0°-90°	7066.2	47.8
90°-120°	1639.7	11.1
90°-150°	5570.3	37.7
90°-180°	7704.0	52.2
0°-180°	14770.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2774	2774	2774	2774	2774	
5°	2774	2764	2734	2756	2750	263
15°	2641	2625	2590	2601	2588	744
25°	2390	2369	2324	2329	2324	1100
35°	2062	2036	1993	1977	1963	1288
45°	1678	1659	1619	1590	1579	1295
55°	1270	1254	1222	1190	1176	1135
65°	856	840	814	790	776	847
75°	448	443	429	414	419	478
85°	109	107	104	96	93	122
90°	2	30	81	76	79	14
95°	121	145	149	149	145	135
105°	500	507	512	516	516	528
115°	931	944	940	937	931	920
125°	1353	1374	1368	1360	1358	1209
135°	1751	1776	1781	1779	1772	1353
145°	2125	2142	2155	2158	2149	1328
155°	2430	2437	2444	2456	2448	1119
165°	2644	2641	2641	2658	2646	746
175°	2751	2744	2739	2756	2742	261
180°	2756	2756	2756	2756	2756	



TEST NUMBER: P915662

CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2774.1	2774.1	2774.1	2774.1	2774.1
2.5°	2790.3	2777.0	2747.6	2774.1	2769.1
5°	2774.1	2763.7	2734.3	2755.5	2750.4
7.5°	2755.5	2739.7	2710.2	2731.8	2726.4
10°	2726.4	2707.7	2675.7	2696.9	2689.0
12.5°	2686.1	2670.3	2638.4	2651.6	2646.3
15°	2640.9	2625.1	2590.2	2601.0	2587.7
17.5°	2584.8	2569.0	2534.2	2547.5	2534.2
20°	2523.4	2507.6	2470.2	2478.1	2467.6
22.5°	2462.3	2438.3	2403.4	2403.4	2398.0
25°	2390.1	2368.9	2323.6	2328.7	2323.6
27.5°	2310.0	2291.3	2256.8	2248.9	2235.6
30°	2230.2	2208.7	2168.8	2160.8	2150.1
32.5°	2144.8	2128.9	2086.1	2070.0	2059.3
35°	2062.1	2035.5	1992.7	1976.7	1963.3
37.5°	1968.7	1944.6	1901.9	1883.3	1869.9
40°	1872.7	1851.2	1808.5	1784.7	1774.0
42.5°	1779.3	1757.8	1715.4	1688.5	1672.7
45°	1678.0	1659.4	1619.1	1590.0	1579.3
47.5°	1579.3	1560.6	1517.8	1488.4	1472.6
50°	1475.1	1461.8	1424.4	1387.1	1373.8
52.5°	1373.8	1355.1	1320.6	1291.2	1272.5
55°	1269.9	1253.8	1221.8	1189.9	1176.5
57.5°	1165.8	1152.5	1117.7	1085.7	1074.9
60°	1061.6	1051.1	1013.8	984.4	976.4
62.5°	960.3	941.6	915.0	888.4	877.7
65°	856.4	840.3	813.6	789.6	776.3
67.5°	749.7	736.2	712.3	693.7	682.9
70°	650.9	640.2	616.2	597.5	587.0
72.5°	549.6	538.8	525.5	506.9	499.0
75°	448.1	442.9	429.4	413.5	418.9
77.5°	357.4	346.7	341.4	333.4	325.5
80°	266.9	264.0	258.6	250.7	245.4
82.5°	181.4	181.4	178.9	168.1	168.1
85°	109.2	106.7	104.2	95.9	93.4
87.5°	48.1	42.7	37.4	29.5	26.6
90°	2.5	29.9	81.4	76.4	78.9
92.5°	51.5	69.8	72.2	74.8	74.8
95°	121.3	144.6	148.7	148.7	144.6
97.5°	201.9	223.5	232.7	232.7	232.7
100°	294.9	314.0	320.7	320.7	318.2
102.5°	393.0	407.1	416.3	418.7	416.3
105°	500.2	506.8	511.8	515.9	515.9
107.5°	606.5	616.5	616.5	618.1	606.5
110°	709.6	722.9	722.9	722.9	716.2



TEST NUMBER: P915662

CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	820.9	835.0	832.5	825.8	820.9
115°	930.6	943.8	939.7	937.2	930.6
117.5°	1039.4	1057.6	1046.0	1039.4	1032.8
120°	1149.1	1167.4	1149.1	1149.1	1141.6
122.5°	1248.8	1272.0	1260.4	1253.7	1248.8
125°	1353.4	1374.2	1367.5	1360.1	1357.6
127.5°	1455.6	1481.4	1472.3	1462.3	1455.6
130°	1551.2	1581.1	1576.9	1571.9	1562.8
132.5°	1658.4	1681.6	1683.3	1671.7	1665.0
135°	1750.6	1776.3	1781.3	1778.8	1772.2
137.5°	1853.6	1874.4	1878.5	1876.8	1866.9
140°	1944.2	1964.9	1976.6	1976.6	1967.5
142.5°	2037.3	2058.0	2064.7	2067.1	2058.0
145°	2125.3	2141.9	2155.2	2157.7	2148.6
147.5°	2204.2	2225.0	2235.0	2239.1	2230.0
150°	2285.7	2299.8	2308.9	2316.4	2308.9
152.5°	2357.9	2372.0	2383.7	2392.9	2383.7
155°	2430.3	2436.8	2444.4	2456.0	2448.5
157.5°	2492.5	2497.5	2501.6	2518.3	2506.6
160°	2548.2	2553.2	2555.7	2569.8	2559.9
162.5°	2599.7	2599.7	2602.2	2618.0	2606.4
165°	2643.7	2641.2	2641.2	2657.8	2646.2
167.5°	2683.6	2676.1	2676.1	2692.8	2681.1
170°	2713.5	2706.9	2704.4	2721.0	2706.9
172.5°	2734.3	2727.6	2725.2	2741.8	2727.6
175°	2750.9	2744.3	2739.3	2755.9	2741.8
177.5°	2760.0	2753.4	2748.4	2762.6	2748.4
180°	2755.9	2755.9	2755.9	2755.9	2755.9



TEST NUMBER: P915662
 CATALOG NUMBER: DFN2DIP-TR4F0-090D110US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.81	10.65	10.78	11.64	12.94	9.38	10.22	10.35	11.21	12.51
	3H	11.47	12.22	12.45	13.22	14.54	10.99	11.75	11.98	12.75	14.07
	4H	12.05	12.77	13.05	13.77	15.10	11.58	12.29	12.58	13.30	14.63
	6H	12.45	13.11	13.46	14.12	15.46	11.98	12.64	12.99	13.64	14.99
	8H	12.56	13.18	13.57	14.21	15.55	12.08	12.71	13.10	13.73	15.07
	12H	12.60	13.20	13.62	14.22	15.58	12.12	12.72	13.14	13.74	15.10
4H	2H	10.27	10.98	11.27	11.98	13.32	9.92	10.64	10.93	11.64	12.97
	3H	12.13	12.73	13.15	13.76	15.10	11.74	12.34	12.75	13.37	14.71
	4H	12.84	13.39	13.87	14.41	15.78	12.44	12.99	13.46	14.01	15.38
	6H	13.36	13.83	14.39	14.87	16.24	12.95	13.42	13.98	14.47	15.83
	8H	13.51	13.95	14.54	14.99	16.36	13.10	13.53	14.13	14.57	15.95
	12H	13.58	13.98	14.63	15.03	16.41	13.16	13.55	14.21	14.61	15.99
8H	4H	13.04	13.48	14.07	14.52	15.90	12.68	13.12	13.71	14.16	15.54
	6H	13.67	14.03	14.73	15.11	16.49	13.31	13.67	14.37	14.75	16.13
	8H	13.89	14.21	14.96	15.28	16.67	13.52	13.84	14.59	14.91	16.30
	12H	14.02	14.30	15.09	15.36	16.80	13.64	13.92	14.71	14.98	16.42
12H	4H	13.02	13.42	14.08	14.48	15.86	12.67	13.07	13.72	14.12	15.51
	6H	13.70	14.02	14.76	15.08	16.48	13.35	13.67	14.41	14.73	16.13
	8H	13.94	14.22	15.01	15.28	16.72	13.58	13.86	14.65	14.93	16.36