

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910218

Luminaire Tested: DFN2DIP-TR4F0-100D050US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910218
REPORT IS A COMBINATION OF REPORTS P900399 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D050US840-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14466.3 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 138.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910218
CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910218
 CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				69
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58				58
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49				49
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41				41
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35				35
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31				31
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27				27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26	24				24
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22				22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19				19
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3122	3122	3122
5°	3127	3078	3099
10°	3101	3037	3057
15°	3056	2987	2991
20°	2994	2917	2924
25°	2933	2834	2846
30°	2856	2757	2747
35°	2783	2666	2643
40°	2694	2573	2544
45°	2604	2481	2442
50°	2507	2384	2324
55°	2405	2272	2216
60°	2289	2139	2092
65°	2163	2001	1945
70°	2002	1833	1788
75°	1780	1632	1642
80°	1512	1376	1364
85°	1094	933	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2604 cd/sqm



TEST NUMBER: P910218

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.8	2.6
10°-20°	1040.6	7.2
20°-30°	1529.3	10.6
30°-40°	1776.1	12.3
40°-50°	1773.9	12.3
50°-60°	1546.8	10.7
60°-70°	1143.4	7.9
70°-80°	646.9	4.5
80°-90°	175.3	1.2
90°-100°	98.8	0.7
100°-110°	314.0	2.2
110°-120°	537.3	3.7
120°-130°	706.6	4.9
130°-140°	793.2	5.5
140°-150°	777.8	5.4
150°-160°	652.5	4.5
160°-170°	432.7	3.0
170°-180°	151.2	1.0
0°-30°	2939.7	20.3
0°-40°	4715.8	32.6
0°-60°	8036.5	55.6
0°-90°	10002.2	69.1
90°-120°	950.1	6.6
90°-150°	3227.7	22.3
90°-180°	4464.0	30.9
0°-180°	14466.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3930	3930	3930	3930	3930	
5°	3930	3915	3873	3903	3896	373
15°	3741	3718	3669	3684	3665	1054
25°	3386	3355	3291	3298	3291	1558
35°	2921	2883	2823	2800	2781	1824
45°	2377	2350	2293	2252	2237	1834
55°	1799	1776	1731	1685	1666	1608
65°	1213	1190	1153	1118	1100	1199
75°	635	627	608	586	593	677
85°	155	151	148	136	132	173
90°	1	17	47	44	46	14
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P910218

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3929.5	3929.5	3929.5	3929.5	3929.5
2.5°	3952.3	3933.4	3891.7	3929.5	3922.2
5°	3929.5	3914.6	3872.9	3903.0	3895.8
7.5°	3903.0	3880.5	3838.8	3869.3	3861.7
10°	3861.7	3835.3	3789.9	3820.0	3808.8
12.5°	3804.8	3782.4	3737.0	3755.9	3748.2
15°	3740.6	3718.2	3668.8	3684.1	3665.3
17.5°	3661.3	3638.8	3589.5	3608.4	3589.5
20°	3574.2	3551.8	3498.9	3510.1	3495.2
22.5°	3487.7	3453.6	3404.3	3404.3	3396.7
25°	3385.5	3355.4	3291.3	3298.4	3291.3
27.5°	3272.0	3245.5	3196.6	3185.4	3166.5
30°	3159.0	3128.5	3071.9	3060.7	3045.5
32.5°	3037.9	3015.5	2954.9	2932.0	2916.8
35°	2920.8	2883.2	2822.6	2799.8	2780.9
37.5°	2788.5	2754.4	2693.9	2667.5	2648.6
40°	2652.6	2622.1	2561.6	2528.0	2512.7
42.5°	2520.3	2489.8	2429.7	2391.7	2369.2
45°	2376.8	2350.4	2293.4	2252.1	2237.0
47.5°	2237.0	2210.5	2149.9	2108.2	2085.8
50°	2089.4	2070.5	2017.6	1964.7	1945.9
52.5°	1945.9	1919.5	1870.5	1828.9	1802.4
55°	1798.8	1775.9	1730.6	1685.3	1666.5
57.5°	1651.2	1632.3	1583.1	1537.8	1522.6
60°	1503.7	1488.8	1435.9	1394.2	1383.0
62.5°	1360.2	1333.7	1296.1	1258.4	1243.1
65°	1213.1	1190.2	1152.6	1118.4	1099.6
67.5°	1062.0	1042.7	1009.1	982.6	967.4
70°	922.0	906.8	872.7	846.3	831.4
72.5°	778.5	763.3	744.5	718.0	706.7
75°	634.6	627.4	608.1	585.7	593.3
77.5°	506.3	491.1	483.4	472.2	461.0
80°	378.0	374.1	366.4	355.2	347.6
82.5°	257.0	257.0	253.4	238.1	238.1
85°	154.7	151.2	147.5	135.9	132.3
87.5°	68.2	60.5	52.9	41.7	37.7
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P910218

CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P910218
 CATALOG NUMBER: DFN2DIP-TR4F0-100D050US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.82	13.89	13.60	14.68	15.65	12.39	13.46	13.17	14.25	15.22
	3H	14.50	15.46	15.29	16.26	17.26	14.03	14.98	14.81	15.79	16.79
	4H	15.10	16.00	15.90	16.81	17.82	14.62	15.53	15.43	16.34	17.35
	6H	15.51	16.34	16.32	17.16	18.19	15.03	15.86	15.85	16.69	17.71
	8H	15.62	16.41	16.44	17.25	18.28	15.14	15.94	15.97	16.78	17.80
	12H	15.67	16.43	16.50	17.26	18.31	15.19	15.95	16.02	16.78	17.83
4H	2H	13.31	14.21	14.12	15.03	16.04	12.97	13.87	13.77	14.68	15.69
	3H	15.19	15.95	16.01	16.80	17.82	14.80	15.56	15.62	16.40	17.43
	4H	15.92	16.60	16.75	17.45	18.50	15.51	16.20	16.35	17.04	18.10
	6H	16.44	17.04	17.29	17.91	18.97	16.03	16.63	16.88	17.50	18.56
	8H	16.60	17.15	17.45	18.02	19.09	16.19	16.74	17.04	17.61	18.68
	12H	16.68	17.18	17.55	18.07	19.14	16.26	16.76	17.13	17.64	18.72
8H	4H	16.13	16.68	16.98	17.55	18.62	15.77	16.32	16.62	17.19	18.26
	6H	16.77	17.23	17.65	18.14	19.21	16.41	16.87	17.29	17.77	18.85
	8H	16.99	17.40	17.88	18.30	19.39	16.62	17.03	17.52	17.93	19.02
	12H	17.13	17.49	18.03	18.39	19.53	16.75	17.11	17.64	18.00	19.14
12H	4H	16.13	16.63	17.00	17.51	18.59	15.77	16.27	16.65	17.16	18.24
	6H	16.80	17.21	17.69	18.11	19.20	16.45	16.86	17.34	17.76	18.85
	8H	17.05	17.41	17.95	18.31	19.45	16.70	17.06	17.59	17.95	19.09