

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912758

Luminaire Tested: DFN2DIP-TR4F0-040D120US850-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P912758  
REPORT IS A COMBINATION OF REPORTS P900513 AND P897293  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-040D120US850-FLLFLL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16169.2 lumens  
Efficiency: N/A  
Efficacy: 131.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 123.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P912758  
CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFLL

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P912758

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30	23				23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21	16				16
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18	14				14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11				11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9				9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8				8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10	8				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1371	1371	1371
5°	1373	1352	1361
10°	1362	1334	1343
15°	1342	1312	1314
20°	1315	1281	1284
25°	1288	1245	1250
30°	1255	1211	1207
35°	1223	1171	1161
40°	1183	1130	1117
45°	1144	1090	1073
50°	1101	1047	1021
55°	1056	998	973
60°	1005	940	919
65°	950	879	855
70°	880	805	785
75°	782	717	721
80°	664	604	599
85°	481	410	397

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 3280 cd/sqm



TEST NUMBER: P912758

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	1.0
10°-20°	457.1	2.8
20°-30°	671.7	4.2
30°-40°	780.2	4.8
40°-50°	779.2	4.8
50°-60°	679.5	4.2
60°-70°	502.3	3.1
70°-80°	284.2	1.8
80°-90°	87.0	0.5
90°-100°	260.4	1.6
100°-110°	827.5	5.1
110°-120°	1416.1	8.8
120°-130°	1862.4	11.5
130°-140°	2090.5	12.9
140°-150°	2050.0	12.7
150°-160°	1719.6	10.6
160°-170°	1140.4	7.1
170°-180°	398.6	2.5
0°-30°	1291.3	8.0
0°-40°	2071.5	12.8
0°-60°	3530.2	21.8
0°-90°	4403.6	27.2
90°-120°	2504.0	15.5
90°-150°	8506.9	52.6
90°-180°	11766.0	72.8
0°-180°	16169.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	4	46	124	117	120	16
95°	185	221	227	227	221	206
105°	764	774	782	788	788	806
115°	1421	1442	1435	1431	1421	1406
125°	2067	2099	2089	2077	2073	1847
135°	2674	2713	2720	2717	2706	2066
145°	3246	3271	3291	3295	3281	2028
155°	3711	3722	3733	3751	3739	1708
165°	4038	4034	4034	4059	4041	1139
175°	4201	4191	4184	4209	4187	399
180°	4209	4209	4209	4209	4209	



TEST NUMBER: P912758

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	3.8	45.7	124.3	116.8	120.5
92.5°	78.6	106.6	110.3	114.2	114.2
95°	185.2	220.8	227.1	227.1	220.8
97.5°	308.3	341.4	355.3	355.3	355.3
100°	450.5	479.6	489.7	489.7	486.0
102.5°	600.2	621.7	635.7	639.6	635.7
105°	763.9	774.0	781.6	787.9	787.9
107.5°	926.2	941.5	941.5	944.0	926.2
110°	1083.6	1103.9	1103.9	1103.9	1093.8



TEST NUMBER: P912758

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1253.6	1275.2	1271.4	1261.3	1253.6
115°	1421.1	1441.5	1435.0	1431.3	1421.1
117.5°	1587.3	1615.3	1597.5	1587.3	1577.2
120°	1754.9	1782.7	1754.9	1754.9	1743.5
122.5°	1907.1	1942.6	1924.9	1914.7	1907.1
125°	2067.0	2098.7	2088.6	2077.2	2073.3
127.5°	2223.1	2262.4	2248.4	2233.2	2223.1
130°	2368.9	2414.6	2408.3	2400.7	2386.7
132.5°	2532.6	2568.2	2570.7	2552.9	2542.8
135°	2673.5	2712.8	2720.5	2716.6	2706.5
137.5°	2830.8	2862.6	2868.9	2866.3	2851.1
140°	2969.1	3000.8	3018.6	3018.6	3004.6
142.5°	3111.3	3143.0	3153.1	3156.9	3143.0
145°	3245.7	3271.1	3291.4	3295.3	3281.3
147.5°	3366.3	3398.0	3413.3	3419.6	3405.6
150°	3490.7	3512.2	3526.2	3537.6	3526.2
152.5°	3601.0	3622.5	3640.4	3654.4	3640.4
155°	3711.4	3721.6	3733.0	3750.7	3739.3
157.5°	3806.6	3814.2	3820.5	3845.9	3828.2
160°	3891.6	3899.2	3903.0	3924.6	3909.3
162.5°	3970.2	3970.2	3974.1	3998.2	3980.4
165°	4037.5	4033.8	4033.8	4059.1	4041.3
167.5°	4098.4	4087.0	4087.0	4112.4	4094.6
170°	4144.1	4133.9	4130.1	4155.5	4133.9
172.5°	4175.8	4165.6	4161.9	4187.3	4165.6
175°	4201.2	4191.0	4183.5	4208.8	4187.3
177.5°	4215.2	4205.0	4197.3	4219.0	4197.3
180°	4208.8	4208.8	4208.8	4208.8	4208.8



TEST NUMBER: P912758  
 CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.75	6.44	6.88	7.56	9.13	5.32	6.01	6.45	7.13	8.70
	3H	7.40	8.02	8.54	9.15	10.73	6.93	7.54	8.07	8.67	10.25
	4H	7.98	8.56	9.13	9.70	11.28	7.51	8.09	8.65	9.22	10.81
	6H	8.37	8.91	9.53	10.04	11.64	7.89	8.43	9.05	9.57	11.16
	8H	8.47	8.98	9.63	10.13	11.72	7.99	8.51	9.15	9.66	11.24
	12H	8.51	9.00	9.67	10.14	11.75	8.03	8.52	9.19	9.66	11.27
4H	2H	6.19	6.78	7.35	7.91	9.49	5.85	6.43	7.00	7.57	9.15
	3H	8.04	8.53	9.20	9.69	11.28	7.65	8.14	8.81	9.30	10.89
	4H	8.75	9.20	9.91	10.35	11.96	8.34	8.79	9.51	9.94	11.56
	6H	9.25	9.64	10.42	10.81	12.41	8.85	9.23	10.01	10.40	12.00
	8H	9.40	9.76	10.57	10.92	12.54	8.99	9.35	10.16	10.51	12.13
	12H	9.47	9.79	10.65	10.96	12.59	9.04	9.37	10.23	10.54	12.17
8H	4H	8.93	9.29	10.10	10.45	12.07	8.57	8.93	9.74	10.09	11.71
	6H	9.56	9.85	10.74	11.06	12.67	9.19	9.49	10.38	10.69	12.31
	8H	9.78	10.03	10.97	11.21	12.85	9.41	9.67	10.60	10.85	12.48
	12H	9.90	10.13	11.10	11.30	12.98	9.51	9.74	10.71	10.92	12.59
12H	4H	8.91	9.24	10.09	10.41	12.03	8.56	8.88	9.74	10.06	11.68
	6H	9.58	9.84	10.78	11.02	12.66	9.23	9.49	10.43	10.67	12.31
	8H	9.82	10.05	11.02	11.22	12.89	9.46	9.69	10.66	10.87	12.54