

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915775

Luminaire Tested: DFN2DIP-TR4F0-120D120US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915775
REPORT IS A COMBINATION OF REPORTS P902049 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D120US927-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18822.2 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 217
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2939	2939	2939
5°	2943	2898	2917
10°	2919	2859	2877
15°	2877	2811	2816
20°	2819	2746	2752
25°	2761	2668	2679
30°	2689	2595	2586
35°	2620	2509	2488
40°	2536	2422	2394
45°	2452	2336	2299
50°	2360	2244	2188
55°	2263	2139	2086
60°	2155	2013	1969
65°	2036	1884	1831
70°	1885	1726	1683
75°	1676	1536	1546
80°	1424	1295	1284
85°	1030	879	851

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2452 cd/sqm

TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.1	1.8
10°-20°	979.5	5.2
20°-30°	1439.5	7.6
30°-40°	1671.9	8.9
40°-50°	1669.9	8.9
50°-60°	1456.0	7.7
60°-70°	1076.3	5.7
70°-80°	609.0	3.2
80°-90°	166.4	0.9
90°-100°	105.8	0.6
100°-110°	394.4	2.1
110°-120°	1045.9	5.6
120°-130°	1734.7	9.2
130°-140°	1842.7	9.8
140°-150°	1712.6	9.1
150°-160°	1376.9	7.3
160°-170°	887.2	4.7
170°-180°	305.4	1.6
0°-30°	2767.2	14.7
0°-40°	4439.1	23.6
0°-60°	7565.0	40.2
0°-90°	9416.7	50.0
90°-120°	1546.1	8.2
90°-150°	6836.0	36.3
90°-180°	9405.0	50.0
0°-180°	18822.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3699	3699	3699	3699	3699	
5°	3699	3685	3646	3674	3667	351
15°	3521	3500	3454	3468	3450	992
25°	3187	3158	3098	3105	3098	1466
35°	2749	2714	2657	2636	2618	1717
45°	2237	2212	2159	2120	2106	1727
55°	1693	1672	1629	1586	1569	1514
65°	1142	1120	1085	1053	1035	1129
75°	597	591	572	551	558	638
85°	146	142	139	128	124	162
90°	2	28	46	58	63	17
95°	151	74	90	102	100	179
105°	706	776	142	167	176	754
115°	1335	1374	1432	358	190	1314
125°	1887	1918	1962	1978	1985	1683
135°	2335	2373	2393	2417	2412	1804
145°	2709	2707	2746	2762	2751	1694
155°	2983	2962	2990	3004	2986	1375
165°	3143	3129	3136	3153	3136	888
175°	3215	3199	3204	3220	3197	306
180°	3208	3208	3208	3208	3208	

TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3698.9	3698.9	3698.9	3698.9	3698.9
2.5°	3720.4	3702.7	3663.4	3698.9	3692.1
5°	3698.9	3684.9	3645.7	3674.0	3667.2
7.5°	3674.0	3652.8	3613.6	3642.3	3635.2
10°	3635.2	3610.2	3567.6	3595.9	3585.3
12.5°	3581.5	3560.4	3517.8	3535.5	3528.3
15°	3521.2	3500.0	3453.6	3467.9	3450.2
17.5°	3446.5	3425.3	3378.9	3396.6	3378.9
20°	3364.6	3343.4	3293.7	3304.2	3290.2
22.5°	3283.0	3251.0	3204.5	3204.5	3197.4
25°	3186.8	3158.5	3098.1	3105.0	3098.1
27.5°	3080.0	3055.1	3009.1	2998.5	2980.8
30°	2973.6	2944.9	2891.7	2881.2	2866.8
32.5°	2859.6	2838.5	2781.5	2760.0	2745.7
35°	2749.4	2714.0	2657.0	2635.5	2617.8
37.5°	2624.9	2592.9	2535.9	2511.0	2493.2
40°	2497.0	2468.4	2411.3	2379.6	2365.3
42.5°	2372.5	2343.8	2287.2	2251.4	2230.2
45°	2237.4	2212.5	2158.9	2120.0	2105.7
47.5°	2105.7	2080.7	2023.8	1984.6	1963.4
50°	1966.8	1949.1	1899.3	1849.4	1831.7
52.5°	1831.7	1806.8	1760.8	1721.5	1696.6
55°	1693.2	1671.7	1629.0	1586.4	1568.7
57.5°	1554.3	1536.6	1490.2	1447.6	1433.2
60°	1415.5	1401.5	1351.7	1312.5	1301.9
62.5°	1280.4	1255.4	1220.0	1184.5	1170.2
65°	1141.9	1120.4	1084.9	1052.8	1035.1
67.5°	999.7	981.5	949.8	925.0	910.6
70°	867.9	853.6	821.5	796.6	782.7
72.5°	732.8	718.5	700.8	675.9	665.3
75°	597.4	590.6	572.4	551.4	558.5
77.5°	476.6	462.2	455.1	444.5	434.0
80°	355.8	352.0	344.9	334.4	327.2
82.5°	241.9	241.9	238.5	224.2	224.2
85°	145.7	142.3	138.9	127.9	124.5
87.5°	64.2	57.0	49.8	39.2	35.5
90°	2.2	27.8	46.3	58.1	62.6
92.5°	58.1	48.8	55.7	60.4	62.6
95°	150.8	74.1	90.4	102.3	99.8
97.5°	271.6	81.4	118.3	125.4	127.6
100°	411.0	92.9	132.3	150.8	155.5
102.5°	564.0	559.6	137.0	162.4	169.5
105°	705.7	775.5	141.7	167.1	176.4
107.5°	870.5	928.4	146.4	171.7	181.1
110°	1028.5	1077.0	406.3	174.2	183.3

TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1177.1	1218.7	1179.3	178.6	185.8
115°	1334.7	1374.2	1432.3	357.5	190.5
117.5°	1471.8	1518.1	1557.8	1225.6	617.5
120°	1625.1	1659.8	1701.7	1729.6	1416.1
122.5°	1754.9	1792.2	1838.7	1852.5	1855.0
125°	1887.2	1917.6	1961.7	1977.9	1984.8
127.5°	2007.9	2040.5	2075.5	2098.6	2100.9
130°	2121.8	2159.0	2184.4	2210.0	2207.8
132.5°	2237.8	2268.2	2293.5	2314.5	2312.3
135°	2335.4	2372.7	2393.3	2416.8	2412.1
137.5°	2437.5	2465.3	2488.7	2511.8	2505.0
140°	2537.3	2556.0	2581.3	2602.3	2590.7
142.5°	2621.0	2637.3	2667.4	2685.8	2674.2
145°	2709.3	2706.8	2746.2	2762.5	2750.8
147.5°	2785.6	2778.7	2818.2	2829.8	2820.6
150°	2860.0	2843.8	2881.0	2894.8	2883.2
152.5°	2922.6	2904.1	2938.9	2952.9	2936.7
155°	2983.0	2962.3	2990.2	3004.0	2985.5
157.5°	3031.8	3013.3	3034.3	3050.5	3031.8
160°	3073.7	3059.6	3073.7	3087.4	3071.2
162.5°	3110.7	3096.9	3108.4	3124.7	3103.8
165°	3143.1	3129.4	3136.2	3152.6	3136.2
167.5°	3168.8	3154.7	3161.9	3178.2	3157.2
170°	3189.7	3175.7	3180.4	3196.6	3175.7
172.5°	3203.5	3189.7	3194.5	3210.7	3189.7
175°	3215.1	3198.8	3203.5	3219.8	3196.6
177.5°	3219.8	3203.5	3206.0	3222.3	3201.4
180°	3208.3	3208.3	3208.3	3208.3	3208.3

TEST NUMBER: P915775

CATALOG NUMBER: DFN2DIP-TR4F0-120D120US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.01	11.88	11.97	12.85	14.12	10.58	11.44	11.54	12.42	13.69
	3H	12.67	13.45	13.64	14.43	15.72	12.20	12.98	13.17	13.96	15.25
	4H	13.26	13.99	14.24	14.98	16.28	12.79	13.52	13.77	14.51	15.81
	6H	13.66	14.34	14.65	15.33	16.64	13.19	13.86	14.18	14.85	16.17
	8H	13.77	14.41	14.77	15.42	16.73	13.29	13.93	14.29	14.94	16.25
	12H	13.81	14.43	14.82	15.43	16.76	13.33	13.95	14.34	14.95	16.28
4H	2H	11.48	12.21	12.46	13.19	14.49	11.13	11.86	12.12	12.85	14.15
	3H	13.34	13.95	14.34	14.97	16.28	12.95	13.56	13.95	14.57	15.89
	4H	14.06	14.61	15.06	15.62	16.96	13.65	14.21	14.66	15.22	16.56
	6H	14.57	15.05	15.59	16.08	17.42	14.16	14.64	15.18	15.67	17.01
	8H	14.72	15.17	15.74	16.19	17.54	14.31	14.76	15.33	15.78	17.13
	12H	14.79	15.20	15.83	16.24	17.60	14.37	14.78	15.41	15.82	17.17
8H	4H	14.25	14.70	15.27	15.73	17.08	13.89	14.34	14.91	15.37	16.72
	6H	14.88	15.26	15.93	16.32	17.67	14.52	14.89	15.56	15.96	17.31
	8H	15.11	15.43	16.16	16.48	17.85	14.74	15.06	15.79	16.11	17.48
	12H	15.24	15.52	16.29	16.57	17.98	14.85	15.14	15.91	16.19	17.60
12H	4H	14.24	14.64	15.28	15.68	17.04	13.89	14.29	14.92	15.33	16.69
	6H	14.91	15.24	15.96	16.29	17.66	14.56	14.89	15.61	15.94	17.31
	8H	15.16	15.44	16.21	16.49	17.90	14.80	15.09	15.85	16.13	17.54

END OF REPORT