

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912760

Luminaire Tested: DFN2DIP-TR4F0-040D120US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912760
REPORT IS A COMBINATION OF REPORTS P900514 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D120US850-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15548.1 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		90	90	90	90		69	69	69		50	50	50		33	33	33
1	92	88	85	81		82	79	76	73		61	59	57		44	43	42		29	28	28
2	84	77	71	67		75	69	64	60		53	50	47		39	37	35		26	25	24
3	77	68	61	56		68	61	55	50		47	43	40		35	32	30		23	22	20
4	70	60	53	47		62	54	48	43		42	38	34		31	28	26		21	19	18
5	64	54	46	40		57	48	42	37		38	33	29		28	25	22		19	17	16
6	59	48	40	35		53	43	37	32		34	29	26		25	22	20		17	15	14
7	55	43	36	30		49	39	32	28		31	26	23		23	20	17		16	14	12
8	51	39	32	27		45	35	29	24		28	23	20		21	18	16		14	12	11
9	47	36	29	24		42	32	26	22		25	21	18		19	16	14		13	11	10
10	44	33	26	21		39	29	23	19		23	19	16		18	15	13		12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1457	1457	1457
5°	1459	1433	1443
10°	1444	1405	1396
15°	1425	1359	1323
20°	1398	1295	1234
25°	1371	1223	1148
30°	1335	1149	1039
35°	1300	1070	943
40°	1264	988	833
45°	1222	897	733
50°	1178	806	636
55°	1133	708	543
60°	1081	605	447
65°	1021	501	402
70°	948	404	364
75°	856	356	331
80°	723	299	287
85°	504	199	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3280 cd/sqm

TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	1.1
10°-20°	471.7	3.0
20°-30°	662.3	4.3
30°-40°	721.9	4.6
40°-50°	663.5	4.3
50°-60°	521.1	3.4
60°-70°	339.2	2.2
70°-80°	174.6	1.1
80°-90°	56.5	0.4
90°-100°	260.4	1.7
100°-110°	827.5	5.3
110°-120°	1416.1	9.1
120°-130°	1862.4	12.0
130°-140°	2090.5	13.4
140°-150°	2050.0	13.2
150°-160°	1719.6	11.1
160°-170°	1140.4	7.3
170°-180°	398.6	2.6
0°-30°	1305.8	8.4
0°-40°	2027.7	13.0
0°-60°	3212.2	20.7
0°-90°	3782.5	24.3
90°-120°	2504.0	16.1
90°-150°	8506.9	54.7
90°-180°	11766.0	75.7
0°-180°	15548.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	4	46	124	117	120	15
95°	185	221	227	227	221	206
105°	764	774	782	788	788	806
115°	1421	1442	1435	1431	1421	1406
125°	2067	2099	2089	2077	2073	1847
135°	2674	2713	2720	2717	2706	2066
145°	3246	3271	3291	3295	3281	2028
155°	3711	3722	3733	3751	3739	1708
165°	4038	4034	4034	4059	4041	1139
175°	4201	4191	4184	4209	4187	399
180°	4209	4209	4209	4209	4209	

TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	3.8	45.7	124.3	116.8	120.5
92.5°	78.6	106.6	110.3	114.2	114.2
95°	185.2	220.8	227.1	227.1	220.8
97.5°	308.3	341.4	355.3	355.3	355.3
100°	450.5	479.6	489.7	489.7	486.0
102.5°	600.2	621.7	635.7	639.6	635.7
105°	763.9	774.0	781.6	787.9	787.9
107.5°	926.2	941.5	941.5	944.0	926.2
110°	1083.6	1103.9	1103.9	1103.9	1093.8

TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1253.6	1275.2	1271.4	1261.3	1253.6
115°	1421.1	1441.5	1435.0	1431.3	1421.1
117.5°	1587.3	1615.3	1597.5	1587.3	1577.2
120°	1754.9	1782.7	1754.9	1754.9	1743.5
122.5°	1907.1	1942.6	1924.9	1914.7	1907.1
125°	2067.0	2098.7	2088.6	2077.2	2073.3
127.5°	2223.1	2262.4	2248.4	2233.2	2223.1
130°	2368.9	2414.6	2408.3	2400.7	2386.7
132.5°	2532.6	2568.2	2570.7	2552.9	2542.8
135°	2673.5	2712.8	2720.5	2716.6	2706.5
137.5°	2830.8	2862.6	2868.9	2866.3	2851.1
140°	2969.1	3000.8	3018.6	3018.6	3004.6
142.5°	3111.3	3143.0	3153.1	3156.9	3143.0
145°	3245.7	3271.1	3291.4	3295.3	3281.3
147.5°	3366.3	3398.0	3413.3	3419.6	3405.6
150°	3490.7	3512.2	3526.2	3537.6	3526.2
152.5°	3601.0	3622.5	3640.4	3654.4	3640.4
155°	3711.4	3721.6	3733.0	3750.7	3739.3
157.5°	3806.6	3814.2	3820.5	3845.9	3828.2
160°	3891.6	3899.2	3903.0	3924.6	3909.3
162.5°	3970.2	3970.2	3974.1	3998.2	3980.4
165°	4037.5	4033.8	4033.8	4059.1	4041.3
167.5°	4098.4	4087.0	4087.0	4112.4	4094.6
170°	4144.1	4133.9	4130.1	4155.5	4133.9
172.5°	4175.8	4165.6	4161.9	4187.3	4165.6
175°	4201.2	4191.0	4183.5	4208.8	4187.3
177.5°	4215.2	4205.0	4197.3	4219.0	4197.3
180°	4208.8	4208.8	4208.8	4208.8	4208.8

TEST NUMBER: P912760

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.36	6.02	6.52	7.16	8.76	1.34	1.99	2.49	3.13	4.73
	3H	7.03	7.61	8.19	8.76	10.37	2.51	3.10	3.67	4.25	5.86
	4H	7.63	8.19	8.80	9.33	10.95	2.96	3.51	4.13	4.66	6.28
	6H	8.04	8.55	9.22	9.70	11.33	3.27	3.78	4.45	4.93	6.56
	8H	8.16	8.65	9.34	9.81	11.43	3.35	3.84	4.53	5.01	6.63
	12H	8.22	8.68	9.40	9.84	11.48	3.39	3.86	4.58	5.01	6.66
4H	2H	5.36	5.92	6.54	7.07	8.68	1.91	2.47	3.09	3.62	5.23
	3H	7.17	7.64	8.36	8.81	10.44	3.25	3.71	4.43	4.88	6.51
	4H	7.86	8.29	9.04	9.45	11.09	3.79	4.22	4.97	5.38	7.02
	6H	8.36	8.73	9.55	9.91	11.55	4.20	4.56	5.39	5.75	7.38
	8H	8.54	8.88	9.72	10.05	11.71	4.32	4.67	5.51	5.84	7.49
	12H	8.62	8.93	9.83	10.12	11.78	4.38	4.69	5.58	5.88	7.54
8H	4H	7.81	8.15	9.00	9.33	10.98	4.05	4.40	5.24	5.57	7.22
	6H	8.37	8.65	9.58	9.87	11.52	4.57	4.85	5.77	6.07	7.72
	8H	8.59	8.83	9.80	10.03	11.70	4.76	5.00	5.97	6.20	7.87
	12H	8.72	8.94	9.93	10.13	11.83	4.87	5.09	6.08	6.28	7.98
12H	4H	7.76	8.07	8.96	9.25	10.91	4.05	4.36	5.25	5.55	7.21
	6H	8.35	8.59	9.56	9.79	11.46	4.62	4.86	5.83	6.06	7.73
	8H	8.56	8.78	9.78	9.97	11.67	4.82	5.03	6.03	6.23	7.93

END OF REPORT