

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912761

Luminaire Tested: DFN2DIP-TR4F0-040D120US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912761
REPORT IS A COMBINATION OF REPORTS P902034 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D120US850-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16945.5 lumens
Efficiency: N/A
Efficacy: 137.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		89	89	89	89		68	68	68		49	49	49		31	31	31
1	92	88	84	81		81	78	75	72		60	58	56		43	42	41		27	27	26
2	84	77	71	66		74	68	64	60		52	49	47		38	36	34		24	23	22
3	76	68	61	55		68	60	55	50		46	43	39		34	31	29		22	20	19
4	70	60	52	47		62	53	47	42		41	37	34		30	27	25		20	18	17
5	64	53	46	40		57	48	41	36		37	32	29		27	24	22		18	16	15
6	59	48	40	35		52	43	36	31		33	29	25		24	21	19		16	14	13
7	54	43	35	30		48	38	32	27		30	25	22		22	19	17		15	13	12
8	50	39	32	27		45	35	29	24		27	23	20		20	17	15		14	12	10
9	47	35	28	23		42	32	26	21		25	20	17		19	16	13		12	11	9
10	44	32	25	21		39	29	23	19		23	19	16		17	14	12		12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1457	1457	1457
5°	1459	1433	1443
10°	1444	1405	1396
15°	1425	1359	1323
20°	1398	1295	1234
25°	1371	1223	1148
30°	1335	1149	1039
35°	1300	1070	943
40°	1264	988	833
45°	1222	897	733
50°	1178	806	636
55°	1133	708	543
60°	1081	605	447
65°	1021	501	402
70°	948	404	364
75°	856	356	331
80°	723	299	287
85°	504	199	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2384 cd/sqm

TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	1.0
10°-20°	471.7	2.8
20°-30°	662.3	3.9
30°-40°	721.9	4.3
40°-50°	663.5	3.9
50°-60°	521.1	3.1
60°-70°	339.2	2.0
70°-80°	174.6	1.0
80°-90°	52.5	0.3
90°-100°	148.1	0.9
100°-110°	552.1	3.3
110°-120°	1464.2	8.6
120°-130°	2428.5	14.3
130°-140°	2579.6	15.2
140°-150°	2397.5	14.1
150°-160°	1927.5	11.4
160°-170°	1242.0	7.3
170°-180°	427.5	2.5
0°-30°	1305.8	7.7
0°-40°	2027.7	12.0
0°-60°	3212.2	19.0
0°-90°	3778.5	22.3
90°-120°	2164.4	12.8
90°-150°	9570.0	56.5
90°-180°	13167.0	77.7
0°-180°	16945.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	3	39	65	81	88	16
95°	211	104	126	143	140	250
105°	988	1086	198	234	247	1056
115°	1869	1924	2005	500	267	1840
125°	2642	2684	2746	2769	2779	2356
135°	3269	3322	3350	3383	3377	2526
145°	3793	3789	3844	3867	3851	2372
155°	4176	4147	4186	4205	4180	1924
165°	4400	4381	4390	4413	4390	1243
175°	4501	4478	4485	4508	4475	428
180°	4491	4491	4491	4491	4491	

TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	3.1	38.9	64.9	81.4	87.6
92.5°	81.4	68.3	78.0	84.5	87.6
95°	211.0	103.8	126.5	143.2	139.7
97.5°	380.2	113.9	165.6	175.6	178.7
100°	575.3	130.1	185.2	211.0	217.7
102.5°	789.6	783.4	191.7	227.3	237.3
105°	987.9	1085.6	198.4	233.9	247.0
107.5°	1218.7	1299.7	204.9	240.4	253.5
110°	1439.8	1507.8	568.8	243.9	256.6

TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1647.9	1706.1	1651.0	250.1	260.1
115°	1868.6	1923.8	2005.2	500.5	266.7
117.5°	2060.4	2125.3	2180.8	1715.7	864.5
120°	2275.0	2323.6	2382.2	2421.3	1982.4
122.5°	2456.8	2508.9	2574.1	2593.4	2596.8
125°	2642.0	2684.4	2746.2	2769.0	2778.6
127.5°	2811.0	2856.6	2905.6	2938.0	2941.1
130°	2970.3	3022.5	3058.0	3093.9	3090.8
132.5°	3132.8	3175.3	3210.8	3240.2	3237.1
135°	3269.4	3321.6	3350.5	3383.3	3376.8
137.5°	3412.3	3451.2	3484.0	3516.4	3506.8
140°	3552.0	3578.2	3613.7	3643.1	3626.9
142.5°	3669.2	3692.1	3734.1	3760.0	3743.8
145°	3792.8	3789.3	3844.5	3867.3	3851.0
147.5°	3899.7	3890.0	3945.3	3961.5	3948.7
150°	4003.8	3981.1	4033.2	4052.5	4036.3
152.5°	4091.4	4065.6	4114.3	4133.9	4111.2
155°	4175.9	4147.0	4186.0	4205.3	4179.5
157.5°	4244.3	4218.4	4247.8	4270.5	4244.3
160°	4302.9	4283.3	4302.9	4322.2	4299.5
162.5°	4354.7	4335.4	4351.6	4374.3	4345.1
165°	4400.2	4380.9	4390.5	4413.4	4390.5
167.5°	4436.1	4416.4	4426.5	4449.2	4419.9
170°	4465.4	4445.8	4452.3	4475.0	4445.8
172.5°	4484.7	4465.4	4472.0	4494.8	4465.4
175°	4500.9	4478.1	4484.7	4507.5	4475.0
177.5°	4507.5	4484.7	4488.2	4511.0	4481.7
180°	4491.3	4491.3	4491.3	4491.3	4491.3

TEST NUMBER: P912761

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.02	5.67	6.19	6.82	8.44	1.00	1.64	2.16	2.79	4.41
	3H	6.69	7.26	7.86	8.42	10.06	2.17	2.75	3.35	3.91	5.54
	4H	7.29	7.83	8.47	8.99	10.63	2.61	3.16	3.80	4.32	5.96
	6H	7.70	8.20	8.89	9.36	11.01	2.93	3.43	4.12	4.59	6.24
	8H	7.82	8.30	9.01	9.47	11.11	3.01	3.49	4.20	4.67	6.31
	12H	7.87	8.33	9.07	9.50	11.16	3.05	3.50	4.25	4.67	6.34
4H	2H	5.02	5.57	6.21	6.72	8.36	1.57	2.12	2.76	3.27	4.91
	3H	6.83	7.29	8.02	8.47	10.12	2.90	3.36	4.10	4.54	6.19
	4H	7.52	7.94	8.71	9.11	10.78	3.44	3.87	4.64	5.04	6.71
	6H	8.02	8.38	9.22	9.57	11.23	3.85	4.21	5.05	5.41	7.07
	8H	8.19	8.53	9.39	9.71	11.39	3.98	4.32	5.18	5.50	7.18
	12H	8.28	8.58	9.49	9.78	11.46	4.04	4.34	5.25	5.54	7.22
8H	4H	7.47	7.80	8.67	8.99	10.66	3.71	4.05	4.91	5.23	6.91
	6H	8.03	8.31	9.25	9.53	11.20	4.22	4.50	5.44	5.73	7.40
	8H	8.24	8.48	9.47	9.69	11.38	4.41	4.65	5.64	5.86	7.55
	12H	8.38	8.59	9.60	9.79	11.51	4.53	4.74	5.75	5.94	7.66
12H	4H	7.41	7.72	8.63	8.91	10.59	3.71	4.01	4.92	5.21	6.89
	6H	8.00	8.24	9.22	9.45	11.14	4.27	4.51	5.49	5.72	7.41
	8H	8.22	8.43	9.44	9.63	11.35	4.47	4.69	5.70	5.89	7.61

END OF REPORT