

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918199

Luminaire Tested: DFN2DIP-TR4F0-040D080US930-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P918199  
REPORT IS A COMBINATION OF REPORTS P901961 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-040D080US930-FLLONL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9685.8 lumens  
Efficiency: N/A  
Efficacy: 106.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 91.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918199  
CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P918199

CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29	24				24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20				20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17				17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15				15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12				12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1008	1008	1008
5°	1010	994	1001
10°	1002	981	987
15°	987	964	966
20°	967	942	944
25°	947	915	919
30°	922	890	887
35°	899	861	854
40°	870	831	821
45°	841	801	789
50°	809	770	751
55°	777	734	716
60°	739	691	675
65°	699	646	628
70°	647	592	577
75°	575	527	530
80°	489	444	441
85°	354	301	292

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1170 cd/sqm



TEST NUMBER: P918199

CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.4	1.2
10°-20°	336.0	3.5
20°-30°	493.8	5.1
30°-40°	573.6	5.9
40°-50°	572.9	5.9
50°-60°	499.5	5.2
60°-70°	369.3	3.8
70°-80°	208.9	2.2
80°-90°	59.0	0.6
90°-100°	72.6	0.7
100°-110°	270.6	2.8
110°-120°	717.6	7.4
120°-130°	1190.2	12.3
130°-140°	1264.3	13.1
140°-150°	1175.0	12.1
150°-160°	944.7	9.8
160°-170°	608.7	6.3
170°-180°	209.5	2.2
0°-30°	949.3	9.8
0°-40°	1522.9	15.7
0°-60°	2595.3	26.8
0°-90°	3232.5	33.4
90°-120°	1060.8	11.0
90°-150°	4690.4	48.4
90°-180°	6453.0	66.6
0°-180°	9685.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	2	19	32	40	43	9
95°	104	51	62	70	68	123
105°	484	532	97	115	121	517
115°	916	943	983	245	131	902
125°	1295	1316	1346	1357	1362	1155
135°	1602	1628	1642	1658	1655	1238
145°	1859	1857	1884	1895	1887	1163
155°	2047	2032	2052	2061	2048	943
165°	2157	2147	2152	2163	2152	609
175°	2206	2195	2198	2209	2193	210
180°	2201	2201	2201	2201	2201	



TEST NUMBER: P918199

CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.5	50.9	62.0	70.2	68.5
97.5°	186.3	55.8	81.1	86.1	87.6
100°	282.0	63.8	90.8	103.5	106.6
102.5°	387.0	383.9	94.0	111.4	116.3
105°	484.2	532.1	97.2	114.6	121.1
107.5°	597.3	637.0	100.4	117.8	124.3
110°	705.7	739.0	278.8	119.5	125.8



TEST NUMBER: P918199

CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	807.6	836.2	809.2	122.5	127.5
115°	915.8	942.9	982.8	245.3	130.7
117.5°	1009.8	1041.6	1068.9	840.9	423.7
120°	1115.0	1138.8	1167.6	1186.7	971.6
122.5°	1204.0	1229.6	1261.6	1271.0	1272.8
125°	1294.9	1315.6	1345.9	1357.1	1361.8
127.5°	1377.7	1400.0	1424.1	1439.9	1441.4
130°	1455.8	1481.3	1498.8	1516.4	1514.8
132.5°	1535.5	1556.2	1573.7	1588.0	1586.5
135°	1602.4	1627.9	1642.1	1658.2	1655.0
137.5°	1672.4	1691.5	1707.6	1723.5	1718.7
140°	1740.8	1753.7	1771.2	1785.5	1777.5
142.5°	1798.4	1809.5	1830.1	1842.8	1834.8
145°	1858.9	1857.2	1884.2	1895.4	1887.4
147.5°	1911.3	1906.6	1933.6	1941.6	1935.3
150°	1962.3	1951.2	1976.7	1986.1	1978.2
152.5°	2005.3	1992.6	2016.4	2026.1	2014.9
155°	2046.7	2032.5	2051.6	2061.1	2048.4
157.5°	2080.2	2067.5	2081.9	2093.0	2080.2
160°	2108.9	2099.3	2108.9	2118.4	2107.2
162.5°	2134.3	2124.8	2132.7	2143.9	2129.6
165°	2156.6	2147.2	2151.9	2163.0	2151.9
167.5°	2174.2	2164.5	2169.4	2180.6	2166.2
170°	2188.6	2178.9	2182.1	2193.3	2178.9
172.5°	2198.0	2188.6	2191.8	2202.9	2188.6
175°	2206.0	2194.8	2198.0	2209.1	2193.3
177.5°	2209.1	2198.0	2199.7	2210.8	2196.5
180°	2201.2	2201.2	2201.2	2201.2	2201.2



TEST NUMBER: P918199  
 CATALOG NUMBER: DFN2DIP-TR4F0-040D080US930-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.52	6.25	6.61	7.34	8.83	5.09	5.82	6.18	6.91	8.40
	3H	7.17	7.83	8.27	8.92	10.43	6.70	7.35	7.80	8.45	9.96
	4H	7.75	8.37	8.86	9.47	10.98	7.28	7.90	8.39	9.00	10.51
	6H	8.15	8.72	9.26	9.82	11.34	7.67	8.24	8.79	9.34	10.87
	8H	8.25	8.79	9.37	9.91	11.42	7.77	8.32	8.89	9.43	10.95
	12H	8.29	8.81	9.41	9.92	11.46	7.81	8.33	8.93	9.43	10.98
4H	2H	5.97	6.59	7.08	7.68	9.20	5.62	6.24	6.74	7.34	8.85
	3H	7.82	8.34	8.94	9.46	10.99	7.43	7.95	8.55	9.07	10.60
	4H	8.53	9.01	9.65	10.12	11.66	8.12	8.60	9.25	9.71	11.26
	6H	9.04	9.44	10.17	10.58	12.12	8.63	9.04	9.76	10.17	11.71
	8H	9.18	9.56	10.31	10.69	12.25	8.77	9.15	9.90	10.28	11.83
	12H	9.25	9.60	10.40	10.73	12.29	8.83	9.17	9.98	10.31	11.87
8H	4H	8.72	9.10	9.85	10.22	11.78	8.36	8.74	9.49	9.86	11.42
	6H	9.34	9.66	10.49	10.83	12.38	8.98	9.29	10.13	10.46	12.01
	8H	9.56	9.84	10.72	10.98	12.56	9.19	9.47	10.35	10.62	12.19
	12H	9.69	9.93	10.85	11.07	12.68	9.30	9.54	10.46	10.69	12.30
12H	4H	8.70	9.04	9.84	10.18	11.74	8.34	8.69	9.49	9.83	11.39
	6H	9.37	9.65	10.53	10.79	12.37	9.02	9.29	10.18	10.44	12.01
	8H	9.61	9.85	10.77	10.99	12.60	9.25	9.49	10.41	10.64	12.24