

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918296

Luminaire Tested: DFN2DIP-TR4F0-070D050US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918296
REPORT IS A COMBINATION OF REPORTS P900394 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D050US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8458.7 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918296
CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918296
 CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57			57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49			49
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42			42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36			36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32			32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28			28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25			25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22			22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20			20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18			18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1874	1874	1874
5°	1877	1844	1856
10°	1858	1808	1795
15°	1833	1748	1702
20°	1799	1666	1587
25°	1764	1573	1477
30°	1718	1479	1336
35°	1672	1377	1213
40°	1626	1272	1072
45°	1572	1155	944
50°	1516	1037	819
55°	1458	911	698
60°	1391	779	575
65°	1313	645	517
70°	1219	520	468
75°	1101	458	426
80°	931	384	369
85°	648	256	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1572 cd/sqm



TEST NUMBER: P918296

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.6
10°-20°	606.9	7.2
20°-30°	852.0	10.1
30°-40°	928.8	11.0
40°-50°	853.6	10.1
50°-60°	670.4	7.9
60°-70°	436.4	5.2
70°-80°	224.6	2.7
80°-90°	61.0	0.7
90°-100°	79.8	0.9
100°-110°	253.5	3.0
110°-120°	433.8	5.1
120°-130°	570.5	6.7
130°-140°	640.4	7.6
140°-150°	627.9	7.4
150°-160°	526.8	6.2
160°-170°	349.3	4.1
170°-180°	122.1	1.4
0°-30°	1679.9	19.9
0°-40°	2608.7	30.8
0°-60°	4132.7	48.9
0°-90°	4854.7	57.4
90°-120°	767.0	9.1
90°-150°	2605.8	30.8
90°-180°	3604.0	42.6
0°-180°	8458.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	14	38	36	37	8
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	



TEST NUMBER: P918296

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0



TEST NUMBER: P918296

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2



TEST NUMBER: P918296
 CATALOG NUMBER: DFN2DIP-TR4F0-070D050US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.99	10.88	10.88	11.79	12.96	5.96	6.85	6.86	7.77	8.93
	3H	11.67	12.47	12.58	13.39	14.58	7.15	7.95	8.06	8.88	10.07
	4H	12.28	13.04	13.21	13.96	15.16	7.61	8.36	8.53	9.29	10.49
	6H	12.70	13.40	13.64	14.33	15.55	7.93	8.63	8.87	9.56	10.77
	8H	12.83	13.49	13.78	14.44	15.65	8.03	8.69	8.97	9.64	10.85
	12H	12.90	13.53	13.85	14.47	15.70	8.07	8.70	9.02	9.65	10.88
4H	2H	10.01	10.77	10.94	11.70	12.89	6.56	7.32	7.49	8.25	9.45
	3H	11.85	12.47	12.79	13.43	14.65	7.92	8.55	8.86	9.51	10.72
	4H	12.54	13.11	13.49	14.07	15.31	8.47	9.04	9.42	10.00	11.23
	6H	13.06	13.55	14.02	14.53	15.77	8.89	9.39	9.86	10.36	11.60
	8H	13.24	13.70	14.20	14.67	15.92	9.03	9.48	9.99	10.46	11.71
	12H	13.33	13.75	14.32	14.74	15.99	9.09	9.51	10.08	10.50	11.75
8H	4H	12.51	12.97	13.48	13.94	15.20	8.76	9.22	9.72	10.19	11.44
	6H	13.08	13.46	14.07	14.47	15.72	9.28	9.66	10.27	10.67	11.92
	8H	13.30	13.63	14.30	14.64	15.90	9.47	9.80	10.47	10.81	12.07
	12H	13.44	13.74	14.44	14.73	16.05	9.59	9.89	10.59	10.88	12.20
12H	4H	12.47	12.88	13.45	13.87	15.13	8.76	9.18	9.75	10.16	11.42
	6H	13.06	13.39	14.06	14.39	15.66	9.33	9.66	10.33	10.66	11.93
	8H	13.28	13.58	14.28	14.57	15.89	9.54	9.84	10.54	10.83	12.15