

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918348

Luminaire Tested: DFN2DIP-TR4F0-080D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918348
REPORT IS A COMBINATION OF REPORTS P900468 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-080D090US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12037.8 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 142.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918348
CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918348
 CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45	40			40
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39	34			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29			29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22			22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2142	2142	2142
5°	2145	2108	2121
10°	2124	2066	2052
15°	2095	1998	1945
20°	2056	1904	1814
25°	2016	1798	1688
30°	1963	1690	1527
35°	1911	1574	1386
40°	1858	1453	1225
45°	1796	1320	1079
50°	1733	1185	935
55°	1666	1041	798
60°	1589	890	657
65°	1501	737	591
70°	1393	594	535
75°	1259	524	487
80°	1064	439	422
85°	741	293	316

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1807 cd/sqm



TEST NUMBER: P918348

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	2.1
10°-20°	693.6	5.8
20°-30°	973.7	8.1
30°-40°	1061.4	8.8
40°-50°	975.6	8.1
50°-60°	766.2	6.4
60°-70°	498.7	4.1
70°-80°	256.7	2.1
80°-90°	72.1	0.6
90°-100°	143.6	1.2
100°-110°	456.3	3.8
110°-120°	780.8	6.5
120°-130°	1026.9	8.5
130°-140°	1152.6	9.6
140°-150°	1130.3	9.4
150°-160°	948.2	7.9
160°-170°	628.8	5.2
170°-180°	219.8	1.8
0°-30°	1919.9	15.9
0°-40°	2981.4	24.8
0°-60°	4723.1	39.2
0°-90°	5550.6	46.1
90°-120°	1380.7	11.5
90°-150°	4690.5	39.0
90°-180°	6487.0	53.9
0°-180°	12037.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	2	25	69	64	66	12
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P918348

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1



TEST NUMBER: P918348

CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P918348
 CATALOG NUMBER: DFN2DIP-TR4F0-080D090US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.41	10.21	10.41	11.21	12.54	5.38	6.18	6.38	7.19	8.52
	3H	11.09	11.80	12.09	12.81	14.16	6.57	7.29	7.58	8.30	9.65
	4H	11.69	12.37	12.71	13.38	14.74	7.02	7.70	8.04	8.71	10.07
	6H	12.11	12.74	13.14	13.75	15.12	7.34	7.96	8.37	8.98	10.35
	8H	12.24	12.83	13.27	13.87	15.23	7.43	8.02	8.47	9.06	10.43
	12H	12.30	12.86	13.34	13.89	15.28	7.48	8.04	8.52	9.07	10.46
4H	2H	9.43	10.10	10.45	11.12	12.47	5.98	6.65	7.00	7.67	9.03
	3H	11.25	11.81	12.29	12.86	14.23	7.32	7.89	8.36	8.93	10.30
	4H	11.94	12.46	12.98	13.49	14.89	7.87	8.39	8.91	9.42	10.82
	6H	12.46	12.90	13.51	13.96	15.35	8.29	8.73	9.34	9.79	11.18
	8H	12.63	13.04	13.68	14.09	15.50	8.42	8.83	9.47	9.88	11.29
	12H	12.72	13.10	13.79	14.16	15.57	8.48	8.86	9.55	9.92	11.33
8H	4H	11.91	12.32	12.96	13.37	14.78	8.15	8.56	9.20	9.61	11.02
	6H	12.47	12.81	13.55	13.91	15.31	8.67	9.01	9.74	10.10	11.50
	8H	12.69	12.99	13.77	14.07	15.49	8.86	9.16	9.94	10.24	11.66
	12H	12.83	13.09	13.91	14.16	15.62	8.98	9.24	10.06	10.31	11.78
12H	4H	11.86	12.23	12.93	13.30	14.71	8.15	8.53	9.22	9.59	11.00
	6H	12.45	12.75	13.53	13.83	15.25	8.72	9.02	9.80	10.09	11.51
	8H	12.67	12.93	13.75	14.00	15.46	8.93	9.19	10.01	10.26	11.72