

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913002

Luminaire Tested: DFN2DIP-TR4F0-110D100US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913002
REPORT IS A COMBINATION OF REPORTS P900491 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D100US850-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21891.7 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	91	87		92	88	85	82		76	73	71		64	63	61		54	53	51
2	90	83	76	71		83	77	72	67		66	62	59		56	53	51		47	45	43
3	82	73	65	59		76	68	61	56		58	53	49		50	46	43		42	39	37
4	75	64	56	50		70	60	53	47		52	46	42		45	40	37		38	34	32
5	69	57	49	43		64	54	46	41		47	41	36		40	36	32		34	30	28
6	64	51	43	37		59	48	41	36		42	36	32		36	32	28		31	27	24
7	59	47	38	33		55	44	36	31		38	32	28		33	28	25		28	24	22
8	55	42	34	29		51	40	33	28		35	29	25		30	26	22		26	22	19
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	20	18
10	48	35	28	23		44	33	27	22		29	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3771	3771	3771
5°	3777	3718	3743
10°	3746	3668	3692
15°	3691	3608	3613
20°	3617	3524	3532
25°	3543	3424	3438
30°	3450	3330	3319
35°	3362	3220	3193
40°	3254	3109	3073
45°	3146	2997	2950
50°	3028	2880	2807
55°	2905	2745	2677
60°	2765	2584	2527
65°	2613	2417	2350
70°	2419	2214	2160
75°	2150	1971	1984
80°	1827	1662	1648
85°	1322	1128	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3146 cd/sqm

TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.8	2.0
10°-20°	1257.0	5.7
20°-30°	1847.3	8.4
30°-40°	2145.5	9.8
40°-50°	2142.9	9.8
50°-60°	1868.5	8.5
60°-70°	1381.3	6.3
70°-80°	781.5	3.6
80°-90°	216.2	1.0
90°-100°	217.0	1.0
100°-110°	689.6	3.2
110°-120°	1180.1	5.4
120°-130°	1552.0	7.1
130°-140°	1742.1	8.0
140°-150°	1708.3	7.8
150°-160°	1433.0	6.5
160°-170°	950.4	4.3
170°-180°	332.2	1.5
0°-30°	3551.1	16.2
0°-40°	5696.6	26.0
0°-60°	9708.0	44.3
0°-90°	12087.0	55.2
90°-120°	2086.7	9.5
90°-150°	7089.1	32.4
90°-180°	9805.0	44.8
0°-180°	21891.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4747	4747	4747	4747	4747	
5°	4747	4729	4678	4715	4706	451
15°	4519	4491	4432	4450	4428	1273
25°	4090	4053	3976	3984	3976	1882
35°	3528	3483	3410	3382	3359	2203
45°	2871	2839	2770	2721	2702	2216
55°	2173	2145	2091	2036	2013	1943
65°	1465	1438	1392	1351	1328	1449
75°	766	758	735	708	717	818
85°	187	182	178	164	160	209
90°	3	38	104	97	100	21
95°	154	184	189	189	184	172
105°	637	645	651	657	657	672
115°	1184	1201	1196	1193	1184	1171
125°	1722	1749	1740	1731	1728	1539
135°	2228	2261	2267	2264	2255	1722
145°	2705	2726	2743	2746	2734	1690
155°	3093	3101	3111	3126	3116	1424
165°	3365	3361	3361	3383	3368	949
175°	3501	3493	3486	3507	3489	333
180°	3507	3507	3507	3507	3507	

TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4746.7	4746.7	4746.7	4746.7	4746.7
2.5°	4774.2	4751.5	4701.2	4746.7	4738.0
5°	4746.7	4728.8	4678.4	4714.7	4706.0
7.5°	4714.7	4687.6	4637.3	4674.1	4664.9
10°	4664.9	4632.8	4578.2	4614.4	4600.9
12.5°	4596.1	4569.0	4514.3	4537.0	4527.8
15°	4518.6	4491.4	4431.9	4450.3	4427.6
17.5°	4422.7	4395.6	4336.1	4358.8	4336.1
20°	4317.7	4290.5	4226.6	4240.2	4222.3
22.5°	4213.1	4171.8	4112.3	4112.3	4103.1
25°	4089.5	4053.3	3975.8	3984.5	3975.8
27.5°	3952.5	3920.5	3861.4	3847.9	3825.2
30°	3816.0	3779.1	3710.8	3697.3	3678.9
32.5°	3669.7	3642.6	3569.4	3541.8	3523.4
35°	3528.3	3482.8	3409.6	3382.0	3359.3
37.5°	3368.5	3327.3	3254.2	3222.2	3199.5
40°	3204.3	3167.5	3094.4	3053.7	3035.3
42.5°	3044.5	3007.7	2935.1	2889.1	2862.0
45°	2871.2	2839.2	2770.4	2720.6	2702.2
47.5°	2702.2	2670.3	2597.1	2546.7	2519.5
50°	2524.0	2501.2	2437.2	2373.4	2350.6
52.5°	2350.6	2318.6	2259.6	2209.1	2177.2
55°	2172.9	2145.2	2090.6	2035.8	2013.1
57.5°	1994.6	1971.9	1912.4	1857.6	1839.2
60°	1816.4	1798.6	1734.6	1684.2	1670.7
62.5°	1643.1	1611.2	1565.6	1520.1	1501.7
65°	1465.3	1437.7	1392.2	1351.1	1328.4
67.5°	1282.8	1259.6	1218.9	1187.0	1168.6
70°	1113.8	1095.4	1054.2	1022.3	1004.3
72.5°	940.4	922.0	899.3	867.3	853.7
75°	766.5	757.9	734.6	707.5	716.7
77.5°	611.6	593.2	584.0	570.5	556.9
80°	456.7	451.8	442.6	429.1	419.9
82.5°	310.4	310.4	306.1	287.7	287.7
85°	187.0	182.5	178.2	164.1	159.8
87.5°	82.3	73.1	63.9	50.3	45.5
90°	3.2	38.0	103.6	97.3	100.5
92.5°	65.5	88.8	92.0	95.2	95.2
95°	154.4	184.0	189.3	189.3	184.0
97.5°	257.0	284.5	296.1	296.1	296.1
100°	375.4	399.7	408.1	408.1	405.0
102.5°	500.2	518.1	529.8	532.9	529.8
105°	636.6	645.0	651.3	656.6	656.6
107.5°	771.9	784.6	784.6	786.7	771.9
110°	903.1	919.9	919.9	919.9	911.5

TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1044.7	1062.6	1059.5	1051.0	1044.7
115°	1184.3	1201.2	1195.9	1192.7	1184.3
117.5°	1322.8	1346.1	1331.2	1322.8	1314.3
120°	1462.3	1485.6	1462.3	1462.3	1452.9
122.5°	1589.2	1618.8	1604.1	1595.6	1589.2
125°	1722.5	1748.9	1740.5	1730.9	1727.8
127.5°	1852.6	1885.3	1873.7	1861.0	1852.6
130°	1974.1	2012.2	2007.0	2000.5	1989.0
132.5°	2110.5	2140.1	2142.3	2127.5	2119.0
135°	2227.9	2260.7	2267.0	2263.9	2255.4
137.5°	2359.1	2385.5	2390.8	2388.7	2375.9
140°	2474.3	2500.7	2515.5	2515.5	2503.9
142.5°	2592.7	2619.1	2627.6	2630.8	2619.1
145°	2704.7	2725.9	2742.9	2746.0	2734.4
147.5°	2805.2	2831.7	2844.4	2849.7	2838.0
150°	2908.9	2926.9	2938.5	2947.9	2938.5
152.5°	3000.8	3018.8	3033.7	3045.3	3033.7
155°	3092.9	3101.3	3110.9	3125.6	3116.1
157.5°	3172.2	3178.5	3183.8	3204.9	3190.1
160°	3243.0	3249.4	3252.5	3270.4	3257.8
162.5°	3308.6	3308.6	3311.7	3331.8	3317.0
165°	3364.6	3361.4	3361.4	3382.6	3367.8
167.5°	3415.4	3405.8	3405.8	3427.0	3412.2
170°	3453.4	3445.0	3441.8	3463.0	3445.0
172.5°	3479.8	3471.4	3468.2	3489.4	3471.4
175°	3501.0	3492.6	3486.3	3507.3	3489.4
177.5°	3512.6	3504.2	3497.8	3515.8	3497.8
180°	3507.3	3507.3	3507.3	3507.3	3507.3

TEST NUMBER: P913002

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.35	13.26	13.26	14.19	15.38	11.91	12.82	12.82	13.75	14.95
	3H	14.01	14.83	14.93	15.77	16.98	13.54	14.35	14.46	15.29	16.51
	4H	14.60	15.37	15.54	16.32	17.54	14.13	14.90	15.06	15.84	17.07
	6H	15.00	15.71	15.95	16.66	17.90	14.53	15.24	15.47	16.19	17.43
	8H	15.11	15.79	16.06	16.75	17.99	14.63	15.31	15.59	16.28	17.52
	12H	15.16	15.80	16.12	16.76	18.03	14.68	15.32	15.64	16.28	17.55
4H	2H	12.81	13.59	13.76	14.53	15.76	12.47	13.24	13.41	14.19	15.41
	3H	14.68	15.33	15.64	16.30	17.55	14.29	14.94	15.24	15.91	17.15
	4H	15.40	15.99	16.36	16.96	18.22	14.99	15.58	15.96	16.55	17.82
	6H	15.92	16.43	16.89	17.42	18.68	15.51	16.02	16.48	17.01	18.27
	8H	16.07	16.54	17.05	17.53	18.81	15.66	16.13	16.63	17.12	18.40
	12H	16.14	16.57	17.14	17.57	18.86	15.72	16.15	16.72	17.15	18.44
8H	4H	15.60	16.07	16.58	17.06	18.34	15.24	15.71	16.22	16.70	17.98
	6H	16.23	16.63	17.24	17.65	18.93	15.87	16.26	16.87	17.29	18.57
	8H	16.45	16.80	17.47	17.82	19.11	16.09	16.43	17.10	17.45	18.74
	12H	16.59	16.89	17.60	17.90	19.25	16.20	16.51	17.22	17.52	18.86
12H	4H	15.59	16.02	16.58	17.02	18.30	15.24	15.66	16.23	16.67	17.95
	6H	16.26	16.61	17.28	17.63	18.92	15.91	16.26	16.92	17.27	18.57
	8H	16.51	16.81	17.52	17.82	19.16	16.15	16.46	17.17	17.47	18.81

END OF REPORT