

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918500

Luminaire Tested: DFN2DIP-TR4F0-120D110US930-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918500
REPORT IS A COMBINATION OF REPORTS P900512 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D110US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16253.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3212	3212	3212
5°	3218	3161	3182
10°	3186	3099	3078
15°	3142	2997	2918
20°	3084	2856	2721
25°	3025	2697	2531
30°	2945	2535	2291
35°	2867	2360	2080
40°	2787	2180	1837
45°	2695	1980	1618
50°	2599	1777	1403
55°	2500	1561	1197
60°	2384	1335	985
65°	2251	1106	887
70°	2090	891	802
75°	1888	786	730
80°	1596	659	632
85°	1112	440	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2695 cd/sqm

TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.0	2.3
10°-20°	1040.3	6.4
20°-30°	1460.6	9.0
30°-40°	1592.1	9.8
40°-50°	1463.4	9.0
50°-60°	1149.2	7.1
60°-70°	748.0	4.6
70°-80°	385.1	2.4
80°-90°	106.4	0.7
90°-100°	175.5	1.1
100°-110°	557.7	3.4
110°-120°	954.3	5.9
120°-130°	1255.1	7.7
130°-140°	1408.8	8.7
140°-150°	1381.5	8.5
150°-160°	1158.9	7.1
160°-170°	768.5	4.7
170°-180°	268.6	1.7
0°-30°	2879.9	17.7
0°-40°	4472.0	27.5
0°-60°	7084.6	43.6
0°-90°	8324.1	51.2
90°-120°	1687.5	10.4
90°-150°	5732.8	35.3
90°-180°	7929.0	48.8
0°-180°	16253.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4044	4044	4044	4044	4044	
5°	4044	4025	3978	4010	4000	383
15°	3846	3806	3681	3612	3575	1084
25°	3491	3374	3132	2982	2927	1606
35°	3008	2821	2500	2269	2188	1883
45°	2459	2214	1830	1570	1482	1899
55°	1870	1584	1189	970	900	1671
65°	1263	966	637	512	501	1252
75°	673	417	293	267	264	712
85°	157	80	70	70	70	181
90°	2	31	84	79	81	16
95°	125	149	153	153	149	139
105°	515	522	527	531	531	543
115°	958	971	967	965	958	947
125°	1393	1414	1407	1400	1397	1245
135°	1802	1828	1833	1831	1824	1393
145°	2187	2204	2218	2221	2211	1367
155°	2501	2508	2516	2528	2520	1151
165°	2721	2718	2718	2735	2723	768
175°	2831	2824	2819	2836	2822	269
180°	2836	2836	2836	2836	2836	

TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4043.6	4043.6	4043.6	4043.6	4043.6
2.5°	4061.8	4043.6	4003.2	4040.0	4032.6
5°	4043.6	4025.3	3977.5	4010.5	3999.7
7.5°	4010.5	3988.8	3937.6	3951.9	3933.7
10°	3966.7	3941.1	3868.0	3856.8	3835.1
12.5°	3911.9	3878.9	3779.9	3758.2	3717.8
15°	3845.9	3805.6	3681.3	3611.8	3575.3
17.5°	3769.0	3710.4	3556.7	3476.4	3417.7
20°	3681.3	3607.9	3425.1	3333.8	3253.0
22.5°	3586.2	3502.0	3289.6	3165.3	3110.6
25°	3491.1	3373.8	3132.3	2982.4	2927.3
27.5°	3377.7	3253.0	2985.9	2814.0	2729.7
30°	3257.0	3117.6	2824.8	2638.5	2539.5
32.5°	3139.7	2971.2	2671.5	2451.8	2360.1
35°	3008.1	2821.3	2499.5	2268.9	2188.1
37.5°	2880.0	2678.5	2338.4	2085.6	1994.4
40°	2744.5	2525.1	2169.9	1910.2	1815.0
42.5°	2605.4	2371.4	2001.8	1730.8	1639.6
45°	2459.1	2213.8	1829.8	1569.7	1481.9
47.5°	2320.1	2060.4	1665.2	1405.1	1324.7
50°	2166.4	1906.7	1504.1	1251.3	1174.8
52.5°	2016.2	1741.6	1350.3	1108.8	1039.3
55°	1869.8	1584.5	1189.2	969.8	900.3
57.5°	1719.9	1427.2	1046.7	841.7	783.1
60°	1566.2	1273.4	896.4	710.1	651.5
62.5°	1416.3	1123.6	768.3	592.9	563.7
65°	1262.6	966.0	636.7	512.5	501.2
67.5°	1116.2	819.5	512.5	450.0	439.1
70°	962.5	677.1	424.4	387.8	373.1
72.5°	816.1	545.1	354.8	325.7	318.4
75°	673.2	416.9	292.8	267.1	263.6
77.5°	530.8	296.2	230.6	215.9	208.5
80°	398.8	212.4	175.5	161.1	161.1
82.5°	278.0	142.8	120.7	113.3	113.3
85°	157.3	80.4	69.5	69.5	69.5
87.5°	58.6	29.1	29.1	25.6	25.6
90°	2.5	30.8	83.8	78.7	81.2
92.5°	53.0	71.8	74.4	77.0	77.0
95°	124.8	148.8	153.0	153.0	148.8
97.5°	207.8	230.0	239.5	239.5	239.5
100°	303.5	323.2	330.0	330.0	327.5
102.5°	404.5	419.0	428.4	431.0	428.4
105°	514.8	521.6	526.8	531.0	531.0
107.5°	624.2	634.5	634.5	636.2	624.2
110°	730.3	744.0	744.0	744.0	737.1

TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	844.8	859.3	856.8	849.9	844.8
115°	957.7	971.3	967.1	964.6	957.7
117.5°	1069.8	1088.5	1076.5	1069.8	1062.9
120°	1182.6	1201.4	1182.6	1182.6	1174.9
122.5°	1285.2	1309.1	1297.1	1290.3	1285.2
125°	1392.9	1414.3	1407.4	1399.8	1397.2
127.5°	1498.1	1524.6	1515.2	1505.0	1498.1
130°	1596.4	1627.3	1622.9	1617.8	1608.4
132.5°	1706.7	1730.7	1732.4	1720.4	1713.6
135°	1801.6	1828.1	1833.3	1830.8	1823.9
137.5°	1907.7	1929.1	1933.3	1931.6	1921.4
140°	2000.9	2022.3	2034.3	2034.3	2024.9
142.5°	2096.7	2118.1	2124.9	2127.4	2118.1
145°	2187.3	2204.4	2218.1	2220.6	2211.3
147.5°	2268.6	2289.9	2300.2	2304.4	2295.1
150°	2352.4	2366.9	2376.3	2384.0	2376.3
152.5°	2426.7	2441.2	2453.2	2462.7	2453.2
155°	2501.2	2507.9	2515.7	2527.7	2519.9
157.5°	2565.3	2570.4	2574.6	2591.8	2579.8
160°	2622.6	2627.7	2630.2	2644.8	2634.6
162.5°	2675.6	2675.6	2678.2	2694.4	2682.4
165°	2720.9	2718.3	2718.3	2735.4	2723.4
167.5°	2761.9	2754.2	2754.2	2771.4	2759.4
170°	2792.7	2785.9	2783.3	2800.4	2785.9
172.5°	2814.1	2807.2	2804.7	2821.8	2807.2
175°	2831.2	2824.4	2819.2	2836.3	2821.8
177.5°	2840.6	2833.7	2828.6	2843.2	2828.6
180°	2836.3	2836.3	2836.3	2836.3	2836.3

TEST NUMBER: P918500

CATALOG NUMBER: DFN2DIP-TR4F0-120D110US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.31	12.15	12.26	13.11	14.37	7.28	8.12	8.24	9.09	10.34
	3H	12.99	13.74	13.95	14.71	15.99	8.47	9.22	9.44	10.20	11.48
	4H	13.59	14.31	14.57	15.28	16.57	8.92	9.63	9.90	10.61	11.90
	6H	14.02	14.67	15.01	15.65	16.95	9.25	9.90	10.24	10.88	12.18
	8H	14.14	14.77	15.14	15.76	17.06	9.34	9.96	10.33	10.96	12.26
	12H	14.21	14.80	15.21	15.79	17.11	9.38	9.97	10.38	10.97	12.29
4H	2H	11.33	12.04	12.31	13.02	14.30	7.88	8.59	8.86	9.57	10.85
	3H	13.16	13.75	14.15	14.76	16.06	9.23	9.82	10.22	10.83	12.13
	4H	13.85	14.39	14.85	15.39	16.71	9.78	10.32	10.78	11.32	12.64
	6H	14.37	14.83	15.38	15.85	17.18	10.20	10.66	11.21	11.69	13.01
	8H	14.54	14.97	15.56	15.99	17.33	10.33	10.76	11.34	11.78	13.12
	12H	14.64	15.03	15.67	16.06	17.40	10.40	10.79	11.43	11.82	13.16
8H	4H	13.82	14.25	14.83	15.27	16.61	10.06	10.49	11.07	11.51	12.85
	6H	14.39	14.74	15.42	15.80	17.14	10.58	10.94	11.62	12.00	13.33
	8H	14.60	14.92	15.65	15.96	17.31	10.77	11.09	11.82	12.13	13.48
	12H	14.74	15.02	15.79	16.06	17.45	10.89	11.17	11.94	12.21	13.60
12H	4H	13.77	14.16	14.80	15.19	16.54	10.07	10.46	11.10	11.49	12.83
	6H	14.36	14.68	15.41	15.72	17.07	10.63	10.94	11.68	11.99	13.34
	8H	14.58	14.86	15.63	15.90	17.29	10.84	11.12	11.89	12.16	13.55

END OF REPORT