

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915490

Luminaire Tested: DFN2DIP-TR4F0-050D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915490
REPORT IS A COMBINATION OF REPORTS P900371 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D040US927-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6725.6 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915490
CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915490
 CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58			58
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54	49			49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	52	50	47	45	41			41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39	35			35
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33	30			30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23	20			20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16			16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17	15			15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1224	1224	1224
5°	1226	1207	1215
10°	1216	1191	1199
15°	1199	1171	1173
20°	1174	1144	1147
25°	1150	1112	1116
30°	1120	1081	1078
35°	1092	1045	1037
40°	1057	1009	998
45°	1021	973	958
50°	983	935	912
55°	943	891	869
60°	898	839	820
65°	848	785	763
70°	785	719	701
75°	698	640	644
80°	593	540	535
85°	429	366	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1021 cd/sqm



TEST NUMBER: P915490

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	2.2
10°-20°	408.1	6.1
20°-30°	599.8	8.9
30°-40°	696.6	10.4
40°-50°	695.8	10.3
50°-60°	606.7	9.0
60°-70°	448.5	6.7
70°-80°	253.7	3.8
80°-90°	69.8	1.0
90°-100°	62.0	0.9
100°-110°	197.0	2.9
110°-120°	337.2	5.0
120°-130°	443.5	6.6
130°-140°	497.8	7.4
140°-150°	488.1	7.3
150°-160°	409.5	6.1
160°-170°	271.5	4.0
170°-180°	94.9	1.4
0°-30°	1153.0	17.1
0°-40°	1849.6	27.5
0°-60°	3152.1	46.9
0°-90°	3924.1	58.3
90°-120°	596.2	8.9
90°-150°	2025.6	30.1
90°-180°	2801.0	41.6
0°-180°	6725.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1531	1528	146
15°	1467	1458	1439	1445	1438	413
25°	1328	1316	1291	1294	1291	611
35°	1146	1131	1107	1098	1091	715
45°	932	922	900	883	877	719
55°	706	697	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	11	30	28	29	6
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P915490

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.2	1541.2	1541.2	1541.2	1541.2
2.5°	1550.1	1542.8	1526.5	1541.2	1538.4
5°	1541.2	1535.4	1519.0	1530.8	1528.0
7.5°	1530.8	1522.0	1505.7	1517.7	1514.7
10°	1514.7	1504.3	1486.5	1498.3	1493.9
12.5°	1492.3	1483.5	1465.8	1473.1	1470.1
15°	1467.1	1458.3	1439.0	1445.0	1437.6
17.5°	1436.0	1427.2	1407.9	1415.2	1407.9
20°	1401.9	1393.1	1372.4	1376.7	1370.9
22.5°	1367.9	1354.6	1335.2	1335.2	1332.2
25°	1327.9	1316.1	1290.9	1293.7	1290.9
27.5°	1283.3	1273.0	1253.8	1249.3	1242.0
30°	1239.0	1227.1	1204.9	1200.5	1194.5
32.5°	1191.5	1182.7	1159.0	1150.0	1144.1
35°	1145.6	1130.8	1107.1	1098.1	1090.8
37.5°	1093.7	1080.4	1056.6	1046.2	1038.9
40°	1040.5	1028.5	1004.7	991.5	985.6
42.5°	988.6	976.6	953.0	938.0	929.2
45°	932.2	921.9	899.5	883.4	877.3
47.5°	877.3	867.0	843.3	826.9	818.1
50°	819.5	812.1	791.4	770.6	763.2
52.5°	763.2	752.8	733.6	717.3	706.9
55°	705.5	696.6	678.7	661.0	653.6
57.5°	647.6	640.2	620.9	603.2	597.1
60°	589.8	584.0	563.2	546.8	542.5
62.5°	533.5	523.2	508.3	493.5	487.6
65°	475.8	466.8	452.0	438.7	431.3
67.5°	416.5	409.0	395.8	385.4	379.4
70°	361.6	355.7	342.3	331.9	326.1
72.5°	305.4	299.4	292.0	281.6	277.2
75°	248.9	246.1	238.5	229.7	232.7
77.5°	198.6	192.6	189.6	185.2	180.9
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.8	100.8	99.3	93.4	93.4
85°	60.7	59.3	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P915490

CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P915490
 CATALOG NUMBER: DFN2DIP-TR4F0-050D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.71	9.65	9.59	10.55	11.70	8.27	9.22	9.16	10.12	11.27
	3H	10.37	11.22	11.27	12.13	13.30	9.90	10.74	10.79	11.66	12.83
	4H	10.96	11.76	11.87	12.68	13.86	10.49	11.29	11.40	12.21	13.39
	6H	11.37	12.10	12.29	13.03	14.22	10.89	11.63	11.81	12.55	13.75
	8H	11.47	12.18	12.40	13.12	14.31	11.00	11.70	11.93	12.64	13.84
	12H	11.52	12.19	12.46	13.13	14.35	11.04	11.71	11.98	12.65	13.87
4H	2H	9.18	9.98	10.09	10.89	12.08	8.83	9.63	9.75	10.55	11.73
	3H	11.05	11.72	11.98	12.67	13.86	10.66	11.32	11.58	12.27	13.47
	4H	11.77	12.38	12.70	13.32	14.54	11.36	11.97	12.30	12.91	14.14
	6H	12.29	12.81	13.24	13.78	15.00	11.88	12.40	12.83	13.37	14.59
	8H	12.44	12.93	13.39	13.89	15.13	12.03	12.52	12.98	13.48	14.72
	12H	12.52	12.96	13.49	13.94	15.18	12.09	12.54	13.06	13.52	14.76
8H	4H	11.97	12.46	12.92	13.42	14.66	11.61	12.10	12.56	13.06	14.30
	6H	12.61	13.01	13.58	14.01	15.25	12.24	12.65	13.22	13.65	14.89
	8H	12.83	13.19	13.81	14.18	15.43	12.46	12.82	13.44	13.81	15.06
	12H	12.96	13.28	13.95	14.26	15.56	12.58	12.89	13.57	13.88	15.18
12H	4H	11.96	12.40	12.93	13.38	14.62	11.61	12.05	12.58	13.03	14.27
	6H	12.64	13.00	13.62	13.99	15.24	12.28	12.64	13.27	13.64	14.89
	8H	12.88	13.20	13.87	14.18	15.48	12.52	12.84	13.51	13.83	15.13