

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920917

Luminaire Tested: DFN2DIP-TR4F0-040D050US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920917
REPORT IS A COMBINATION OF REPORTS P901908 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D050US935-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7189.3 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 69.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1131	1131	1131
5°	1133	1113	1120
10°	1121	1091	1083
15°	1106	1055	1027
20°	1086	1005	958
25°	1065	949	891
30°	1037	892	807
35°	1009	831	732
40°	981	767	647
45°	949	697	570
50°	915	626	494
55°	880	550	421
60°	839	470	347
65°	792	389	312
70°	736	314	282
75°	664	277	257
80°	561	232	223
85°	392	155	167

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 949 cd/sqm

TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	1.9
10°-20°	366.2	5.1
20°-30°	514.2	7.2
30°-40°	560.5	7.8
40°-50°	515.1	7.2
50°-60°	404.5	5.6
60°-70°	263.3	3.7
70°-80°	135.6	1.9
80°-90°	37.2	0.5
90°-100°	47.9	0.7
100°-110°	178.6	2.5
110°-120°	473.7	6.6
120°-130°	785.6	10.9
130°-140°	834.5	11.6
140°-150°	775.6	10.8
150°-160°	623.5	8.7
160°-170°	401.8	5.6
170°-180°	138.3	1.9
0°-30°	1013.8	14.1
0°-40°	1574.2	21.9
0°-60°	2493.9	34.7
0°-90°	2929.9	40.8
90°-120°	700.2	9.7
90°-150°	3095.8	43.1
90°-180°	4259.0	59.2
0°-180°	7189.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	1	13	21	26	28	7
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0

TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P920917

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.64	7.40	7.68	8.44	9.84	2.61	3.37	3.65	4.41	5.81
	3H	8.31	8.99	9.36	10.04	11.46	3.80	4.48	4.85	5.53	6.95
	4H	8.92	9.56	9.98	10.61	12.04	4.25	4.89	5.31	5.94	7.37
	6H	9.33	9.93	10.40	10.98	12.42	4.56	5.16	5.63	6.21	7.65
	8H	9.46	10.02	10.53	11.09	12.53	4.65	5.22	5.73	6.29	7.72
	12H	9.52	10.05	10.60	11.12	12.57	4.69	5.23	5.77	6.29	7.75
4H	2H	6.65	7.29	7.72	8.35	9.77	3.20	3.84	4.27	4.90	6.32
	3H	8.47	9.01	9.55	10.09	11.53	4.55	5.08	5.62	6.16	7.60
	4H	9.16	9.65	10.24	10.72	12.18	5.09	5.58	6.17	6.65	8.11
	6H	9.67	10.09	10.76	11.19	12.64	5.51	5.93	6.60	7.02	8.48
	8H	9.85	10.24	10.94	11.32	12.79	5.64	6.03	6.72	7.11	8.58
	12H	9.94	10.29	11.04	11.39	12.87	5.70	6.05	6.80	7.15	8.63
8H	4H	9.12	9.52	10.21	10.60	12.07	5.37	5.76	6.45	6.84	8.31
	6H	9.69	10.01	10.80	11.14	12.61	5.88	6.21	6.99	7.33	8.80
	8H	9.90	10.19	11.02	11.30	12.78	6.07	6.36	7.19	7.47	8.95
	12H	10.04	10.29	11.16	11.39	12.92	6.19	6.44	7.31	7.55	9.07
12H	4H	9.07	9.43	10.18	10.53	12.00	5.37	5.72	6.47	6.82	8.30
	6H	9.66	9.95	10.78	11.06	12.54	5.93	6.22	7.05	7.33	8.81
	8H	9.88	10.13	11.00	11.24	12.76	6.14	6.39	7.26	7.49	9.02

END OF REPORT