

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915549

Luminaire Tested: DFN2DIP-TR4F0-060D090US927-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P915549  
REPORT IS A COMBINATION OF REPORTS P901984 AND P898849  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-060D090US927-RLLONL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11098.4 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 121  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P915549  
CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P915549  
 CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31			31
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32	27			27
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28	23			23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20			20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	18			18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16			16
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17	14			14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13			13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12			12
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13	11			11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1561	1561	1561
5°	1563	1536	1546
10°	1548	1506	1495
15°	1526	1456	1417
20°	1498	1387	1322
25°	1469	1310	1230
30°	1431	1232	1113
35°	1393	1147	1010
40°	1354	1059	893
45°	1309	962	786
50°	1263	863	682
55°	1214	758	582
60°	1158	649	479
65°	1094	537	431
70°	1015	433	390
75°	917	382	355
80°	775	320	307
85°	540	213	230

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1309 cd/sqm



TEST NUMBER: P915549

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.1	1.7
10°-20°	505.4	4.6
20°-30°	709.6	6.4
30°-40°	773.5	7.0
40°-50°	710.9	6.4
50°-60°	558.3	5.0
60°-70°	363.4	3.3
70°-80°	187.1	1.7
80°-90°	52.0	0.5
90°-100°	79.3	0.7
100°-110°	295.8	2.7
110°-120°	784.4	7.1
120°-130°	1301.0	11.7
130°-140°	1382.0	12.5
140°-150°	1284.4	11.6
150°-160°	1032.6	9.3
160°-170°	665.4	6.0
170°-180°	229.0	2.1
0°-30°	1399.1	12.6
0°-40°	2172.6	19.6
0°-60°	3441.9	31.0
0°-90°	4044.4	36.4
90°-120°	1159.5	10.4
90°-150°	5127.0	46.2
90°-180°	7054.0	63.6
0°-180°	11098.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1956	1932	1948	1943	186
15°	1868	1849	1788	1755	1737	527
25°	1696	1639	1522	1449	1422	780
35°	1461	1371	1214	1102	1063	915
45°	1195	1076	889	763	720	923
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	203	142	130	128	346
85°	76	39	34	34	34	88
90°	2	21	35	44	47	10
95°	113	56	68	77	75	134
105°	529	582	106	125	132	566
115°	1001	1031	1074	268	143	986
125°	1415	1438	1471	1483	1489	1262
135°	1752	1780	1795	1813	1809	1353
145°	2032	2030	2060	2072	2063	1271
155°	2237	2222	2243	2253	2239	1031
165°	2357	2347	2352	2364	2352	666
175°	2411	2399	2403	2415	2398	229
180°	2406	2406	2406	2406	2406	



TEST NUMBER: P915549

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1964.5	1964.5	1964.5	1964.5	1964.5
2.5°	1973.3	1964.5	1944.8	1962.7	1959.1
5°	1964.5	1955.6	1932.4	1948.4	1943.1
7.5°	1948.4	1937.8	1913.0	1919.9	1911.1
10°	1927.1	1914.6	1879.2	1873.7	1863.1
12.5°	1900.5	1884.4	1836.4	1825.8	1806.2
15°	1868.4	1848.8	1788.4	1754.7	1736.9
17.5°	1831.1	1802.6	1727.9	1688.9	1660.4
20°	1788.4	1752.8	1664.0	1619.6	1580.4
22.5°	1742.2	1701.3	1598.1	1537.8	1511.2
25°	1696.1	1639.1	1521.8	1449.0	1422.2
27.5°	1641.0	1580.4	1450.6	1367.1	1326.2
30°	1582.3	1514.6	1372.4	1281.8	1233.7
32.5°	1525.3	1443.5	1297.9	1191.1	1146.6
35°	1461.4	1370.7	1214.3	1102.2	1063.0
37.5°	1399.2	1301.2	1136.1	1013.3	968.9
40°	1333.3	1226.8	1054.2	928.0	881.8
42.5°	1265.8	1152.1	972.5	840.8	796.5
45°	1194.7	1075.5	889.0	762.6	719.9
47.5°	1127.2	1001.0	809.0	682.6	643.6
50°	1052.5	926.3	730.7	607.9	570.8
52.5°	979.5	846.1	656.0	538.7	504.9
55°	908.4	769.8	577.7	471.2	437.4
57.5°	835.6	693.3	508.5	408.9	380.4
60°	760.9	618.7	435.5	345.0	316.5
62.5°	688.1	545.9	373.3	288.0	273.9
65°	613.4	469.3	309.3	249.0	243.5
67.5°	542.2	398.2	249.0	218.6	213.3
70°	467.5	328.9	206.1	188.5	181.3
72.5°	396.5	264.8	172.4	158.3	154.6
75°	327.1	202.6	142.2	129.8	128.1
77.5°	257.9	143.9	112.0	104.9	101.3
80°	193.7	103.1	85.2	78.3	78.3
82.5°	135.1	69.4	58.6	55.1	55.1
85°	76.4	39.1	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.9
97.5°	203.7	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.3	113.1	116.6
102.5°	423.0	419.7	102.7	121.8	127.1
105°	529.3	581.6	106.2	125.3	132.3
107.5°	652.9	696.3	109.8	128.8	135.9
110°	771.3	807.8	304.8	130.6	137.5



TEST NUMBER: P915549

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	882.8	914.0	884.5	134.0	139.3
115°	1001.1	1030.6	1074.3	268.2	142.8
117.5°	1103.8	1138.6	1168.3	919.2	463.1
120°	1218.8	1244.8	1276.3	1297.1	1062.1
122.5°	1316.2	1344.1	1379.0	1389.3	1391.2
125°	1415.4	1438.1	1471.2	1483.4	1488.6
127.5°	1505.9	1530.3	1556.6	1574.0	1575.6
130°	1591.3	1619.3	1638.3	1657.5	1655.9
132.5°	1678.4	1701.1	1720.1	1735.9	1734.2
135°	1751.6	1779.5	1795.0	1812.6	1809.1
137.5°	1828.1	1849.0	1866.5	1883.9	1878.7
140°	1902.9	1917.0	1936.0	1951.7	1943.1
142.5°	1965.8	1978.0	2000.5	2014.4	2005.7
145°	2031.9	2030.0	2059.7	2071.9	2063.2
147.5°	2089.2	2084.1	2113.6	2122.3	2115.4
150°	2145.1	2132.9	2160.8	2171.1	2162.4
152.5°	2192.0	2178.1	2204.2	2214.7	2202.5
155°	2237.3	2221.8	2242.6	2253.0	2239.1
157.5°	2273.9	2260.0	2275.7	2287.9	2273.9
160°	2305.2	2294.7	2305.2	2315.6	2303.4
162.5°	2333.0	2322.6	2331.3	2343.5	2327.8
165°	2357.4	2347.0	2352.2	2364.4	2352.2
167.5°	2376.6	2366.1	2371.4	2383.6	2367.9
170°	2392.3	2381.8	2385.3	2397.5	2381.8
172.5°	2402.7	2392.3	2395.8	2408.0	2392.3
175°	2411.3	2399.1	2402.7	2414.8	2397.5
177.5°	2414.8	2402.7	2404.5	2416.7	2401.0
180°	2406.2	2406.2	2406.2	2406.2	2406.2



TEST NUMBER: P915549  
 CATALOG NUMBER: DFN2DIP-TR4F0-060D090US927-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.27	8.00	8.34	9.07	10.53	3.25	3.98	4.32	5.05	6.50
	3H	8.94	9.60	10.02	10.67	12.15	4.43	5.08	5.51	6.16	7.63
	4H	9.55	10.17	10.64	11.24	12.72	4.88	5.49	5.97	6.57	8.05
	6H	9.96	10.53	11.06	11.61	13.11	5.19	5.76	6.29	6.84	8.33
	8H	10.09	10.63	11.19	11.73	13.21	5.28	5.82	6.38	6.92	8.40
	12H	10.14	10.66	11.25	11.75	13.26	5.32	5.84	6.43	6.93	8.43
4H	2H	7.28	7.90	8.38	8.98	10.46	3.83	4.45	4.93	5.53	7.01
	3H	9.10	9.61	10.20	10.72	12.21	5.17	5.69	6.28	6.79	8.28
	4H	9.79	10.26	10.90	11.36	12.87	5.72	6.19	6.83	7.29	8.80
	6H	10.30	10.70	11.41	11.82	13.33	6.13	6.54	7.25	7.66	9.16
	8H	10.47	10.85	11.59	11.96	13.48	6.26	6.64	7.38	7.75	9.27
	12H	10.56	10.90	11.69	12.03	13.55	6.32	6.66	7.45	7.79	9.31
8H	4H	9.75	10.13	10.86	11.24	12.76	5.99	6.37	7.11	7.48	9.00
	6H	10.31	10.62	11.45	11.77	13.29	6.51	6.82	7.64	7.97	9.49
	8H	10.53	10.80	11.67	11.93	13.47	6.70	6.97	7.84	8.10	9.64
	12H	10.66	10.90	11.81	12.03	13.60	6.81	7.05	7.96	8.18	9.76
12H	4H	9.70	10.04	10.83	11.16	12.69	5.99	6.33	7.12	7.45	8.98
	6H	10.29	10.56	11.43	11.69	13.23	6.55	6.83	7.70	7.96	9.50
	8H	10.50	10.74	11.65	11.87	13.45	6.76	7.00	7.91	8.13	9.71