

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921017

Luminaire Tested: DFN2DIP-TR4F0-060D120US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921017
REPORT IS A COMBINATION OF REPORTS P902038 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-060D120US935-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14619.7 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 144.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1696	1696	1696
5°	1699	1669	1680
10°	1682	1637	1625
15°	1659	1582	1541
20°	1628	1508	1437
25°	1597	1424	1337
30°	1555	1339	1210
35°	1514	1246	1098
40°	1472	1151	970
45°	1423	1045	854
50°	1372	938	741
55°	1320	824	632
60°	1259	705	520
65°	1189	584	468
70°	1104	471	424
75°	997	415	385
80°	842	348	334
85°	587	232	251

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1851 cd/sqm

TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	1.4
10°-20°	549.3	3.8
20°-30°	771.2	5.3
30°-40°	840.7	5.8
40°-50°	772.7	5.3
50°-60°	606.8	4.2
60°-70°	395.0	2.7
70°-80°	203.3	1.4
80°-90°	58.0	0.4
90°-100°	115.0	0.8
100°-110°	428.6	2.9
110°-120°	1136.8	7.8
120°-130°	1885.4	12.9
130°-140°	2002.8	13.7
140°-150°	1861.3	12.7
150°-160°	1496.5	10.2
160°-170°	964.3	6.6
170°-180°	331.9	2.3
0°-30°	1520.7	10.4
0°-40°	2361.4	16.2
0°-60°	3740.9	25.6
0°-90°	4397.2	30.1
90°-120°	1680.4	11.5
90°-150°	7429.9	50.8
90°-180°	10223.0	69.9
0°-180°	14619.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	2	30	50	63	68	14
95°	164	81	98	111	108	194
105°	767	843	154	182	192	820
115°	1451	1494	1557	389	207	1428
125°	2051	2084	2132	2150	2157	1829
135°	2538	2579	2601	2627	2622	1961
145°	2945	2942	2985	3002	2990	1842
155°	3242	3220	3250	3265	3245	1494
165°	3416	3401	3409	3426	3409	965
175°	3494	3477	3482	3500	3474	333
180°	3487	3487	3487	3487	3487	

TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	2.4	30.2	50.4	63.2	68.0
92.5°	63.2	53.0	60.5	65.6	68.0
95°	163.8	80.6	98.2	111.2	108.5
97.5°	295.2	88.4	128.5	136.3	138.7
100°	446.7	101.0	143.8	163.8	169.0
102.5°	613.0	608.2	148.9	176.5	184.3
105°	767.0	842.8	154.0	181.6	191.7
107.5°	946.2	1009.1	159.1	186.7	196.8
110°	1117.8	1170.6	441.6	189.3	199.2

TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1279.4	1324.6	1281.8	194.2	201.9
115°	1450.7	1493.6	1556.8	388.6	207.1
117.5°	1599.6	1650.0	1693.2	1332.0	671.1
120°	1766.3	1804.0	1849.5	1879.8	1539.1
122.5°	1907.4	1947.8	1998.5	2013.4	2016.1
125°	2051.2	2084.1	2132.1	2149.7	2157.2
127.5°	2182.4	2217.8	2255.8	2281.0	2283.4
130°	2306.1	2346.6	2374.1	2402.0	2399.6
132.5°	2432.2	2465.2	2492.8	2515.6	2513.2
135°	2538.3	2578.8	2601.2	2626.7	2621.7
137.5°	2649.2	2679.4	2704.9	2730.1	2722.6
140°	2757.7	2778.0	2805.6	2828.4	2815.8
142.5°	2848.7	2866.4	2899.1	2919.1	2906.6
145°	2944.6	2941.9	2984.7	3002.5	2989.8
147.5°	3027.6	3020.1	3063.0	3075.6	3065.7
150°	3108.5	3090.8	3131.3	3146.3	3133.7
152.5°	3176.5	3156.4	3194.2	3209.5	3191.8
155°	3242.1	3219.6	3249.9	3264.9	3244.8
157.5°	3295.1	3275.1	3297.9	3315.5	3295.1
160°	3340.7	3325.4	3340.7	3355.7	3338.0
162.5°	3380.9	3365.9	3378.5	3396.1	3373.4
165°	3416.2	3401.2	3408.7	3426.4	3408.7
167.5°	3444.1	3428.8	3436.6	3454.2	3431.5
170°	3466.8	3451.6	3456.6	3474.3	3451.6
172.5°	3481.8	3466.8	3472.0	3489.6	3466.8
175°	3494.4	3476.7	3481.8	3499.5	3474.3
177.5°	3499.5	3481.8	3484.5	3502.2	3479.5
180°	3487.0	3487.0	3487.0	3487.0	3487.0

TEST NUMBER: P921017

CATALOG NUMBER: DFN2DIP-TR4F0-060D120US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.76	7.45	7.87	8.55	10.09	2.73	3.42	3.85	4.53	6.06
	3H	8.42	9.04	9.55	10.16	11.70	3.91	4.53	5.03	5.64	7.19
	4H	9.02	9.61	10.16	10.73	12.28	4.35	4.94	5.49	6.05	7.61
	6H	9.44	9.98	10.58	11.10	12.66	4.67	5.21	5.81	6.33	7.89
	8H	9.56	10.07	10.71	11.21	12.77	4.75	5.27	5.90	6.40	7.96
	12H	9.62	10.10	10.77	11.23	12.81	4.79	5.28	5.94	6.41	7.99
4H	2H	6.76	7.34	7.90	8.46	10.01	3.31	3.89	4.45	5.01	6.56
	3H	8.57	9.06	9.72	10.20	11.77	4.65	5.13	5.79	6.28	7.84
	4H	9.26	9.71	10.41	10.84	12.42	5.19	5.64	6.34	6.77	8.35
	6H	9.77	10.15	10.92	11.30	12.88	5.60	5.98	6.76	7.14	8.72
	8H	9.94	10.30	11.09	11.44	13.04	5.73	6.09	6.88	7.23	8.82
	12H	10.03	10.35	11.20	11.51	13.11	5.79	6.11	6.96	7.27	8.87
8H	4H	9.22	9.58	10.37	10.72	12.31	5.46	5.82	6.61	6.96	8.55
	6H	9.78	10.07	10.95	11.26	12.85	5.97	6.27	7.15	7.46	9.05
	8H	9.99	10.25	11.17	11.42	13.03	6.16	6.42	7.34	7.59	9.20
	12H	10.13	10.35	11.31	11.52	13.16	6.28	6.50	7.46	7.67	9.31
12H	4H	9.16	9.49	10.33	10.64	12.24	5.46	5.78	6.63	6.94	8.54
	6H	9.75	10.01	10.93	11.18	12.79	6.02	6.28	7.20	7.45	9.06
	8H	9.97	10.19	11.15	11.36	13.00	6.23	6.45	7.41	7.62	9.26

END OF REPORT