

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915594

Luminaire Tested: DFN2DIP-TR4F0-070D120US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915594
REPORT IS A COMBINATION OF REPORTS P900519 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D120US927-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13902.7 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 156.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915594
CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915594

CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	39	39	39	33
2	87	80	74	68	79	73	67	63	59	56	53	47	45	43	36	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	28	28	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	21	21	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	19	19	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	16	16	16	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	13	13	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1714	1714	1714
5°	1717	1690	1702
10°	1703	1667	1678
15°	1678	1640	1642
20°	1644	1602	1606
25°	1611	1556	1563
30°	1568	1514	1509
35°	1528	1464	1451
40°	1479	1413	1397
45°	1430	1362	1341
50°	1376	1309	1276
55°	1320	1248	1217
60°	1257	1174	1149
65°	1188	1099	1068
70°	1100	1007	982
75°	977	896	902
80°	831	755	749
85°	601	513	496

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2343 cd/sqm



TEST NUMBER: P915594

CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	1.5
10°-20°	571.4	4.1
20°-30°	839.7	6.0
30°-40°	975.3	7.0
40°-50°	974.1	7.0
50°-60°	849.4	6.1
60°-70°	627.9	4.5
70°-80°	355.2	2.6
80°-90°	102.3	0.7
90°-100°	186.0	1.3
100°-110°	591.1	4.3
110°-120°	1011.6	7.3
120°-130°	1330.4	9.6
130°-140°	1493.3	10.7
140°-150°	1464.3	10.5
150°-160°	1228.4	8.8
160°-170°	814.6	5.9
170°-180°	284.7	2.0
0°-30°	1614.2	11.6
0°-40°	2589.5	18.6
0°-60°	4412.9	31.7
0°-90°	5498.4	39.5
90°-120°	1788.7	12.9
90°-150°	6076.6	43.7
90°-180°	8404.0	60.4
0°-180°	13902.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2127	2143	2139	205
15°	2054	2042	2015	2023	2013	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1002
45°	1305	1291	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	3	33	89	83	86	14
95°	132	158	162	162	158	147
105°	546	553	558	563	563	576
115°	1015	1030	1025	1022	1015	1004
125°	1476	1499	1492	1484	1481	1319
135°	1910	1938	1943	1940	1933	1476
145°	2318	2337	2351	2354	2344	1449
155°	2651	2658	2667	2679	2671	1220
165°	2884	2881	2881	2900	2887	814
175°	3001	2994	2988	3006	2991	285
180°	3006	3006	3006	3006	3006	



TEST NUMBER: P915594

CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.7	2157.7	2157.7	2157.7	2157.7
2.5°	2170.3	2159.9	2137.0	2157.7	2153.7
5°	2157.7	2149.6	2126.7	2143.2	2139.2
7.5°	2143.2	2130.8	2107.9	2124.7	2120.5
10°	2120.5	2105.9	2081.1	2097.6	2091.4
12.5°	2089.2	2076.9	2052.1	2062.4	2058.2
15°	2054.0	2041.7	2014.6	2023.0	2012.6
17.5°	2010.4	1998.1	1971.0	1981.4	1971.0
20°	1962.6	1950.4	1921.3	1927.5	1919.3
22.5°	1915.1	1896.4	1869.3	1869.3	1865.1
25°	1859.0	1842.5	1807.3	1811.2	1807.3
27.5°	1796.7	1782.2	1755.3	1749.1	1738.8
30°	1734.6	1717.8	1686.9	1680.7	1672.3
32.5°	1668.1	1655.8	1622.5	1610.0	1601.6
35°	1603.8	1583.2	1549.9	1537.4	1527.0
37.5°	1531.2	1512.5	1479.2	1464.7	1454.4
40°	1456.6	1439.9	1406.6	1388.1	1379.7
42.5°	1383.9	1367.2	1334.2	1313.3	1300.9
45°	1305.1	1290.6	1259.3	1236.7	1228.3
47.5°	1228.3	1213.8	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.9	1068.5
52.5°	1068.5	1054.0	1027.1	1004.2	989.7
55°	987.7	975.2	950.3	925.4	915.0
57.5°	906.7	896.4	869.3	844.4	836.1
60°	825.7	817.5	788.5	765.6	759.5
62.5°	746.9	732.4	711.7	691.0	682.6
65°	666.1	653.5	632.9	614.2	603.8
67.5°	583.1	572.6	554.1	539.6	531.2
70°	506.3	498.0	479.2	464.7	456.5
72.5°	427.5	419.1	408.8	394.3	388.1
75°	348.5	344.5	333.9	321.6	325.8
77.5°	278.1	269.7	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	2.7	32.6	88.8	83.4	86.1
92.5°	56.2	76.1	78.8	81.6	81.6
95°	132.3	157.7	162.2	162.2	157.7
97.5°	220.2	243.8	253.8	253.8	253.8
100°	321.8	342.6	349.8	349.8	347.1
102.5°	428.7	444.1	454.1	456.9	454.1
105°	545.7	552.9	558.3	562.8	562.8
107.5°	661.6	672.6	672.6	674.3	661.6
110°	774.0	788.5	788.5	788.5	781.3



TEST NUMBER: P915594

CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	895.5	910.9	908.2	900.9	895.5
115°	1015.1	1029.7	1025.1	1022.4	1015.1
117.5°	1133.8	1153.8	1141.1	1133.8	1126.6
120°	1253.5	1273.4	1253.5	1253.5	1245.4
122.5°	1362.3	1387.7	1375.0	1367.7	1362.3
125°	1476.5	1499.1	1491.9	1483.8	1481.0
127.5°	1588.0	1616.0	1606.1	1595.2	1588.0
130°	1692.2	1724.8	1720.3	1714.8	1704.9
132.5°	1809.1	1834.5	1836.3	1823.6	1816.4
135°	1909.7	1937.8	1943.3	1940.5	1933.3
137.5°	2022.1	2044.8	2049.3	2047.5	2036.6
140°	2120.9	2143.6	2156.2	2156.2	2146.3
142.5°	2222.5	2245.1	2252.3	2255.0	2245.1
145°	2318.5	2336.6	2351.1	2353.9	2343.9
147.5°	2404.6	2427.2	2438.2	2442.7	2432.7
150°	2493.5	2508.8	2518.8	2527.0	2518.8
152.5°	2572.3	2587.7	2600.4	2610.4	2600.4
155°	2651.1	2658.4	2666.6	2679.2	2671.1
157.5°	2719.2	2724.5	2729.1	2747.2	2734.5
160°	2779.8	2785.3	2788.0	2803.4	2792.5
162.5°	2836.0	2836.0	2838.8	2856.0	2843.3
165°	2884.1	2881.4	2881.4	2899.5	2886.8
167.5°	2927.6	2919.4	2919.4	2937.6	2924.9
170°	2960.2	2952.9	2950.2	2968.4	2952.9
172.5°	2982.9	2975.6	2972.9	2991.0	2975.6
175°	3001.0	2993.7	2988.3	3006.4	2991.0
177.5°	3011.0	3003.7	2998.2	3013.7	2998.2
180°	3006.4	3006.4	3006.4	3006.4	3006.4



TEST NUMBER: P915594
 CATALOG NUMBER: DFN2DIP-TR4F0-070D120US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.09	8.86	9.13	9.91	11.32	7.65	8.43	8.70	9.48	10.89
	3H	9.74	10.43	10.79	11.49	12.92	9.27	9.96	10.32	11.02	12.45
	4H	10.32	10.98	11.39	12.04	13.48	9.85	10.51	10.91	11.57	13.01
	6H	10.72	11.32	11.79	12.39	13.84	10.24	10.85	11.32	11.91	13.36
	8H	10.82	11.40	11.90	12.48	13.92	10.35	10.92	11.42	12.00	13.45
	12H	10.87	11.41	11.95	12.49	13.96	10.39	10.93	11.47	12.01	13.48
4H	2H	8.54	9.20	9.61	10.25	11.69	8.19	8.85	9.26	9.91	11.35
	3H	10.40	10.94	11.47	12.03	13.48	10.00	10.55	11.08	11.64	13.09
	4H	11.11	11.61	12.19	12.69	14.16	10.70	11.20	11.78	12.28	13.75
	6H	11.62	12.05	12.71	13.15	14.62	11.21	11.64	12.30	12.74	14.21
	8H	11.76	12.17	12.86	13.26	14.74	11.35	11.76	12.44	12.85	14.33
	12H	11.83	12.20	12.94	13.30	14.79	11.41	11.78	12.52	12.88	14.37
8H	4H	11.30	11.70	12.39	12.79	14.27	10.94	11.34	12.03	12.43	13.91
	6H	11.92	12.26	13.04	13.39	14.87	11.56	11.89	12.67	13.03	14.51
	8H	12.14	12.44	13.26	13.55	15.05	11.77	12.07	12.89	13.18	14.68
	12H	12.27	12.53	13.40	13.64	15.18	11.89	12.14	13.01	13.26	14.79
12H	4H	11.28	11.64	12.39	12.75	14.24	10.93	11.29	12.03	12.40	13.88
	6H	11.95	12.25	13.07	13.36	14.86	11.60	11.89	12.72	13.01	14.51
	8H	12.19	12.45	13.32	13.56	15.10	11.83	12.09	12.96	13.20	14.74