

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915710

Luminaire Tested: DFN2DIP-TR4F0-110D050US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915710
REPORT IS A COMBINATION OF REPORTS P900401 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D050US927-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12132.3 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 150.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915710
CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915710
 CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	64	64	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	54	54	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	46	46	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	40	40	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	34	34	34	32
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	30	30	30	30	28
7	61	49	40	35	58	46	39	33	42	36	31	39	33	29	35	30	27	27	27	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	24	24	24	22
9	53	41	33	28	50	39	32	27	36	29	25	33	27	24	30	25	22	22	22	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2694	2694	2694
5°	2698	2656	2674
10°	2676	2620	2638
15°	2637	2577	2581
20°	2584	2517	2523
25°	2531	2446	2456
30°	2464	2379	2371
35°	2402	2300	2281
40°	2324	2221	2195
45°	2247	2141	2107
50°	2163	2057	2005
55°	2075	1960	1912
60°	1975	1846	1805
65°	1866	1727	1679
70°	1728	1582	1543
75°	1536	1408	1417
80°	1305	1187	1177
85°	945	806	781

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2247 cd/sqm



TEST NUMBER: P915710

CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.1	2.6
10°-20°	897.9	7.4
20°-30°	1319.6	10.9
30°-40°	1532.6	12.6
40°-50°	1530.7	12.6
50°-60°	1334.7	11.0
60°-70°	986.7	8.1
70°-80°	558.2	4.6
80°-90°	150.9	1.2
90°-100°	77.5	0.6
100°-110°	246.3	2.0
110°-120°	421.5	3.5
120°-130°	554.3	4.6
130°-140°	622.2	5.1
140°-150°	610.1	5.0
150°-160°	511.8	4.2
160°-170°	339.4	2.8
170°-180°	118.6	1.0
0°-30°	2536.6	20.9
0°-40°	4069.2	33.5
0°-60°	6934.6	57.2
0°-90°	8630.4	71.1
90°-120°	745.3	6.1
90°-150°	2532.0	20.9
90°-180°	3502.0	28.9
0°-180°	12132.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3391	3391	3391	3391	3391	
5°	3391	3378	3342	3368	3362	322
15°	3228	3208	3166	3179	3163	909
25°	2921	2895	2840	2846	2840	1344
35°	2520	2488	2436	2416	2400	1574
45°	2051	2028	1979	1943	1930	1583
55°	1552	1532	1493	1454	1438	1388
65°	1047	1027	994	965	949	1035
75°	548	541	525	505	512	585
85°	134	130	127	117	114	149
90°	1	14	37	35	36	12
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P915710

CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3390.7	3390.7	3390.7	3390.7	3390.7
2.5°	3410.3	3394.1	3358.1	3390.7	3384.4
5°	3390.7	3377.9	3341.9	3367.8	3361.6
7.5°	3367.8	3348.5	3312.5	3338.8	3332.2
10°	3332.2	3309.3	3270.3	3296.2	3286.5
12.5°	3283.1	3263.7	3224.7	3240.9	3234.3
15°	3227.7	3208.3	3165.8	3178.9	3162.7
17.5°	3159.2	3139.9	3097.3	3113.6	3097.3
20°	3084.2	3064.8	3019.2	3028.8	3016.1
22.5°	3009.5	2980.0	2937.5	2937.5	2930.9
25°	2921.2	2895.3	2840.0	2846.2	2840.0
27.5°	2823.3	2800.5	2758.3	2748.6	2732.4
30°	2725.8	2699.5	2650.7	2641.1	2627.9
32.5°	2621.3	2602.0	2549.7	2530.0	2516.8
35°	2520.3	2487.8	2435.6	2415.8	2399.6
37.5°	2406.2	2376.8	2324.6	2301.7	2285.4
40°	2288.9	2262.6	2210.4	2181.4	2168.2
42.5°	2174.8	2148.5	2096.6	2063.7	2044.4
45°	2051.0	2028.1	1978.9	1943.4	1930.2
47.5°	1930.2	1907.4	1855.1	1819.2	1799.8
50°	1802.9	1786.7	1741.0	1695.3	1679.1
52.5°	1679.1	1656.2	1614.1	1578.0	1555.2
55°	1552.1	1532.4	1493.3	1454.2	1438.0
57.5°	1424.8	1408.6	1366.0	1326.9	1313.8
60°	1297.5	1284.8	1239.1	1203.1	1193.4
62.5°	1173.7	1150.9	1118.3	1085.8	1072.7
65°	1046.7	1027.0	994.5	965.1	948.9
67.5°	916.3	899.8	870.7	847.9	834.7
70°	795.6	782.4	753.0	730.2	717.4
72.5°	671.8	658.6	642.4	619.6	609.8
75°	547.6	541.4	524.7	505.4	512.0
77.5°	436.9	423.7	417.2	407.5	397.8
80°	326.2	322.7	316.2	306.5	299.9
82.5°	221.7	221.7	218.6	205.5	205.5
85°	133.6	130.4	127.3	117.2	114.2
87.5°	58.8	52.2	45.6	36.0	32.5
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5



TEST NUMBER: P915710

CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P915710
 CATALOG NUMBER: DFN2DIP-TR4F0-110D050US927-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	13.55	13.22	14.33	15.26	12.03	13.12	12.78	13.90	14.83
	3H	14.14	15.12	14.91	15.90	16.87	13.67	14.65	14.43	15.43	16.40
	4H	14.74	15.66	15.52	16.46	17.43	14.27	15.19	15.05	15.98	16.96
	6H	15.15	16.00	15.95	16.80	17.79	14.68	15.53	15.47	16.33	17.32
	8H	15.26	16.07	16.07	16.89	17.89	14.79	15.60	15.59	16.42	17.41
	12H	15.32	16.09	16.13	16.91	17.92	14.84	15.61	15.65	16.43	17.44
4H	2H	12.95	13.88	13.74	14.67	15.65	12.61	13.53	13.40	14.33	15.30
	3H	14.84	15.61	15.64	16.44	17.43	14.45	15.22	15.25	16.05	17.04
	4H	15.56	16.27	16.38	17.09	18.11	15.16	15.86	15.97	16.69	17.71
	6H	16.09	16.70	16.92	17.55	18.58	15.68	16.29	16.51	17.14	18.17
	8H	16.25	16.81	17.08	17.66	18.70	15.83	16.40	16.67	17.25	18.29
	12H	16.33	16.84	17.18	17.71	18.75	15.91	16.42	16.76	17.29	18.33
8H	4H	15.78	16.35	16.61	17.19	18.23	15.42	15.99	16.25	16.83	17.87
	6H	16.42	16.89	17.28	17.78	18.82	16.06	16.53	16.92	17.42	18.45
	8H	16.64	17.06	17.51	17.94	19.00	16.27	16.69	17.15	17.57	18.63
	12H	16.78	17.15	17.66	18.03	19.14	16.40	16.77	17.28	17.64	18.75
12H	4H	15.77	16.29	16.63	17.15	18.20	15.42	15.93	16.28	16.80	17.85
	6H	16.45	16.87	17.32	17.75	18.81	16.10	16.52	16.97	17.40	18.46
	8H	16.70	17.07	17.58	17.95	19.06	16.35	16.72	17.22	17.59	18.70