

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921180

Luminaire Tested: DFN2DIP-TR4F0-110D080US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921180
REPORT IS A COMBINATION OF REPORTS P900456 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D080US935-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14146.2 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 171.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27
7	61	49	41	35	57	46	39	34	40	35	31	35	31	28	31	27	25
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20
10	49	37	30	26	46	35	29	24	32	26	22	28	24	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3110	3110	3110
5°	3115	3060	3080
10°	3084	3000	2979
15°	3041	2901	2824
20°	2985	2764	2634
25°	2928	2611	2451
30°	2851	2454	2218
35°	2775	2285	2013
40°	2698	2110	1779
45°	2609	1916	1566
50°	2516	1721	1358
55°	2420	1511	1159
60°	2308	1293	954
65°	2179	1070	858
70°	2024	863	777
75°	1828	761	706
80°	1544	638	612
85°	1076	425	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2609 cd/sqm

TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	2.6
10°-20°	1007.1	7.1
20°-30°	1413.9	10.0
30°-40°	1541.3	10.9
40°-50°	1416.6	10.0
50°-60°	1112.5	7.9
60°-70°	724.2	5.1
70°-80°	372.8	2.6
80°-90°	101.4	0.7
90°-100°	134.8	1.0
100°-110°	428.3	3.0
110°-120°	733.0	5.2
120°-130°	964.0	6.8
130°-140°	1082.0	7.6
140°-150°	1061.0	7.5
150°-160°	890.1	6.3
160°-170°	590.3	4.2
170°-180°	206.3	1.5
0°-30°	2787.9	19.7
0°-40°	4329.1	30.6
0°-60°	6858.3	48.5
0°-90°	8056.5	57.0
90°-120°	1296.1	9.2
90°-150°	4403.1	31.1
90°-180°	6090.0	43.1
0°-180°	14146.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3914	3914	3914	3914	3914	
5°	3914	3897	3850	3882	3872	371
15°	3723	3684	3564	3496	3461	1049
25°	3380	3266	3032	2887	2834	1554
35°	2912	2731	2420	2196	2118	1823
45°	2381	2143	1771	1520	1435	1838
55°	1810	1534	1151	939	872	1617
65°	1222	935	616	496	485	1212
75°	652	404	283	259	255	689
85°	152	78	67	67	67	175
90°	2	24	64	60	62	14
95°	96	114	118	118	114	107
105°	395	401	405	408	408	417
115°	736	746	743	741	736	728
125°	1070	1086	1081	1075	1073	956
135°	1384	1404	1408	1406	1401	1070
145°	1680	1693	1704	1706	1698	1050
155°	1921	1926	1932	1941	1935	884
165°	2090	2088	2088	2101	2092	590
175°	2174	2169	2165	2178	2167	207
180°	2178	2178	2178	2178	2178	

TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3914.4	3914.4	3914.4	3914.4	3914.4
2.5°	3932.0	3914.4	3875.3	3911.0	3903.9
5°	3914.4	3896.7	3850.5	3882.4	3871.9
7.5°	3882.4	3861.3	3811.7	3825.7	3807.9
10°	3840.0	3815.1	3744.5	3733.5	3712.5
12.5°	3786.9	3755.0	3659.2	3638.1	3599.0
15°	3723.0	3684.0	3563.7	3496.4	3461.0
17.5°	3648.7	3591.9	3443.0	3365.2	3308.5
20°	3563.7	3492.6	3315.6	3227.3	3149.1
22.5°	3471.6	3390.0	3184.5	3064.2	3011.2
25°	3379.5	3266.0	3032.3	2887.2	2833.8
27.5°	3269.8	3149.1	2890.5	2724.0	2642.5
30°	3152.9	3018.0	2734.6	2554.2	2458.3
32.5°	3039.4	2876.2	2586.1	2373.4	2284.7
35°	2912.0	2731.2	2419.7	2196.4	2118.2
37.5°	2788.0	2592.9	2263.6	2019.0	1930.7
40°	2656.8	2444.5	2100.6	1849.1	1757.0
42.5°	2522.2	2295.6	1937.8	1675.5	1587.2
45°	2380.6	2143.0	1771.3	1519.5	1434.6
47.5°	2246.0	1994.6	1612.0	1360.1	1282.4
50°	2097.1	1845.7	1456.0	1211.3	1137.3
52.5°	1951.7	1686.0	1307.2	1073.4	1006.1
55°	1810.0	1533.8	1151.2	938.8	871.6
57.5°	1665.0	1381.6	1013.2	814.8	758.0
60°	1516.1	1232.8	867.8	687.4	630.7
62.5°	1371.1	1087.7	743.8	573.9	545.7
65°	1222.2	935.0	616.4	496.1	485.2
67.5°	1080.6	793.4	496.1	435.6	425.1
70°	931.7	655.5	410.8	375.5	361.2
72.5°	790.0	527.7	343.5	315.3	308.2
75°	651.7	403.6	283.4	258.6	255.2
77.5°	513.8	286.8	223.3	209.0	201.8
80°	386.0	205.6	169.9	156.0	156.0
82.5°	269.1	138.3	116.9	109.8	109.8
85°	152.2	77.8	67.2	67.2	67.2
87.5°	56.7	28.2	28.2	24.8	24.8
90°	2.0	23.7	64.4	60.4	62.4
92.5°	40.7	55.2	57.2	59.1	59.1
95°	95.9	114.3	117.5	117.5	114.3
97.5°	159.6	176.7	183.9	183.9	183.9
100°	233.2	248.2	253.5	253.5	251.5
102.5°	310.6	321.8	329.0	331.0	329.0
105°	395.4	400.6	404.6	407.9	407.9
107.5°	479.4	487.3	487.3	488.6	479.4
110°	560.9	571.4	571.4	571.4	566.1

TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	648.8	660.0	658.1	652.8	648.8
115°	735.6	746.1	742.8	740.8	735.6
117.5°	821.6	836.0	826.8	821.6	816.3
120°	908.3	922.7	908.3	908.3	902.3
122.5°	987.0	1005.5	996.3	991.0	987.0
125°	1069.8	1086.2	1081.0	1075.0	1073.1
127.5°	1150.6	1171.0	1163.7	1155.9	1150.6
130°	1226.1	1249.7	1246.5	1242.6	1235.4
132.5°	1310.9	1329.2	1330.6	1321.4	1316.1
135°	1383.7	1404.1	1408.1	1406.1	1400.8
137.5°	1465.2	1481.6	1484.9	1483.6	1475.7
140°	1536.8	1553.2	1562.4	1562.4	1555.1
142.5°	1610.3	1626.8	1632.0	1634.0	1626.8
145°	1680.0	1693.1	1703.6	1705.6	1698.3
147.5°	1742.3	1758.8	1766.6	1770.0	1762.7
150°	1806.7	1817.8	1825.1	1831.0	1825.1
152.5°	1863.8	1875.0	1884.2	1891.4	1884.2
155°	1921.0	1926.2	1932.2	1941.3	1935.4
157.5°	1970.2	1974.2	1977.5	1990.5	1981.4
160°	2014.2	2018.2	2020.2	2031.3	2023.4
162.5°	2054.9	2054.9	2056.9	2069.4	2060.2
165°	2089.7	2087.7	2087.7	2100.9	2091.7
167.5°	2121.2	2115.4	2115.4	2128.5	2119.3
170°	2144.9	2139.7	2137.7	2150.9	2139.7
172.5°	2161.4	2156.1	2154.1	2167.2	2156.1
175°	2174.5	2169.2	2165.2	2178.4	2167.2
177.5°	2181.7	2176.4	2172.5	2183.7	2172.5
180°	2178.4	2178.4	2178.4	2178.4	2178.4

TEST NUMBER: P921180

CATALOG NUMBER: DFN2DIP-TR4F0-110D080US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.71	12.60	12.61	13.52	14.69	7.68	8.57	8.58	9.49	10.66
	3H	13.39	14.19	14.30	15.11	16.31	8.88	9.67	9.79	10.60	11.79
	4H	14.00	14.75	14.93	15.68	16.89	9.33	10.08	10.26	11.01	12.22
	6H	14.43	15.12	15.37	16.06	17.27	9.65	10.35	10.60	11.28	12.50
	8H	14.55	15.21	15.50	16.17	17.38	9.75	10.41	10.70	11.36	12.58
	12H	14.62	15.24	15.57	16.19	17.43	9.79	10.42	10.75	11.37	12.61
4H	2H	11.73	12.49	12.67	13.42	14.62	8.28	9.04	9.22	9.97	11.17
	3H	13.57	14.19	14.51	15.16	16.38	9.64	10.27	10.59	11.23	12.45
	4H	14.26	14.83	15.22	15.79	17.03	10.19	10.76	11.15	11.72	12.96
	6H	14.78	15.27	15.75	16.25	17.50	10.62	11.11	11.58	12.09	13.33
	8H	14.96	15.42	15.93	16.39	17.65	10.75	11.20	11.72	12.18	13.44
	12H	15.05	15.47	16.04	16.46	17.72	10.81	11.23	11.80	12.22	13.48
8H	4H	14.24	14.69	15.20	15.67	16.92	10.48	10.93	11.45	11.91	13.17
	6H	14.80	15.18	15.80	16.20	17.45	11.00	11.38	11.99	12.39	13.65
	8H	15.02	15.35	16.02	16.36	17.63	11.19	11.52	12.19	12.53	13.80
	12H	15.16	15.45	16.17	16.45	17.77	11.31	11.61	12.32	12.60	13.93
12H	4H	14.19	14.60	15.18	15.59	16.86	10.48	10.90	11.47	11.89	13.15
	6H	14.78	15.11	15.78	16.12	17.39	11.05	11.38	12.05	12.39	13.66
	8H	15.00	15.30	16.01	16.29	17.61	11.26	11.56	12.27	12.55	13.87

END OF REPORT