

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918249

Luminaire Tested: DFN2DIP-TR4F0-050D110US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918249
REPORT IS A COMBINATION OF REPORTS P902018 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D110US930-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12343.6 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 126.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	43	39	35	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1338	1338	1338
5°	1341	1317	1326
10°	1327	1291	1282
15°	1309	1249	1216
20°	1285	1190	1134
25°	1260	1124	1055
30°	1227	1056	955
35°	1194	984	866
40°	1161	908	766
45°	1123	825	674
50°	1083	741	585
55°	1041	651	499
60°	993	556	410
65°	938	461	370
70°	871	371	334
75°	787	327	304
80°	665	274	263
85°	463	183	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1606 cd/sqm

TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.3
10°-20°	433.5	3.5
20°-30°	608.6	4.9
30°-40°	663.4	5.4
40°-50°	609.7	4.9
50°-60°	478.8	3.9
60°-70°	311.7	2.5
70°-80°	160.4	1.3
80°-90°	46.3	0.4
90°-100°	99.8	0.8
100°-110°	372.1	3.0
110°-120°	986.7	8.0
120°-130°	1636.6	13.3
130°-140°	1738.4	14.1
140°-150°	1615.7	13.1
150°-160°	1298.9	10.5
160°-170°	837.0	6.8
170°-180°	288.1	2.3
0°-30°	1200.0	9.7
0°-40°	1863.4	15.1
0°-60°	2951.9	23.9
0°-90°	3470.3	28.1
90°-120°	1458.6	11.8
90°-150°	6449.2	52.2
90°-180°	8873.0	71.9
0°-180°	12343.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	2	26	44	55	59	11
95°	142	70	85	96	94	169
105°	666	732	134	158	166	711
115°	1259	1296	1351	337	180	1240
125°	1780	1809	1851	1866	1872	1588
135°	2203	2238	2258	2280	2276	1702
145°	2556	2554	2591	2606	2595	1599
155°	2814	2795	2821	2834	2816	1297
165°	2965	2952	2959	2974	2959	838
175°	3033	3018	3022	3038	3016	289
180°	3027	3027	3027	3027	3027	

TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	2.1	26.3	43.7	54.9	59.0
92.5°	54.9	46.1	52.5	57.0	59.0
95°	142.3	70.0	85.3	96.4	94.2
97.5°	256.2	76.7	111.5	118.3	120.4
100°	387.8	87.6	124.8	142.3	146.7
102.5°	532.1	527.9	129.2	153.2	160.0
105°	665.8	731.6	133.7	157.6	166.5
107.5°	821.3	875.9	138.1	162.0	170.9
110°	970.3	1016.1	383.4	164.4	172.9

TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1110.5	1149.7	1112.6	168.5	175.3
115°	1259.2	1296.4	1351.4	337.3	179.7
117.5°	1388.5	1432.2	1469.7	1156.3	582.5
120°	1533.1	1565.9	1605.4	1631.7	1335.9
122.5°	1655.6	1690.7	1734.6	1747.7	1750.0
125°	1780.4	1809.1	1850.6	1866.0	1872.5
127.5°	1894.3	1925.0	1958.0	1979.9	1982.0
130°	2001.7	2036.9	2060.7	2085.0	2082.9
132.5°	2111.2	2139.8	2163.8	2183.5	2181.5
135°	2203.3	2238.4	2257.9	2280.1	2275.6
137.5°	2299.5	2325.8	2347.9	2369.7	2363.2
140°	2393.7	2411.3	2435.3	2455.0	2444.1
142.5°	2472.7	2488.0	2516.4	2533.9	2522.9
145°	2556.0	2553.6	2590.8	2606.2	2595.3
147.5°	2628.0	2621.5	2658.7	2669.6	2661.1
150°	2698.2	2682.9	2718.0	2731.0	2720.1
152.5°	2757.3	2739.8	2772.6	2785.9	2770.5
155°	2814.2	2794.7	2820.9	2834.0	2816.5
157.5°	2860.2	2842.8	2862.6	2877.9	2860.2
160°	2899.8	2886.5	2899.8	2912.7	2897.4
162.5°	2934.6	2921.6	2932.5	2947.9	2928.1
165°	2965.3	2952.3	2958.8	2974.1	2958.8
167.5°	2989.5	2976.2	2983.0	2998.3	2978.6
170°	3009.3	2996.0	3000.4	3015.8	2996.0
172.5°	3022.2	3009.3	3013.7	3029.0	3009.3
175°	3033.2	3017.8	3022.2	3037.6	3015.8
177.5°	3037.6	3022.2	3024.6	3039.9	3020.2
180°	3026.7	3026.7	3026.7	3026.7	3026.7

TEST NUMBER: P918249

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.66	6.34	6.79	7.45	9.01	1.63	2.31	2.76	3.43	4.98
	3H	7.32	7.93	8.46	9.06	10.63	2.81	3.42	3.95	4.54	6.11
	4H	7.92	8.50	9.07	9.63	11.20	3.25	3.83	4.40	4.96	6.53
	6H	8.34	8.87	9.49	10.00	11.58	3.57	4.10	4.72	5.22	6.81
	8H	8.46	8.96	9.62	10.11	11.69	3.65	4.16	4.81	5.30	6.88
	12H	8.52	8.99	9.68	10.13	11.73	3.69	4.17	4.85	5.31	6.91
4H	2H	5.66	6.23	6.81	7.36	8.94	2.21	2.78	3.36	3.91	5.49
	3H	7.47	7.95	8.63	9.10	10.69	3.54	4.02	4.70	5.18	6.76
	4H	8.16	8.60	9.32	9.74	11.35	4.09	4.53	5.25	5.67	7.28
	6H	8.66	9.04	9.83	10.21	11.80	4.50	4.88	5.67	6.04	7.64
	8H	8.84	9.19	10.00	10.34	11.96	4.62	4.98	5.79	6.13	7.75
	12H	8.92	9.24	10.11	10.41	12.03	4.68	5.00	5.86	6.17	7.79
8H	4H	8.11	8.47	9.28	9.62	11.24	4.36	4.71	5.52	5.86	7.48
	6H	8.67	8.96	9.86	10.16	11.77	4.87	5.16	6.05	6.36	7.97
	8H	8.89	9.14	10.08	10.32	11.95	5.06	5.31	6.25	6.49	8.12
	12H	9.02	9.24	10.22	10.42	12.08	5.17	5.39	6.37	6.57	8.23
12H	4H	8.06	8.38	9.24	9.55	11.16	4.35	4.67	5.54	5.84	7.46
	6H	8.65	8.90	9.84	10.08	11.71	4.92	5.17	6.11	6.35	7.98
	8H	8.86	9.09	10.06	10.26	11.92	5.12	5.34	6.32	6.52	8.18

END OF REPORT