

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923644

Luminaire Tested: DFN2DIP-TR4F0-040D050US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923644
REPORT IS A COMBINATION OF REPORTS P900388 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D050US940-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6977.6 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 69.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1171	1171	1171
5°	1173	1153	1160
10°	1161	1130	1122
15°	1145	1093	1064
20°	1124	1041	992
25°	1103	983	923
30°	1074	924	835
35°	1045	860	758
40°	1016	795	670
45°	982	722	590
50°	948	648	512
55°	911	569	436
60°	869	487	359
65°	821	403	323
70°	762	325	292
75°	688	286	266
80°	581	240	231
85°	405	160	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1100 cd/sqm

TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.0
10°-20°	379.3	5.4
20°-30°	532.5	7.6
30°-40°	580.5	8.3
40°-50°	533.5	7.6
50°-60°	419.0	6.0
60°-70°	272.7	3.9
70°-80°	140.4	2.0
80°-90°	39.8	0.6
90°-100°	87.3	1.3
100°-110°	277.2	4.0
110°-120°	474.5	6.8
120°-130°	624.0	8.9
130°-140°	700.4	10.0
140°-150°	686.8	9.8
150°-160°	576.1	8.3
160°-170°	382.1	5.5
170°-180°	133.5	1.9
0°-30°	1049.9	15.0
0°-40°	1630.4	23.4
0°-60°	2582.9	37.0
0°-90°	3035.8	43.5
90°-120°	838.9	12.0
90°-150°	2850.1	40.8
90°-180°	3942.0	56.5
0°-180°	6977.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	15	42	39	40	7
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	

TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4

TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1

TEST NUMBER: P923644

CATALOG NUMBER: DFN2DIP-TR4F0-040D050US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.05	7.83	8.07	8.85	10.22	3.02	3.80	4.04	4.83	6.19
	3H	8.72	9.42	9.75	10.45	11.84	4.21	4.91	5.24	5.94	7.32
	4H	9.33	9.99	10.37	11.02	12.42	4.66	5.32	5.70	6.35	7.74
	6H	9.75	10.36	10.80	11.39	12.80	4.98	5.59	6.03	6.62	8.03
	8H	9.87	10.45	10.93	11.51	12.90	5.07	5.65	6.12	6.70	8.10
	12H	9.93	10.48	10.99	11.53	12.95	5.11	5.66	6.17	6.71	8.13
4H	2H	7.06	7.72	8.11	8.76	10.15	3.61	4.27	4.66	5.31	6.70
	3H	8.89	9.44	9.94	10.50	11.90	4.96	5.51	6.01	6.57	7.97
	4H	9.58	10.08	10.64	11.13	12.56	5.51	6.01	6.57	7.06	8.49
	6H	10.09	10.52	11.16	11.60	13.02	5.92	6.36	6.99	7.43	8.85
	8H	10.26	10.67	11.33	11.73	13.17	6.05	6.46	7.12	7.52	8.96
	12H	10.36	10.72	11.44	11.80	13.24	6.12	6.48	7.20	7.56	9.00
8H	4H	9.54	9.94	10.61	11.01	12.45	5.78	6.19	6.85	7.25	8.69
	6H	10.11	10.44	11.20	11.55	12.98	6.30	6.63	7.39	7.74	9.18
	8H	10.32	10.61	11.42	11.71	13.16	6.49	6.78	7.59	7.88	9.33
	12H	10.46	10.71	11.56	11.80	13.30	6.61	6.87	7.71	7.95	9.45
12H	4H	9.49	9.85	10.58	10.94	12.38	5.79	6.15	6.87	7.23	8.67
	6H	10.08	10.37	11.18	11.47	12.92	6.35	6.64	7.45	7.73	9.19
	8H	10.30	10.56	11.40	11.64	13.14	6.56	6.82	7.66	7.90	9.40