

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923664

Luminaire Tested: DFN2DIP-TR4F0-040D100US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923664
REPORT IS A COMBINATION OF REPORTS P900478 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D100US940-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10923.5 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 108.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	23
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	29	26	24	21	19	17
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1171	1171	1171
5°	1173	1153	1160
10°	1161	1130	1122
15°	1145	1093	1064
20°	1124	1041	992
25°	1103	983	923
30°	1074	924	835
35°	1045	860	758
40°	1016	795	670
45°	982	722	590
50°	948	648	512
55°	911	569	436
60°	869	487	359
65°	821	403	323
70°	762	325	292
75°	688	286	266
80°	581	240	231
85°	405	160	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2199 cd/sqm

TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	1.3
10°-20°	379.3	3.5
20°-30°	532.5	4.9
30°-40°	580.5	5.3
40°-50°	533.5	4.9
50°-60°	419.0	3.8
60°-70°	272.7	2.5
70°-80°	140.4	1.3
80°-90°	43.9	0.4
90°-100°	174.5	1.6
100°-110°	554.5	5.1
110°-120°	948.9	8.7
120°-130°	1247.9	11.4
130°-140°	1400.8	12.8
140°-150°	1373.6	12.6
150°-160°	1152.3	10.5
160°-170°	764.1	7.0
170°-180°	267.1	2.4
0°-30°	1049.9	9.6
0°-40°	1630.4	14.9
0°-60°	2582.9	23.6
0°-90°	3039.8	27.8
90°-120°	1677.9	15.4
90°-150°	5700.1	52.2
90°-180°	7884.0	72.2
0°-180°	10923.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	3	31	83	78	81	11
95°	124	148	152	152	148	138
105°	512	519	524	528	528	540
115°	952	966	962	959	952	942
125°	1385	1406	1400	1392	1389	1238
135°	1791	1818	1823	1820	1814	1385
145°	2175	2192	2206	2208	2199	1359
155°	2487	2494	2501	2513	2506	1145
165°	2705	2703	2703	2720	2708	763
175°	2815	2808	2803	2820	2806	267
180°	2820	2820	2820	2820	2820	

TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	2.6	30.6	83.3	78.2	80.8
92.5°	52.7	71.4	74.0	76.5	76.5
95°	124.1	147.9	152.2	152.2	147.9
97.5°	206.6	228.7	238.1	238.1	238.1
100°	301.8	321.4	328.1	328.1	325.7
102.5°	402.2	416.6	426.0	428.5	426.0
105°	511.8	518.6	523.7	528.0	528.0
107.5°	620.6	630.9	630.9	632.6	620.6
110°	726.1	739.7	739.7	739.7	732.9

TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	840.0	854.4	851.9	845.1	840.0
115°	952.3	965.8	961.6	959.0	952.3
117.5°	1063.6	1082.4	1070.4	1063.6	1056.8
120°	1175.8	1194.5	1175.8	1175.8	1168.2
122.5°	1277.8	1301.6	1289.8	1283.0	1277.8
125°	1385.0	1406.2	1399.5	1391.8	1389.3
127.5°	1489.6	1515.9	1506.5	1496.4	1489.6
130°	1587.3	1617.9	1613.7	1608.6	1599.3
132.5°	1697.0	1720.8	1722.5	1710.7	1703.8
135°	1791.4	1817.8	1822.8	1820.3	1813.5
137.5°	1896.8	1918.1	1922.3	1920.7	1910.4
140°	1989.5	2010.7	2022.7	2022.7	2013.3
142.5°	2084.7	2106.0	2112.7	2115.3	2106.0
145°	2174.8	2191.8	2205.5	2208.0	2198.6
147.5°	2255.6	2276.9	2287.1	2291.3	2282.0
150°	2339.0	2353.4	2362.8	2370.3	2362.8
152.5°	2412.9	2427.3	2439.3	2448.6	2439.3
155°	2486.9	2493.7	2501.3	2513.2	2505.5
157.5°	2550.6	2555.7	2560.0	2577.0	2565.1
160°	2607.6	2612.7	2615.2	2629.7	2619.5
162.5°	2660.3	2660.3	2662.8	2679.0	2667.1
165°	2705.4	2702.8	2702.8	2719.8	2707.9
167.5°	2746.2	2738.5	2738.5	2755.6	2743.6
170°	2776.8	2770.0	2767.4	2784.5	2770.0
172.5°	2798.0	2791.2	2788.6	2805.7	2791.2
175°	2815.0	2808.3	2803.2	2820.1	2805.7
177.5°	2824.4	2817.6	2812.5	2826.9	2812.5
180°	2820.1	2820.1	2820.1	2820.1	2820.1

TEST NUMBER: P923664

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.15	5.82	6.28	6.94	8.50	1.12	1.80	2.25	2.92	4.48
	3H	6.81	7.42	7.95	8.55	10.12	2.30	2.90	3.44	4.03	5.61
	4H	7.41	7.99	8.56	9.12	10.70	2.74	3.32	3.89	4.45	6.02
	6H	7.83	8.36	8.98	9.49	11.08	3.06	3.58	4.21	4.72	6.31
	8H	7.95	8.45	9.11	9.60	11.18	3.14	3.65	4.30	4.79	6.37
	12H	8.01	8.48	9.17	9.62	11.23	3.18	3.66	4.34	4.80	6.40
4H	2H	5.15	5.72	6.30	6.85	8.43	1.70	2.27	2.85	3.40	4.98
	3H	6.96	7.44	8.12	8.59	10.19	3.03	3.51	4.19	4.67	6.26
	4H	7.65	8.09	8.81	9.23	10.84	3.58	4.02	4.74	5.16	6.77
	6H	8.15	8.53	9.32	9.70	11.30	3.99	4.37	5.16	5.53	7.13
	8H	8.33	8.68	9.49	9.83	11.45	4.12	4.47	5.28	5.62	7.24
	12H	8.41	8.73	9.60	9.90	11.52	4.17	4.49	5.36	5.66	7.28
8H	4H	7.60	7.96	8.77	9.11	10.73	3.85	4.20	5.01	5.35	6.97
	6H	8.16	8.45	9.35	9.65	11.27	4.36	4.65	5.55	5.85	7.46
	8H	8.38	8.63	9.57	9.81	11.44	4.55	4.80	5.74	5.98	7.61
	12H	8.51	8.73	9.71	9.91	11.58	4.66	4.88	5.86	6.06	7.73
12H	4H	7.55	7.87	8.73	9.04	10.66	3.84	4.16	5.03	5.33	6.95
	6H	8.14	8.39	9.33	9.57	11.20	4.41	4.66	5.60	5.84	7.47
	8H	8.35	8.57	9.55	9.75	11.42	4.61	4.83	5.81	6.01	7.68

END OF REPORT