

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923692

Luminaire Tested: DFN2DIP-TR4F0-050D080US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923692
REPORT IS A COMBINATION OF REPORTS P900444 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D080US940-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10103.1 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 101.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1464	1464	1464
5°	1466	1441	1450
10°	1452	1412	1403
15°	1432	1366	1330
20°	1405	1301	1240
25°	1378	1229	1154
30°	1342	1155	1044
35°	1306	1076	948
40°	1270	993	837
45°	1228	902	737
50°	1185	810	639
55°	1139	711	546
60°	1086	608	449
65°	1026	504	404
70°	953	406	366
75°	861	358	332
80°	727	300	288
85°	507	201	217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1758 cd/sqm

TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.7
10°-20°	474.1	4.7
20°-30°	665.6	6.6
30°-40°	725.6	7.2
40°-50°	666.9	6.6
50°-60°	523.7	5.2
60°-70°	340.9	3.4
70°-80°	175.5	1.7
80°-90°	51.2	0.5
90°-100°	139.6	1.4
100°-110°	443.6	4.4
110°-120°	759.1	7.5
120°-130°	998.3	9.9
130°-140°	1120.6	11.1
140°-150°	1098.9	10.9
150°-160°	921.8	9.1
160°-170°	611.3	6.1
170°-180°	213.7	2.1
0°-30°	1312.4	13.0
0°-40°	2038.0	20.2
0°-60°	3228.6	32.0
0°-90°	3796.2	37.6
90°-120°	1342.3	13.3
90°-150°	4560.1	45.1
90°-180°	6307.0	62.4
0°-180°	10103.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	2	24	67	63	65	10
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	

TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3

TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1



TEST NUMBER: P923692

CATALOG NUMBER: DFN2DIP-TR4F0-050D080US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.18	7.92	8.24	8.98	10.42	3.15	3.89	4.22	4.95	6.39
	3H	8.85	9.51	9.92	10.58	12.04	4.34	5.00	5.41	6.07	7.53
	4H	9.45	10.08	10.54	11.15	12.62	4.78	5.41	5.87	6.48	7.95
	6H	9.87	10.45	10.96	11.52	13.00	5.10	5.68	6.19	6.75	8.23
	8H	9.99	10.54	11.09	11.63	13.10	5.19	5.74	6.28	6.83	8.30
	12H	10.05	10.57	11.15	11.66	13.15	5.23	5.75	6.33	6.83	8.33
4H	2H	7.19	7.81	8.28	8.88	10.35	3.74	4.36	4.83	5.44	6.90
	3H	9.01	9.53	10.10	10.63	12.11	5.08	5.60	6.18	6.70	8.18
	4H	9.70	10.17	10.80	11.26	12.76	5.63	6.10	6.73	7.19	8.69
	6H	10.21	10.61	11.32	11.73	13.22	6.04	6.45	7.15	7.56	9.05
	8H	10.38	10.76	11.49	11.87	13.37	6.17	6.55	7.28	7.65	9.16
	12H	10.47	10.82	11.60	11.93	13.45	6.23	6.57	7.36	7.69	9.20
8H	4H	9.66	10.04	10.77	11.14	12.65	5.90	6.28	7.01	7.38	8.89
	6H	10.22	10.53	11.35	11.68	13.19	6.41	6.73	7.55	7.88	9.38
	8H	10.44	10.71	11.57	11.84	13.36	6.61	6.88	7.74	8.01	9.53
	12H	10.57	10.81	11.71	11.94	13.50	6.72	6.96	7.86	8.09	9.65
12H	4H	9.60	9.95	10.73	11.07	12.58	5.90	6.24	7.03	7.36	8.87
	6H	10.20	10.47	11.33	11.60	13.12	6.46	6.74	7.60	7.87	9.39
	8H	10.41	10.65	11.55	11.78	13.34	6.67	6.91	7.81	8.04	9.60

END OF REPORT