

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923726

Luminaire Tested: DFN2DIP-TR4F0-060D080US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923726
REPORT IS A COMBINATION OF REPORTS P900445 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-060D080US940-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11610.1 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 112.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923726
CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P923726

CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1654	1654	1654
5°	1657	1631	1642
10°	1643	1609	1619
15°	1619	1582	1585
20°	1586	1545	1549
25°	1554	1501	1508
30°	1513	1460	1456
35°	1475	1412	1400
40°	1427	1363	1348
45°	1380	1314	1294
50°	1328	1263	1231
55°	1274	1204	1174
60°	1213	1133	1108
65°	1146	1060	1031
70°	1061	971	947
75°	943	865	870
80°	801	729	723
85°	579	494	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1758 cd/sqm



TEST NUMBER: P923726

CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	1.7
10°-20°	551.3	4.7
20°-30°	810.2	7.0
30°-40°	941.0	8.1
40°-50°	939.8	8.1
50°-60°	819.5	7.1
60°-70°	605.8	5.2
70°-80°	342.7	3.0
80°-90°	96.9	0.8
90°-100°	139.6	1.2
100°-110°	443.6	3.8
110°-120°	759.1	6.5
120°-130°	998.3	8.6
130°-140°	1120.6	9.7
140°-150°	1098.9	9.5
150°-160°	921.8	7.9
160°-170°	611.3	5.3
170°-180°	213.7	1.8
0°-30°	1557.4	13.4
0°-40°	2498.4	21.5
0°-60°	4257.8	36.7
0°-90°	5303.2	45.7
90°-120°	1342.3	11.6
90°-150°	4560.1	39.3
90°-180°	6307.0	54.3
0°-180°	11610.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2074	2052	2068	2064	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	825
35°	1548	1528	1495	1483	1473	966
45°	1259	1245	1215	1193	1185	972
55°	953	941	917	893	883	852
65°	643	631	611	592	583	635
75°	336	332	322	310	314	359
85°	82	80	78	72	70	91
90°	2	24	67	63	65	11
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	



TEST NUMBER: P923726

CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2081.8	2081.8	2081.8	2081.8	2081.8
2.5°	2093.9	2083.9	2061.8	2081.8	2078.0
5°	2081.8	2073.9	2051.8	2067.8	2064.0
7.5°	2067.8	2055.9	2033.8	2050.0	2045.9
10°	2045.9	2031.9	2007.9	2023.8	2017.9
12.5°	2015.8	2003.9	1979.9	1989.9	1985.8
15°	1981.7	1969.9	1943.8	1951.9	1941.9
17.5°	1939.7	1927.9	1901.8	1911.6	1901.8
20°	1893.6	1881.8	1853.7	1859.7	1851.8
22.5°	1847.8	1829.7	1803.6	1803.6	1799.6
25°	1793.6	1777.7	1743.7	1747.5	1743.7
27.5°	1733.5	1719.5	1693.5	1687.7	1677.7
30°	1673.7	1657.4	1627.5	1621.6	1613.5
32.5°	1609.4	1597.6	1565.5	1553.4	1545.3
35°	1547.5	1527.5	1495.4	1483.3	1473.3
37.5°	1477.4	1459.3	1427.3	1413.2	1403.2
40°	1405.3	1389.2	1357.2	1339.3	1331.2
42.5°	1335.2	1319.1	1287.3	1267.1	1255.2
45°	1259.3	1245.2	1215.0	1193.2	1185.1
47.5°	1185.1	1171.1	1139.1	1117.0	1105.0
50°	1107.0	1097.0	1069.0	1040.9	1030.9
52.5°	1030.9	1016.9	991.0	968.9	954.9
55°	953.0	940.8	916.9	892.9	882.9
57.5°	874.9	864.9	838.7	814.8	806.6
60°	796.7	788.8	760.8	738.7	732.7
62.5°	720.6	706.6	686.6	666.6	658.6
65°	642.7	630.6	610.6	592.5	582.6
67.5°	562.6	552.4	534.6	520.6	512.5
70°	488.5	480.5	462.4	448.4	440.5
72.5°	412.4	404.4	394.4	380.4	374.4
75°	336.2	332.4	322.2	310.3	314.3
77.5°	268.2	260.2	256.1	250.2	244.2
80°	200.3	198.1	194.1	188.2	184.1
82.5°	136.2	136.2	134.2	126.2	126.2
85°	81.9	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3



TEST NUMBER: P923726

CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1



TEST NUMBER: P923726
 CATALOG NUMBER: DFN2DIP-TR4F0-060D080US940-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.42	9.59	10.43	11.76	8.17	8.99	9.16	10.00	11.33
	3H	10.26	11.00	11.26	12.01	13.36	9.78	10.52	10.79	11.54	12.89
	4H	10.84	11.54	11.86	12.56	13.92	10.37	11.07	11.39	12.09	13.45
	6H	11.24	11.88	12.27	12.91	14.28	10.77	11.41	11.79	12.43	13.80
	8H	11.34	11.96	12.38	13.00	14.36	10.87	11.48	11.90	12.52	13.89
	12H	11.39	11.97	12.43	13.01	14.40	10.91	11.49	11.95	12.53	13.92
4H	2H	9.06	9.76	10.08	10.77	12.13	8.71	9.41	9.74	10.43	11.79
	3H	10.92	11.50	11.95	12.55	13.92	10.53	11.11	11.56	12.16	13.53
	4H	11.63	12.17	12.67	13.20	14.60	11.23	11.76	12.27	12.80	14.19
	6H	12.14	12.60	13.19	13.67	15.06	11.74	12.20	12.78	13.26	14.65
	8H	12.29	12.72	13.34	13.78	15.18	11.88	12.31	12.93	13.36	14.77
	12H	12.36	12.75	13.43	13.82	15.23	11.94	12.33	13.01	13.40	14.81
8H	4H	11.83	12.26	12.88	13.31	14.72	11.47	11.90	12.52	12.95	14.36
	6H	12.45	12.81	13.53	13.91	15.31	12.09	12.45	13.17	13.54	14.95
	8H	12.68	12.99	13.76	14.07	15.49	12.31	12.62	13.39	13.70	15.12
	12H	12.81	13.08	13.89	14.15	15.62	12.42	12.70	13.51	13.77	15.23
12H	4H	11.81	12.20	12.88	13.27	14.68	11.46	11.85	12.53	12.91	14.33
	6H	12.48	12.80	13.57	13.88	15.30	12.13	12.45	13.21	13.52	14.95
	8H	12.73	13.00	13.81	14.07	15.54	12.37	12.64	13.45	13.72	15.18