

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923752

Luminaire Tested: DFN2DIP-TR4F0-070D050US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923752
REPORT IS A COMBINATION OF REPORTS P900394 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D050US940-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9251.5 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		56	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	42	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	34	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		26	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2049	2049	2049
5°	2053	2017	2030
10°	2033	1977	1964
15°	2004	1912	1862
20°	1968	1822	1736
25°	1930	1721	1615
30°	1879	1617	1462
35°	1829	1506	1327
40°	1778	1391	1172
45°	1719	1263	1032
50°	1658	1134	895
55°	1595	996	764
60°	1521	852	629
65°	1436	705	566
70°	1334	569	512
75°	1205	501	466
80°	1018	421	404
85°	709	280	303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1719 cd/sqm

TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.8	2.6
10°-20°	663.7	7.2
20°-30°	931.9	10.1
30°-40°	1015.8	11.0
40°-50°	933.6	10.1
50°-60°	733.2	7.9
60°-70°	477.3	5.2
70°-80°	245.7	2.7
80°-90°	66.7	0.7
90°-100°	87.3	0.9
100°-110°	277.2	3.0
110°-120°	474.5	5.1
120°-130°	624.0	6.7
130°-140°	700.4	7.6
140°-150°	686.8	7.4
150°-160°	576.1	6.2
160°-170°	382.1	4.1
170°-180°	133.5	1.4
0°-30°	1837.4	19.9
0°-40°	2853.2	30.8
0°-60°	4520.0	48.9
0°-90°	5309.6	57.4
90°-120°	838.9	9.1
90°-150°	2850.1	30.8
90°-180°	3942.0	42.6
0°-180°	9251.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2580	2580	2580	2580	2580	
5°	2580	2568	2538	2559	2552	245
15°	2454	2428	2349	2304	2281	691
25°	2227	2152	1998	1903	1868	1024
35°	1919	1800	1595	1448	1396	1201
45°	1569	1412	1167	1002	946	1212
55°	1193	1011	759	619	574	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	1	15	42	39	40	9
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	

TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2579.8	2579.8	2579.8	2579.8	2579.8
2.5°	2591.4	2579.8	2554.0	2577.6	2572.9
5°	2579.8	2568.1	2537.7	2558.8	2551.8
7.5°	2558.8	2544.9	2512.2	2521.3	2509.7
10°	2530.8	2514.4	2467.8	2460.7	2446.8
12.5°	2495.8	2474.8	2411.6	2397.7	2371.9
15°	2453.7	2427.9	2348.7	2304.4	2281.1
17.5°	2404.7	2367.3	2269.2	2217.9	2180.5
20°	2348.7	2301.9	2185.2	2127.0	2075.5
22.5°	2288.0	2234.3	2098.7	2019.5	1984.6
25°	2227.3	2152.5	1998.4	1902.8	1867.7
27.5°	2155.0	2075.5	1905.1	1795.4	1741.6
30°	2078.0	1989.0	1802.2	1683.4	1620.2
32.5°	2003.1	1895.7	1704.4	1564.2	1505.7
35°	1919.1	1800.0	1594.7	1447.6	1396.1
37.5°	1837.5	1708.9	1491.9	1330.6	1272.5
40°	1751.0	1611.1	1384.4	1218.7	1158.0
42.5°	1662.3	1513.0	1277.1	1104.2	1046.1
45°	1569.0	1412.4	1167.4	1001.5	945.5
47.5°	1480.2	1314.6	1062.4	896.4	845.2
50°	1382.2	1216.5	959.6	798.3	749.6
52.5°	1286.3	1111.2	861.5	707.4	663.1
55°	1192.9	1010.8	758.7	618.8	574.4
57.5°	1097.3	910.5	667.8	537.0	499.6
60°	999.3	812.4	571.9	453.1	415.6
62.5°	903.6	716.8	490.2	378.3	359.6
65°	805.5	616.3	406.3	327.0	319.8
67.5°	712.1	522.9	327.0	287.0	280.2
70°	614.0	431.9	270.7	247.4	238.0
72.5°	520.7	347.8	226.4	207.9	203.1
75°	429.5	266.0	186.7	170.4	168.2
77.5°	338.6	189.0	147.1	137.7	133.0
80°	254.4	135.5	112.0	102.8	102.8
82.5°	177.4	91.1	77.0	72.3	72.3
85°	100.3	51.3	44.3	44.3	44.3
87.5°	37.4	18.5	18.5	16.3	16.3
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4

TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1

TEST NUMBER: P923752

CATALOG NUMBER: DFN2DIP-TR4F0-070D050US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.30	11.19	11.20	12.10	13.27	6.27	7.17	7.17	8.08	9.24
	3H	11.98	12.78	12.89	13.70	14.89	7.47	8.27	8.38	9.19	10.38
	4H	12.59	13.35	13.52	14.27	15.47	7.92	8.67	8.85	9.60	10.80
	6H	13.02	13.71	13.95	14.64	15.86	8.24	8.94	9.18	9.87	11.09
	8H	13.14	13.81	14.09	14.76	15.97	8.34	9.00	9.28	9.95	11.16
	12H	13.21	13.84	14.16	14.78	16.02	8.38	9.01	9.33	9.96	11.19
4H	2H	10.32	11.08	11.25	12.01	13.21	6.87	7.63	7.81	8.56	9.76
	3H	12.16	12.79	13.10	13.74	14.96	8.23	8.86	9.17	9.82	11.03
	4H	12.85	13.43	13.80	14.38	15.62	8.78	9.35	9.73	10.31	11.55
	6H	13.37	13.86	14.34	14.84	16.08	9.21	9.70	10.17	10.67	11.91
	8H	13.55	14.01	14.51	14.98	16.23	9.34	9.80	10.30	10.77	12.02
	12H	13.65	14.06	14.63	15.05	16.30	9.41	9.82	10.39	10.81	12.06
8H	4H	12.83	13.29	13.79	14.26	15.51	9.07	9.53	10.03	10.50	11.75
	6H	13.39	13.77	14.38	14.79	16.04	9.59	9.97	10.58	10.98	12.23
	8H	13.61	13.95	14.61	14.95	16.22	9.78	10.12	10.78	11.12	12.39
	12H	13.75	14.05	14.75	15.04	16.36	9.90	10.20	10.91	11.19	12.51
12H	4H	12.78	13.19	13.76	14.18	15.44	9.07	9.49	10.06	10.48	11.73
	6H	13.37	13.70	14.37	14.71	15.97	9.64	9.97	10.64	10.97	12.24
	8H	13.59	13.89	14.60	14.88	16.20	9.85	10.15	10.85	11.14	12.46

END OF REPORT