

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923834

Luminaire Tested: DFN2DIP-TR4F0-090D080US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923834
REPORT IS A COMBINATION OF REPORTS P900451 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D080US940-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14258.5 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923834
CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P923834

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61	56			56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47			47
2	90	83	77	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39			39
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	40	37	33			33
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29			29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25			25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22			22
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19			19
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17			17
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	16			16
10	48	36	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16	14			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2481	2481	2481
5°	2485	2446	2463
10°	2465	2413	2429
15°	2428	2373	2377
20°	2380	2318	2324
25°	2331	2252	2262
30°	2270	2191	2183
35°	2212	2118	2100
40°	2141	2045	2021
45°	2070	1972	1941
50°	1992	1895	1847
55°	1911	1806	1761
60°	1819	1700	1662
65°	1719	1590	1546
70°	1591	1457	1421
75°	1415	1297	1305
80°	1202	1093	1085
85°	870	742	718

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2070 cd/sqm



TEST NUMBER: P923834

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.9	2.1
10°-20°	827.0	5.8
20°-30°	1215.3	8.5
30°-40°	1411.5	9.9
40°-50°	1409.7	9.9
50°-60°	1229.3	8.6
60°-70°	908.7	6.4
70°-80°	514.1	3.6
80°-90°	142.1	1.0
90°-100°	139.6	1.0
100°-110°	443.6	3.1
110°-120°	759.1	5.3
120°-130°	998.3	7.0
130°-140°	1120.6	7.9
140°-150°	1098.9	7.7
150°-160°	921.8	6.5
160°-170°	611.3	4.3
170°-180°	213.7	1.5
0°-30°	2336.2	16.4
0°-40°	3747.7	26.3
0°-60°	6386.7	44.8
0°-90°	7951.6	55.8
90°-120°	1342.3	9.4
90°-150°	4560.1	32.0
90°-180°	6307.0	44.2
0°-180°	14258.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3123	3123	3123	3123	3123	
5°	3123	3111	3078	3102	3096	296
15°	2973	2955	2916	2928	2913	837
25°	2690	2666	2616	2621	2616	1238
35°	2321	2291	2243	2225	2210	1449
45°	1889	1868	1823	1790	1778	1458
55°	1430	1411	1375	1339	1324	1278
65°	964	946	916	889	874	953
75°	504	499	483	466	472	538
85°	123	120	117	108	105	137
90°	2	24	67	63	65	14
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	



TEST NUMBER: P923834

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3122.7	3122.7	3122.7	3122.7	3122.7
2.5°	3140.9	3125.9	3092.8	3122.7	3117.0
5°	3122.7	3110.9	3077.8	3101.7	3095.9
7.5°	3101.7	3083.9	3050.7	3075.0	3068.9
10°	3068.9	3047.9	3011.8	3035.7	3026.8
12.5°	3023.6	3005.8	2969.8	2984.7	2978.8
15°	2972.7	2954.9	2915.6	2927.8	2912.8
17.5°	2909.6	2891.7	2852.6	2867.6	2852.6
20°	2840.5	2822.6	2780.5	2789.4	2777.7
22.5°	2771.6	2744.6	2705.4	2705.4	2699.3
25°	2690.4	2666.5	2615.6	2621.3	2615.6
27.5°	2600.2	2579.2	2540.4	2531.5	2516.5
30°	2510.4	2486.2	2441.2	2432.3	2420.3
32.5°	2414.2	2396.4	2348.2	2330.1	2318.0
35°	2321.2	2291.2	2243.1	2225.0	2210.0
37.5°	2216.1	2189.0	2140.8	2119.9	2104.9
40°	2108.0	2083.8	2035.7	2008.9	1996.9
42.5°	2002.9	1978.7	1930.9	1900.7	1882.8
45°	1888.8	1867.9	1822.6	1789.8	1777.7
47.5°	1777.7	1756.7	1708.5	1675.4	1657.6
50°	1660.5	1645.5	1603.4	1561.4	1546.4
52.5°	1546.4	1525.4	1486.5	1453.4	1432.4
55°	1429.5	1411.3	1375.3	1339.3	1324.4
57.5°	1312.2	1297.3	1258.1	1222.1	1210.0
60°	1195.0	1183.2	1141.1	1108.0	1099.1
62.5°	1080.9	1059.9	1029.9	1000.1	987.9
65°	964.0	945.8	915.9	888.9	873.9
67.5°	843.9	828.7	801.8	780.9	768.7
70°	732.7	720.6	693.6	672.5	660.8
72.5°	618.7	606.5	591.6	570.6	561.7
75°	504.4	498.6	483.3	465.5	471.5
77.5°	402.3	390.3	384.2	375.3	366.4
80°	300.4	297.2	291.1	282.2	276.3
82.5°	204.2	204.2	201.3	189.2	189.2
85°	123.0	120.1	117.3	108.0	105.1
87.5°	54.1	48.1	42.1	33.2	30.0
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3



TEST NUMBER: P923834

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1



TEST NUMBER: P923834
 CATALOG NUMBER: DFN2DIP-TR4F0-090D080US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.94	11.85	11.84	12.78	13.97	10.51	11.42	11.41	12.35	13.53
	3H	12.60	13.42	13.52	14.36	15.57	12.13	12.95	13.05	13.89	15.10
	4H	13.19	13.97	14.13	14.91	16.13	12.72	13.50	13.65	14.44	15.66
	6H	13.60	14.31	14.54	15.26	16.49	13.12	13.84	14.06	14.78	16.02
	8H	13.70	14.38	14.65	15.35	16.58	13.23	13.91	14.18	14.87	16.10
	12H	13.75	14.40	14.71	15.36	16.61	13.27	13.92	14.23	14.88	16.13
4H	2H	11.41	12.18	12.35	13.12	14.34	11.06	11.84	12.00	12.78	14.00
	3H	13.28	13.93	14.23	14.90	16.13	12.89	13.53	13.83	14.50	15.74
	4H	13.99	14.59	14.95	15.55	16.81	13.59	14.18	14.55	15.15	16.40
	6H	14.51	15.02	15.48	16.01	17.27	14.10	14.61	15.07	15.60	16.86
	8H	14.66	15.14	15.64	16.12	17.39	14.25	14.73	15.22	15.71	16.98
	12H	14.74	15.17	15.73	16.17	17.45	14.32	14.75	15.31	15.75	17.02
8H	4H	14.20	14.67	15.17	15.65	16.93	13.84	14.31	14.81	15.29	16.57
	6H	14.83	15.22	15.83	16.25	17.52	14.47	14.86	15.46	15.88	17.16
	8H	15.05	15.40	16.06	16.41	17.70	14.68	15.03	15.69	16.04	17.33
	12H	15.18	15.49	16.19	16.50	17.83	14.80	15.11	15.81	16.11	17.45
12H	4H	14.18	14.61	15.18	15.61	16.89	13.83	14.26	14.82	15.26	16.54
	6H	14.86	15.21	15.87	16.22	17.51	14.51	14.86	15.51	15.87	17.16
	8H	15.10	15.41	16.11	16.42	17.75	14.75	15.05	15.76	16.06	17.39