

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918436

Luminaire Tested: DFN2DIP-TR4F0-110D040US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918436
REPORT IS A COMBINATION OF REPORTS P900384 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D040US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10509.2 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 143
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66
2	95	88	82	77	90	83	78	74	76	71	68	68	65	62	62	59	57
3	87	78	70	65	82	74	68	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	54	60	55	50	55	50	47	50	46	43
5	74	62	54	48	70	60	52	47	54	48	44	50	45	41	45	41	38
6	68	56	48	42	65	54	47	41	49	43	39	45	40	36	41	37	34
7	64	51	43	38	60	49	42	37	45	39	34	41	36	32	38	34	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	28
9	55	43	35	30	53	41	34	30	38	32	28	35	30	27	33	28	25
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2945	2945	2945
5°	2949	2898	2916
10°	2920	2841	2821
15°	2880	2747	2675
20°	2827	2618	2495
25°	2772	2472	2321
30°	2699	2324	2100
35°	2628	2164	1906
40°	2555	1998	1684
45°	2470	1815	1483
50°	2382	1629	1286
55°	2291	1431	1097
60°	2185	1224	903
65°	2064	1014	813
70°	1916	817	735
75°	1731	720	669
80°	1462	604	580
85°	1019	403	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2470 cd/sqm

TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	3.3
10°-20°	953.6	9.1
20°-30°	1338.9	12.7
30°-40°	1459.5	13.9
40°-50°	1341.4	12.8
50°-60°	1053.5	10.0
60°-70°	685.7	6.5
70°-80°	353.0	3.4
80°-90°	93.1	0.9
90°-100°	63.8	0.6
100°-110°	202.8	1.9
110°-120°	347.0	3.3
120°-130°	456.4	4.3
130°-140°	512.3	4.9
140°-150°	502.4	4.8
150°-160°	421.4	4.0
160°-170°	279.5	2.7
170°-180°	97.7	0.9
0°-30°	2639.9	25.1
0°-40°	4099.4	39.0
0°-60°	6494.2	61.8
0°-90°	7626.0	72.6
90°-120°	613.6	5.8
90°-150°	2084.7	19.8
90°-180°	2883.0	27.4
0°-180°	10509.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3707	3707	3707	3707	3707	
5°	3707	3690	3646	3676	3666	351
15°	3525	3488	3374	3311	3277	993
25°	3200	3093	2871	2734	2683	1472
35°	2757	2586	2291	2080	2006	1726
45°	2254	2029	1677	1439	1358	1741
55°	1714	1452	1090	889	825	1532
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	653
85°	144	74	64	64	64	165
90°	1	11	30	29	30	10
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	

TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3706.6	3706.6	3706.6	3706.6	3706.6
2.5°	3723.3	3706.6	3669.6	3703.4	3696.6
5°	3706.6	3689.9	3646.1	3676.3	3666.4
7.5°	3676.3	3656.4	3609.4	3622.6	3605.8
10°	3636.1	3612.6	3545.7	3535.4	3515.5
12.5°	3585.9	3555.7	3464.9	3445.0	3407.9
15°	3525.4	3488.4	3374.5	3310.8	3277.3
17.5°	3455.0	3401.3	3260.3	3186.6	3132.9
20°	3374.5	3307.3	3139.6	3056.0	2982.0
22.5°	3287.4	3210.1	3015.5	2901.6	2851.3
25°	3200.1	3092.7	2871.3	2733.9	2683.4
27.5°	3096.3	2982.0	2737.1	2579.4	2502.2
30°	2985.5	2857.8	2589.5	2418.6	2327.8
32.5°	2878.1	2723.6	2448.8	2247.5	2163.5
35°	2757.4	2586.2	2291.2	2079.8	2005.8
37.5°	2640.0	2455.3	2143.5	1911.8	1828.2
40°	2515.8	2314.7	1989.1	1750.9	1663.8
42.5°	2388.3	2173.7	1835.0	1586.6	1502.9
45°	2254.2	2029.3	1677.3	1438.8	1358.4
47.5°	2126.8	1888.7	1526.4	1287.9	1214.3
50°	1985.8	1747.8	1378.8	1147.0	1076.9
52.5°	1848.1	1596.5	1237.8	1016.4	952.7
55°	1713.9	1452.4	1090.1	889.0	825.3
57.5°	1576.6	1308.2	959.4	771.6	717.8
60°	1435.7	1167.3	821.7	650.9	597.2
62.5°	1298.3	1030.0	704.3	543.5	516.7
65°	1157.3	885.4	583.7	469.8	459.4
67.5°	1023.2	751.3	469.8	412.5	402.5
70°	882.2	620.7	389.0	355.6	342.0
72.5°	748.0	499.7	325.3	298.6	291.8
75°	617.1	382.2	268.3	244.8	241.7
77.5°	486.5	271.6	211.4	197.9	191.1
80°	365.5	194.7	160.9	147.7	147.7
82.5°	254.8	130.9	110.7	104.0	104.0
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1



TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4

TEST NUMBER: P918436

CATALOG NUMBER: DFN2DIP-TR4F0-110D040US930-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.78	13.84	13.53	14.60	15.51	8.76	9.81	9.50	10.57	11.48
	3H	14.48	15.42	15.24	16.19	17.14	9.96	10.91	10.72	11.68	12.62
	4H	15.10	15.99	15.87	16.77	17.72	10.43	11.32	11.20	12.09	13.05
	6H	15.53	16.35	16.32	17.14	18.10	10.76	11.58	11.55	12.37	13.33
	8H	15.66	16.44	16.46	17.25	18.22	10.86	11.64	11.65	12.44	13.41
	12H	15.73	16.48	16.53	17.27	18.27	10.91	11.65	11.71	12.45	13.45
4H	2H	12.83	13.72	13.61	14.50	15.45	9.38	10.27	10.16	11.05	12.00
	3H	14.68	15.42	15.47	16.23	17.20	10.75	11.49	11.54	12.30	13.27
	4H	15.38	16.05	16.18	16.86	17.86	11.31	11.98	12.11	12.79	13.79
	6H	15.91	16.49	16.73	17.32	18.33	11.74	12.32	12.56	13.16	14.16
	8H	16.09	16.63	16.91	17.46	18.48	11.88	12.42	12.70	13.25	14.27
	12H	16.19	16.68	17.04	17.53	18.55	11.95	12.44	12.80	13.29	14.31
8H	4H	15.36	15.91	16.19	16.74	17.75	11.61	12.15	12.43	12.98	14.00
	6H	15.94	16.39	16.79	17.26	18.28	12.13	12.58	12.99	13.46	14.47
	8H	16.16	16.55	17.02	17.42	18.46	12.33	12.72	13.19	13.59	14.63
	12H	16.30	16.65	17.17	17.52	18.61	12.46	12.81	13.32	13.67	14.76
12H	4H	15.33	15.81	16.17	16.67	17.69	11.62	12.11	12.47	12.96	13.98
	6H	15.91	16.31	16.78	17.18	18.22	12.18	12.58	13.05	13.45	14.49
	8H	16.15	16.49	17.01	17.36	18.45	12.40	12.75	13.27	13.62	14.71