

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923873

Luminaire Tested: DFN2DIP-TR4F0-100D080US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923873
REPORT IS A COMBINATION OF REPORTS P901974 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D080US940-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14641.9 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 160.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923873
CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P923873

CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52	52	52	52
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50	45	45	45	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38	38	38	38
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33	33	33	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29	29	29	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25	25	25	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22	22	22	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20	20	20	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18	18	18	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16	16	16	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2928	2928	2928
5°	2933	2881	2900
10°	2904	2825	2805
15°	2864	2731	2659
20°	2811	2603	2480
25°	2757	2458	2307
30°	2684	2310	2088
35°	2613	2151	1895
40°	2540	1987	1675
45°	2456	1804	1474
50°	2369	1620	1279
55°	2278	1423	1091
60°	2173	1217	898
65°	2052	1008	808
70°	1905	812	731
75°	1721	716	665
80°	1454	601	577
85°	1013	401	433

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2456 cd/sqm



TEST NUMBER: P923873

CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.4
10°-20°	948.2	6.5
20°-30°	1331.2	9.1
30°-40°	1451.1	9.9
40°-50°	1333.8	9.1
50°-60°	1047.4	7.2
60°-70°	681.8	4.7
70°-80°	351.0	2.4
80°-90°	93.8	0.6
90°-100°	79.4	0.5
100°-110°	295.9	2.0
110°-120°	784.9	5.4
120°-130°	1301.8	8.9
130°-140°	1382.8	9.4
140°-150°	1285.1	8.8
150°-160°	1033.2	7.1
160°-170°	665.8	4.5
170°-180°	229.2	1.6
0°-30°	2624.8	17.9
0°-40°	4076.0	27.8
0°-60°	6457.2	44.1
0°-90°	7583.8	51.8
90°-120°	1160.2	7.9
90°-150°	5129.9	35.0
90°-180°	7058.0	48.2
0°-180°	14641.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	2	21	35	44	47	14
95°	113	56	68	77	75	134
105°	530	582	106	125	132	566
115°	1002	1031	1075	268	143	986
125°	1416	1439	1472	1484	1489	1263
135°	1753	1780	1796	1814	1810	1354
145°	2033	2031	2061	2073	2064	1272
155°	2238	2223	2244	2254	2240	1032
165°	2359	2348	2354	2366	2354	666
175°	2413	2400	2404	2416	2399	230
180°	2408	2408	2408	2408	2408	



TEST NUMBER: P923873

CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	1.7	20.9	34.8	43.6	47.0
92.5°	43.6	36.6	41.8	45.3	47.0
95°	113.2	55.6	67.9	76.8	74.9
97.5°	203.8	61.0	88.7	94.2	95.8
100°	308.4	69.7	99.3	113.2	116.6
102.5°	423.3	419.9	102.8	121.8	127.2
105°	529.6	581.9	106.3	125.4	132.4
107.5°	653.3	696.7	109.9	128.9	135.9
110°	771.9	808.2	305.0	130.7	137.6



TEST NUMBER: P923873

CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	883.3	914.5	885.0	134.0	139.5
115°	1001.7	1031.3	1074.9	268.3	142.9
117.5°	1104.5	1139.2	1169.0	919.7	463.4
120°	1219.5	1245.5	1277.0	1297.9	1062.7
122.5°	1316.9	1344.9	1379.8	1390.2	1392.0
125°	1416.2	1439.0	1472.0	1484.3	1489.4
127.5°	1506.8	1531.2	1557.6	1574.8	1576.5
130°	1592.2	1620.1	1639.2	1658.5	1656.8
132.5°	1679.4	1702.1	1721.2	1736.9	1735.2
135°	1752.6	1780.5	1796.0	1813.6	1810.1
137.5°	1829.2	1850.0	1867.6	1885.0	1879.8
140°	1904.0	1918.1	1937.2	1952.8	1944.1
142.5°	1966.9	1979.1	2001.6	2015.5	2006.8
145°	2033.1	2031.2	2060.8	2073.0	2064.3
147.5°	2090.4	2085.3	2114.8	2123.5	2116.7
150°	2146.3	2134.0	2162.0	2172.3	2163.6
152.5°	2193.3	2179.3	2205.4	2216.0	2203.8
155°	2238.5	2223.0	2243.9	2254.2	2240.4
157.5°	2275.1	2261.3	2277.0	2289.2	2275.1
160°	2306.6	2296.1	2306.6	2316.9	2304.7
162.5°	2334.3	2324.0	2332.6	2344.8	2329.1
165°	2358.8	2348.4	2353.6	2365.7	2353.6
167.5°	2377.9	2367.4	2372.8	2385.0	2369.3
170°	2393.7	2383.1	2386.7	2398.9	2383.1
172.5°	2404.1	2393.7	2397.2	2409.4	2393.7
175°	2412.7	2400.5	2404.1	2416.2	2398.9
177.5°	2416.2	2404.1	2405.8	2418.1	2402.4
180°	2407.5	2407.5	2407.5	2407.5	2407.5



TEST NUMBER: P923873
 CATALOG NUMBER: DFN2DIP-TR4F0-100D080US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.04	11.89	11.99	12.85	14.09	7.01	7.86	7.96	8.82	10.07
	3H	12.72	13.47	13.68	14.44	15.72	8.20	8.96	9.16	9.93	11.20
	4H	13.33	14.04	14.30	15.02	16.30	8.66	9.37	9.63	10.34	11.62
	6H	13.75	14.41	14.74	15.39	16.68	8.98	9.64	9.96	10.61	11.91
	8H	13.88	14.50	14.87	15.50	16.79	9.07	9.70	10.06	10.69	11.98
	12H	13.94	14.53	14.94	15.52	16.84	9.12	9.71	10.11	10.70	12.01
4H	2H	11.06	11.77	12.04	12.75	14.03	7.61	8.33	8.59	9.30	10.58
	3H	12.89	13.48	13.88	14.49	15.78	8.96	9.56	9.95	10.56	11.85
	4H	13.58	14.13	14.58	15.12	16.44	9.51	10.05	10.51	11.05	12.37
	6H	14.10	14.57	15.11	15.58	16.90	9.93	10.40	10.94	11.42	12.73
	8H	14.28	14.71	15.29	15.72	17.05	10.06	10.50	11.07	11.51	12.84
	12H	14.37	14.76	15.40	15.79	17.13	10.13	10.52	11.16	11.55	12.88
8H	4H	13.55	13.99	14.56	15.00	16.33	9.79	10.23	10.80	11.24	12.57
	6H	14.12	14.48	15.15	15.53	16.86	10.31	10.67	11.35	11.73	13.05
	8H	14.34	14.65	15.38	15.69	17.04	10.51	10.82	11.55	11.86	13.21
	12H	14.48	14.75	15.52	15.79	17.18	10.63	10.90	11.67	11.94	13.33
12H	4H	13.51	13.90	14.53	14.93	16.26	9.80	10.19	10.83	11.22	12.55
	6H	14.10	14.41	15.14	15.45	16.80	10.36	10.68	11.41	11.72	13.07
	8H	14.32	14.59	15.36	15.63	17.02	10.58	10.85	11.62	11.89	13.28