

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918460

Luminaire Tested: DFN2DIP-TR4F0-110D100US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918460
REPORT IS A COMBINATION OF REPORTS P900492 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-110D100US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14838.5 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918460
CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918460
 CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	63	61	59	52	50	49	52	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	50	46	44	42	46	44	42	38
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	37	34	32	28
5	70	58	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	28	25	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	23	28	25	23	20
8	55	43	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2945	2945	2945
5°	2949	2898	2916
10°	2920	2841	2821
15°	2880	2747	2675
20°	2827	2618	2495
25°	2772	2472	2321
30°	2699	2324	2100
35°	2628	2164	1906
40°	2555	1998	1684
45°	2470	1815	1483
50°	2382	1629	1286
55°	2291	1431	1097
60°	2185	1224	903
65°	2064	1014	813
70°	1916	817	735
75°	1731	720	669
80°	1462	604	580
85°	1019	403	435

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2470 cd/sqm



TEST NUMBER: P918460
 CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	2.3
10°-20°	953.6	6.4
20°-30°	1338.9	9.0
30°-40°	1459.5	9.8
40°-50°	1341.4	9.0
50°-60°	1053.5	7.1
60°-70°	685.7	4.6
70°-80°	353.0	2.4
80°-90°	97.4	0.7
90°-100°	159.6	1.1
100°-110°	507.0	3.4
110°-120°	867.6	5.8
120°-130°	1141.0	7.7
130°-140°	1280.7	8.6
140°-150°	1255.9	8.5
150°-160°	1053.5	7.1
160°-170°	698.7	4.7
170°-180°	244.2	1.6
0°-30°	2639.9	17.8
0°-40°	4099.4	27.6
0°-60°	6494.2	43.8
0°-90°	7630.4	51.4
90°-120°	1534.1	10.3
90°-150°	5211.7	35.1
90°-180°	7208.0	48.6
0°-180°	14838.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3707	3707	3707	3707	3707	
5°	3707	3690	3646	3676	3666	351
15°	3525	3488	3374	3311	3277	993
25°	3200	3093	2871	2734	2683	1472
35°	2757	2586	2291	2080	2006	1726
45°	2254	2029	1677	1439	1358	1741
55°	1714	1452	1090	889	825	1532
65°	1157	885	584	470	459	1147
75°	617	382	268	245	242	653
85°	144	74	64	64	64	165
90°	2	28	76	72	74	15
95°	114	135	139	139	135	126
105°	468	474	479	483	483	494
115°	871	883	879	877	871	861
125°	1266	1286	1280	1272	1270	1132
135°	1638	1662	1667	1664	1658	1266
145°	1988	2004	2016	2019	2010	1242
155°	2274	2280	2287	2298	2291	1047
165°	2474	2471	2471	2487	2476	698
175°	2574	2568	2563	2578	2565	245
180°	2578	2578	2578	2578	2578	



TEST NUMBER: P918460

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3706.6	3706.6	3706.6	3706.6	3706.6
2.5°	3723.3	3706.6	3669.6	3703.4	3696.6
5°	3706.6	3689.9	3646.1	3676.3	3666.4
7.5°	3676.3	3656.4	3609.4	3622.6	3605.8
10°	3636.1	3612.6	3545.7	3535.4	3515.5
12.5°	3585.9	3555.7	3464.9	3445.0	3407.9
15°	3525.4	3488.4	3374.5	3310.8	3277.3
17.5°	3455.0	3401.3	3260.3	3186.6	3132.9
20°	3374.5	3307.3	3139.6	3056.0	2982.0
22.5°	3287.4	3210.1	3015.5	2901.6	2851.3
25°	3200.1	3092.7	2871.3	2733.9	2683.4
27.5°	3096.3	2982.0	2737.1	2579.4	2502.2
30°	2985.5	2857.8	2589.5	2418.6	2327.8
32.5°	2878.1	2723.6	2448.8	2247.5	2163.5
35°	2757.4	2586.2	2291.2	2079.8	2005.8
37.5°	2640.0	2455.3	2143.5	1911.8	1828.2
40°	2515.8	2314.7	1989.1	1750.9	1663.8
42.5°	2388.3	2173.7	1835.0	1586.6	1502.9
45°	2254.2	2029.3	1677.3	1438.8	1358.4
47.5°	2126.8	1888.7	1526.4	1287.9	1214.3
50°	1985.8	1747.8	1378.8	1147.0	1076.9
52.5°	1848.1	1596.5	1237.8	1016.4	952.7
55°	1713.9	1452.4	1090.1	889.0	825.3
57.5°	1576.6	1308.2	959.4	771.6	717.8
60°	1435.7	1167.3	821.7	650.9	597.2
62.5°	1298.3	1030.0	704.3	543.5	516.7
65°	1157.3	885.4	583.7	469.8	459.4
67.5°	1023.2	751.3	469.8	412.5	402.5
70°	882.2	620.7	389.0	355.6	342.0
72.5°	748.0	499.7	325.3	298.6	291.8
75°	617.1	382.2	268.3	244.8	241.7
77.5°	486.5	271.6	211.4	197.9	191.1
80°	365.5	194.7	160.9	147.7	147.7
82.5°	254.8	130.9	110.7	104.0	104.0
85°	144.1	73.7	63.7	63.7	63.7
87.5°	53.7	26.7	26.7	23.5	23.5
90°	2.4	28.0	76.1	71.5	73.9
92.5°	48.2	65.3	67.7	70.0	70.0
95°	113.5	135.3	139.2	139.2	135.3
97.5°	188.9	209.1	217.7	217.7	217.7
100°	276.0	293.8	300.0	300.0	297.7
102.5°	367.7	380.9	389.5	391.8	389.5
105°	468.0	474.2	478.8	482.7	482.7
107.5°	567.4	576.8	576.8	578.4	567.4
110°	663.9	676.3	676.3	676.3	670.1



TEST NUMBER: P918460

CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	768.0	781.2	778.9	772.7	768.0
115°	870.7	883.0	879.2	876.9	870.7
117.5°	972.5	989.6	978.7	972.5	966.2
120°	1075.1	1092.2	1075.1	1075.1	1068.1
122.5°	1168.3	1190.1	1179.2	1173.1	1168.3
125°	1266.3	1285.7	1279.5	1272.5	1270.2
127.5°	1362.0	1386.0	1377.4	1368.2	1362.0
130°	1451.3	1479.3	1475.4	1470.7	1462.2
132.5°	1551.6	1573.4	1574.9	1564.1	1557.8
135°	1637.9	1662.0	1666.6	1664.3	1658.1
137.5°	1734.3	1753.7	1757.6	1756.1	1746.7
140°	1819.0	1838.4	1849.3	1849.3	1840.8
142.5°	1906.1	1925.5	1931.7	1934.1	1925.5
145°	1988.4	2004.0	2016.5	2018.8	2010.2
147.5°	2062.3	2081.8	2091.1	2095.0	2086.4
150°	2138.5	2151.7	2160.3	2167.2	2160.3
152.5°	2206.1	2219.3	2230.2	2238.8	2230.2
155°	2273.8	2280.0	2287.0	2297.8	2290.8
157.5°	2332.1	2336.7	2340.6	2356.1	2345.3
160°	2384.2	2388.8	2391.1	2404.3	2395.0
162.5°	2432.4	2432.4	2434.6	2449.4	2438.6
165°	2473.5	2471.2	2471.2	2486.7	2475.9
167.5°	2510.9	2503.9	2503.9	2519.4	2508.5
170°	2538.8	2532.6	2530.3	2545.9	2532.6
172.5°	2558.2	2552.0	2549.7	2565.3	2552.0
175°	2573.8	2567.6	2563.0	2578.5	2565.3
177.5°	2582.4	2576.2	2571.5	2584.7	2571.5
180°	2578.5	2578.5	2578.5	2578.5	2578.5



TEST NUMBER: P918460
 CATALOG NUMBER: DFN2DIP-TR4F0-110D100US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.02	11.87	11.98	12.83	14.08	7.00	7.84	7.95	8.80	10.06
	3H	12.70	13.46	13.67	14.43	15.70	8.19	8.94	9.15	9.91	11.19
	4H	13.31	14.02	14.29	15.00	16.28	8.64	9.35	9.62	10.33	11.61
	6H	13.73	14.39	14.72	15.37	16.67	8.96	9.62	9.95	10.60	11.90
	8H	13.86	14.48	14.85	15.48	16.78	9.05	9.68	10.05	10.68	11.97
	12H	13.92	14.51	14.92	15.51	16.83	9.10	9.69	10.10	10.68	12.00
4H	2H	11.04	11.76	12.03	12.73	14.02	7.60	8.31	8.58	9.28	10.57
	3H	12.87	13.47	13.87	14.47	15.77	8.95	9.54	9.94	10.54	11.84
	4H	13.57	14.11	14.57	15.11	16.43	9.50	10.04	10.50	11.04	12.36
	6H	14.08	14.55	15.09	15.57	16.89	9.92	10.38	10.93	11.40	12.72
	8H	14.26	14.69	15.27	15.71	17.04	10.05	10.48	11.06	11.50	12.83
	12H	14.35	14.74	15.38	15.78	17.11	10.11	10.50	11.14	11.54	12.87
8H	4H	13.54	13.97	14.55	14.98	16.32	9.78	10.21	10.79	11.23	12.56
	6H	14.10	14.46	15.14	15.52	16.85	10.30	10.66	11.33	11.71	13.04
	8H	14.32	14.63	15.36	15.68	17.03	10.49	10.80	11.53	11.85	13.20
	12H	14.46	14.74	15.51	15.77	17.17	10.61	10.89	11.66	11.92	13.32
12H	4H	13.49	13.88	14.52	14.91	16.25	9.78	10.17	10.81	11.20	12.54
	6H	14.08	14.39	15.12	15.44	16.79	10.35	10.66	11.39	11.71	13.06
	8H	14.30	14.58	15.35	15.61	17.01	10.56	10.84	11.61	11.87	13.27