

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918492

Luminaire Tested: DFN2DIP-TR4F0-120D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918492
REPORT IS A COMBINATION OF REPORTS P900476 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D090US930-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14809.9 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 193.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918492
CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918492
 CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3212	3212	3212
5°	3218	3161	3182
10°	3186	3099	3078
15°	3142	2997	2918
20°	3084	2856	2721
25°	3025	2697	2531
30°	2945	2535	2291
35°	2867	2360	2080
40°	2787	2180	1837
45°	2695	1980	1618
50°	2599	1777	1403
55°	2500	1561	1197
60°	2384	1335	985
65°	2251	1106	887
70°	2090	891	802
75°	1888	786	730
80°	1596	659	632
85°	1112	440	475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2695 cd/sqm



TEST NUMBER: P918492

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.0	2.6
10°-20°	1040.3	7.0
20°-30°	1460.6	9.9
30°-40°	1592.1	10.8
40°-50°	1463.4	9.9
50°-60°	1149.2	7.8
60°-70°	748.0	5.1
70°-80°	385.1	2.6
80°-90°	104.9	0.7
90°-100°	143.6	1.0
100°-110°	456.3	3.1
110°-120°	780.8	5.3
120°-130°	1026.9	6.9
130°-140°	1152.6	7.8
140°-150°	1130.3	7.6
150°-160°	948.2	6.4
160°-170°	628.8	4.2
170°-180°	219.8	1.5
0°-30°	2879.9	19.4
0°-40°	4472.0	30.2
0°-60°	7084.6	47.8
0°-90°	8322.6	56.2
90°-120°	1380.7	9.3
90°-150°	4690.5	31.7
90°-180°	6487.0	43.8
0°-180°	14809.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4044	4044	4044	4044	4044	
5°	4044	4025	3978	4010	4000	383
15°	3846	3806	3681	3612	3575	1084
25°	3491	3374	3132	2982	2927	1606
35°	3008	2821	2500	2269	2188	1883
45°	2459	2214	1830	1570	1482	1899
55°	1870	1584	1189	970	900	1671
65°	1263	966	637	512	501	1252
75°	673	417	293	267	264	712
85°	157	80	70	70	70	181
90°	2	25	69	64	66	15
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P918492

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4043.6	4043.6	4043.6	4043.6	4043.6
2.5°	4061.8	4043.6	4003.2	4040.0	4032.6
5°	4043.6	4025.3	3977.5	4010.5	3999.7
7.5°	4010.5	3988.8	3937.6	3951.9	3933.7
10°	3966.7	3941.1	3868.0	3856.8	3835.1
12.5°	3911.9	3878.9	3779.9	3758.2	3717.8
15°	3845.9	3805.6	3681.3	3611.8	3575.3
17.5°	3769.0	3710.4	3556.7	3476.4	3417.7
20°	3681.3	3607.9	3425.1	3333.8	3253.0
22.5°	3586.2	3502.0	3289.6	3165.3	3110.6
25°	3491.1	3373.8	3132.3	2982.4	2927.3
27.5°	3377.7	3253.0	2985.9	2814.0	2729.7
30°	3257.0	3117.6	2824.8	2638.5	2539.5
32.5°	3139.7	2971.2	2671.5	2451.8	2360.1
35°	3008.1	2821.3	2499.5	2268.9	2188.1
37.5°	2880.0	2678.5	2338.4	2085.6	1994.4
40°	2744.5	2525.1	2169.9	1910.2	1815.0
42.5°	2605.4	2371.4	2001.8	1730.8	1639.6
45°	2459.1	2213.8	1829.8	1569.7	1481.9
47.5°	2320.1	2060.4	1665.2	1405.1	1324.7
50°	2166.4	1906.7	1504.1	1251.3	1174.8
52.5°	2016.2	1741.6	1350.3	1108.8	1039.3
55°	1869.8	1584.5	1189.2	969.8	900.3
57.5°	1719.9	1427.2	1046.7	841.7	783.1
60°	1566.2	1273.4	896.4	710.1	651.5
62.5°	1416.3	1123.6	768.3	592.9	563.7
65°	1262.6	966.0	636.7	512.5	501.2
67.5°	1116.2	819.5	512.5	450.0	439.1
70°	962.5	677.1	424.4	387.8	373.1
72.5°	816.1	545.1	354.8	325.7	318.4
75°	673.2	416.9	292.8	267.1	263.6
77.5°	530.8	296.2	230.6	215.9	208.5
80°	398.8	212.4	175.5	161.1	161.1
82.5°	278.0	142.8	120.7	113.3	113.3
85°	157.3	80.4	69.5	69.5	69.5
87.5°	58.6	29.1	29.1	25.6	25.6
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1



TEST NUMBER: P918492

CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P918492
 CATALOG NUMBER: DFN2DIP-TR4F0-120D090US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.76	12.64	12.66	13.56	14.74	7.73	8.61	8.64	9.54	10.72
	3H	13.44	14.23	14.36	15.16	16.37	8.92	9.71	9.84	10.65	11.85
	4H	14.05	14.79	14.98	15.73	16.95	9.38	10.12	10.31	11.06	12.28
	6H	14.47	15.16	15.42	16.10	17.33	9.70	10.39	10.65	11.33	12.56
	8H	14.60	15.25	15.55	16.21	17.44	9.79	10.45	10.75	11.41	12.63
	12H	14.66	15.28	15.62	16.24	17.49	9.84	10.46	10.80	11.41	12.67
4H	2H	11.78	12.53	12.72	13.46	14.68	8.33	9.08	9.27	10.01	11.23
	3H	13.61	14.23	14.57	15.20	16.43	9.69	10.31	10.64	11.27	12.51
	4H	14.31	14.87	15.27	15.84	17.09	10.24	10.80	11.20	11.77	13.02
	6H	14.83	15.31	15.80	16.30	17.55	10.66	11.15	11.63	12.13	13.39
	8H	15.00	15.46	15.98	16.44	17.70	10.79	11.24	11.77	12.22	13.49
	12H	15.10	15.51	16.09	16.51	17.78	10.86	11.27	11.85	12.26	13.54
8H	4H	14.28	14.73	15.26	15.71	16.98	10.52	10.98	11.50	11.95	13.22
	6H	14.85	15.22	15.85	16.24	17.51	11.04	11.42	12.04	12.44	13.71
	8H	15.06	15.40	16.07	16.41	17.69	11.23	11.57	12.24	12.57	13.86
	12H	15.21	15.50	16.22	16.50	17.83	11.36	11.65	12.37	12.65	13.98
12H	4H	14.23	14.64	15.23	15.64	16.91	10.53	10.94	11.52	11.93	13.21
	6H	14.82	15.15	15.83	16.16	17.45	11.09	11.42	12.10	12.43	13.72
	8H	15.05	15.34	16.06	16.34	17.67	11.31	11.60	12.32	12.60	13.93